



# Extra low mercury

## T8 Standard

Philips T8 lamps are energy-efficient lighting solutions.

### Benefits

- Better for the environment - only 1.7mg of mercury per lamp with ALTO II Technology
- Reduce maintenance costs by extending the relamping cycle

### Features

- 95% lumen maintenance and reduced lamp-end blackening
- Available in multiple wattages: 17W, 25W and 32W
- Available in multiple color temperatures: 3000K, 3500K, 4100K, and 5000K

### Application

- Ideal for applications requiring maximum maintained light output.


### Versions



LPPR F-T8-Unv G13 GB

# T8 Standard

## Dimensional drawing



Product
F17T8/TL835/ALTO 30PK
F17T8/TL841/ALTO 30PK

General Information	
Cap-Base	G13
Light Technical	
Color rendering index (CRI)	85
Luminous Flux	1,375 lm
Operating and Electrical	
Power Consumption	17 W
Mechanical and Housing	
Bulb Shape	T-8 (T8)
Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg

## Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color
			Temperature (Nom)
927850083503	F17T8/TL835/ALTO 30PK	TL835	3500 K

Order Code	Full Product Name	Color Designation	Correlated Color
			Temperature (Nom)
927850084102	F17T8/TL841/ALTO 30PK	TL841	4100 K

