



Extra low mercury

T8 Standard

Philips T8 lamps are energy-efficient lighting solutions.

Benefits

- Better for the environment - only 1.7mg of mercury per lamp with ALTO II Technology
- Reduce maintenance costs by extending the relamping cycle

Features

- 95% lumen maintenance and reduced lamp-end blackening
- Available in multiple wattages: 17W, 25W and 32W
- Available in multiple color temperatures: 3000K, 3500K, 4100K, and 5000K

Application

- Ideal for applications requiring maximum maintained light output.

Warnings and Safety

- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Versions




G13, T8

G13, T8

T8 Standard

Dimensional drawing



Product
F25T8/TL835/ALTO 30PK
F17T8/TL841/ALTO 30PK
F17T8/TL835/ALTO 30PK
F25T8/TL841/ALTO 30PK
F25T8/TL850 ALTO 30PK
F17T8/TL850 ALTO 30PK

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg
General Information	
Cap-Base	G13
Life 12-Hr Instant Start [Hrs]	30000 h
Life 12-Hr Programstart [Hrs]	36000 h
Life 3-Hr Instant Start [Hrs]	24000 h
Life 3-Hr Program Start [Hrs]	30000 h
Mechanical and Housing	
Bulb Shape	T8

Approval and Application

Order Code	Full Product Name	Picogram Per Lumen Hour
281881	F17T8/TL835/ALTO 30PK	54 pg/lm.h
281899	F17T8/TL841/ALTO 30PK	54 pg/lm.h
281907	F25T8/TL835/ALTO 30PK	35 pg/lm.h
281915	F25T8/TL841/ALTO 30PK	35 pg/lm.h
280925	F25T8/TL850 ALTO 30PK	36 pg/lm.h
280909	F17T8/TL850 ALTO 30PK	54 pg/lm.h

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
281881	F17T8/TL835/ALTO 30PK	17 W
281899	F17T8/TL841/ALTO 30PK	17 W
281907	F25T8/TL835/ALTO 30PK	25 W

Order Code	Full Product Name	Power (Rated) (Nom)
281915	F25T8/TL841/ALTO 30PK	25 W
280925	F25T8/TL850 ALTO 30PK	25 W
280909	F17T8/TL850 ALTO 30PK	17 W

Light Technical (1/2)

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)
281881	F17T8/TL835/ALTO 30PK	TL835	TL835	3500 K	85
281899	F17T8/TL841/ALTO 30PK	TL841	TL841	4100 K	85
281907	F25T8/TL835/ALTO 30PK	TL835	TL835	3500 K	85

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)
281915	F25T8/TL841/ALTO 30PK	TL841	TL841	4100 K	85
280925	F25T8/TL850 ALTO 30PK	TL850	TL850	5000 K	82
280909	F17T8/TL850 ALTO 30PK	TL850	TL850	5000 K	82

Light Technical (2/2)

Order Code	Full Product Name	Design Mean Lumens	Luminous Flux (Nom)
281881	F17T8/TL835/ALTO 30PK	1310 lm	1375 lm
281899	F17T8/TL841/ALTO 30PK	1310 lm	1375 lm

Order Code	Full Product Name	Design Mean Lumens	Luminous Flux (Nom)
281907	F25T8/TL835/ALTO 30PK	2045 lm	2150 lm
281915	F25T8/TL841/ALTO 30PK	2045 lm	2150 lm

T8 Standard

Order Code	Full Product Name	Design Mean Lumens	Luminous Flux (Nom)	Order Code	Full Product Name	Design Mean Lumens	Luminous Flux (Nom)
280925	F25T8/TL850 ALTO 30PK	1995 lm	2100 lm	280909	F17T8/TL850 ALTO 30PK	1235 lm	1300 lm

