

Lighting

PHILIPS

Smart CFL-I downlight FBS111/112/113/115/11 6 – a reliable way to create outstanding lighting

Theta FBS110

Our Smart CFL-I downlight is a safe, reliable and flexible solution that comes in five sizes for different cut-outs. Its elegant design guarantees a perfect fit in any retail or hospitality environment. And because the downlight has been designed specifically for CFL-I lamps, installation and maintenance couldn't be any simpler.

Benefits

- Safe
- Durable
- Flexible

Features

- · Specular diamond faceted reflector for a wide and efficient beam
- · Special sandblasted louver for glare-free visual comfort
- · New class I three-way connector and sleeving to prevent electrical shocks
- · New self-adjusting mounting clips for easy installation
- Suitable for wide range of retrofit energy saving lamps 3W to 23W CFLs (may varies for different type of luminaires)
- · CCC-certified; truly safe and reliable
- Available in five sizes for different cut-outs; two models can be adjusted to accommodate more types of lamp
- · Elegant design; integrates perfectly into shop and hotel environments

Theta FBS110

Application

- Households
- Condominiums
- Shops
- Hotels
- Restaurants
- Offices
- Hospitals
- Shopping areas
- Office lobbies
- Hotels, restaurants, hospitals and other public areas

Specifications

Туре	FBS111 (cut out Ø 125 mm version)		
	FBS112 (cut out Ø 70 mm version)		
	FBS113 (cut out Ø 105 mm version)		
	FBS115 (cut out Ø 160 mm version)		
	FBS116 (cut out Ø 175 mm version)		
Light source	Compact fluorescent:		
	- 1 x Genie / E27 / 5-18 W		
	- 1 x Tornado / E27 / 5-15 W		
	- 1 x Essential / E27 / 8-18 W		

Lamp included	No
Lamp position	Vertical
Light distribution	Direct
Optic	Prismatic reflector, medium beam
Material	Housing: anodized aluminum
	Optic: spinned aluminum
Color	White
Installation	Fixation by means of spring fasteners
Maintenance	Direct lamp access

Versions



Theta FBS115 downlight



Theta FBS110 downlight

Theta FBS110

Approval and Application			
Ingress protection code	IP20		
Operating and Electrical			
Input Voltage	220 to 240 V		
Maximum lamp power	MAX18		
General Information			
Cap-Base	E27		
Protection class IEC	Safety class II (II)		
Kombipack	-		
Number of light sources	1		
Mechanical and Housing			
Colour	White		

General Information

Order Code	Full Product Name	Country version	Gear	Lamp family code	Lamp power
910403630467	FBS115 MAX18W-E27 220-240V	NO	-	-	-
911401141480	FBS110 C MAX18W-E27 220-240V TH	ТН	-	ESSENTIAL	18 W
911401154780	FBS110 C MAX18W-E27 220-240V ID	ID	-	ESSENTIAL	18 W



© 2018 Philips Lighting Holding B.V. All rights reserved. Philips Lighting reserves the right to make changes in specifications and/or to discontinue any product at any timewithout notice or obligation and will not be liable for any consequences resulting from the use of this publication.

www.lighting.philips.com 2018, July 5 - data subject to change