



Philips Halogen Aluminum Reflector Lamps

ALR 37/56 mm

Delivers high lumen output and excellent color rendering for precise accent and display lighting. Philips Halogen Aluminum Reflector Lamps provide continuous color and high luminous intensity for precise accent and display lighting. These lamps offer a rated average life ranging from 2000 hours and feature excellent beam qualities for accent or ambient lighting.

Benefits

- No harsh streaks or hotspots, directs all heat out of fixture, eliminates stray light, superior beam control.
- Reduces fading and protects reflector for continuous color.
- Securely mounts in fixture, won't freeze in socket and allows less obtrusive luminaire design.

Features

- Aluminum Reflector.
- Front Cover Glass.
- Corrosion-Resistant Bayonet Base.
- Lightweight Compact-Light Source.
- Available in: ALR 37: 20 watt; ALR 56: 50 watt.

Application

- Ideal for display lighting, accent lighting, task lighting and wall washing.

ALR 37/56 mm

Versions




B15/BA15d R37 Frosted

Dimensional drawing

□

Product	D (max)	C (max)
GBF 20W 12V 32DEG 50PK	38 mm	41 mm




Accent Diagrams



ALR 37/56 mm

Beam Diagrams



LDBE_HALUPAB_20W_32D-Beam diagram

