



Low Voltage Capsules

Low Voltage Capsules

Functional light with substantial energy savings. Philips Halogen Low Voltage Capsules provide sparkling, white light. These lamps offer an average rated life of 2000 hours making them perfect for undercabinet or task lighting.

Benefits

- Bright white light

Features

- Must always be used in an enclosed fixture.
- Low voltage types require a fixture with a 12 volt transformer. Never interchange 12 and 120 volt types.
- Available in: T3: 10 and 20 watt; T4: 35, 50 and 75 watt.

Application


- Ideal for desk lamps, undercabinet fixtures, cabinet lighting, and more.

Warnings and Safety

- This lamp is pressurized and could shatter, so to avoid any injury and to avoid exposure to ultraviolet radiation, use only in fixtures that provide a protective shield of tempered glass.

Low Voltage Capsules

Dimensional drawing



Product	D (max)	L	C (max)
BC20W/T3/LAND/TP/12VCAPSULE 2PK	10 mm	22 mm	33 mm
CAPSL 20W G4 12V CL 1BL/12	10 mm	22 mm	33 mm

General Information	
Cap-Base	G4
Rated Lifetime (Hours)	2,000 hour(s)
Switching Cycle	8,000
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux	255 lm
Operating and Electrical	
Voltage (Nom)	12 V
Power Consumption	20 W
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T9

General Information

Order Code	Full Product Name	Nominal lifetime
924062217123	BC20W/T3/LAND/TP/12VCAPSULE 2PK	2,000,000 hour(s)
924062217184	CAPSL 20W G4 12V CL 1BL/12	2,000 hour(s)

