



Mini-Candelabra

Mini-Candelabra

Bright, white light with higher performance for accent lighting. Halogen Mini Candelabra T4 Capsule lamps provide bright, white light for decorative and accent lighting and general illumination. Offered in T4 bulb size with mini candelabra base configurations. These lamps offer a rated average life ranging from 1000 to 2000 hours depending upon the product. * Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

Benefits

- Compact size fits most decorative, accent and specialty fixtures.
- Available in a variety of wattages to meet most application needs.

Features

- Bright, white light.
- Must always be used in an enclosed fixture.
- 120 volt types require a fixture specifically designed for 120 volt operation. Never interchange 12 and 120 volt types.
- Available in 50, 75, 100, 150, 250 and 500 Watts.

Application

- Ideal for indoor decorative and accent lighting such as wall sconces, undercabinet lighting, and jewelry display cabinets. Not for use in low voltage fixtures.


Mini-Candelabra

Versions



Mini Candelabra T-4 Clear

Dimensional drawing



Product

BC50Q/CL 120V 12/1PK

BC100Q/CL ESN 12/1P

Operating and electrical

Voltage (Nom) 120 V

General information

Cap-Base E11
Operating Position Universal
Rated Lifetime (Hours) 1000 h

Light technical

Color Rendering Index (Nom) 100

Mechanical and housing

Bulb Finish Clear
Bulb Shape T4

Operating and electrical

Order Code	Full Product Name	Power (Nom)
415554	BC50Q/CL 120V 12/1PK	50 W

Order Code	Full Product Name	Power (Nom)
416339	BC100Q/CL ESN 12/1PK	100 W

Light technical

Mini-Candelabra

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux (Nom)
415554	BC50Q/CL 120V 12/1PK	-	-

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux (Nom)
416339	BC100Q/CL ESN 12/1PK	2800 K	1600 lm

