



# Philips Twistline GU10

## Twistline GU10

Bright, white accent light with superior energy savings Philips Twistline GU10 Philips Halogen Twistline MR16 with GU10 base provide bright white accent light. The twist and lock base enables easy installation and a secure fit. Suited for track and recessed lighting applications.

### Benefits

### Features

### Application

### Versions




20W/25W35W/40W, GU10



50W, GU10, MR16

# Twistline GU10

## Dimensional drawing



Product
BC50GU10/HAL/TL 120V 6/3
50TWISTERLINE/FL 120V5/6
BC50TWISTLINE GU10/FL25 TP
BC50TWISTLINE GU10/FL 6/6
BC25 TWISTLINE GU10 / FL25
BC35 TWISTLINE GU10/FL25 TP

Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Controls and Dimming	
Dimmable	Yes
Operating and Electrical	
Voltage (Nom)	120 V
Starting Time (Nom)	0.0 s
General Information	
Cap-Base	GU10
Nominal Lifetime (Nom)	2000 h
Operating Position	UNIVERSAL
Rated Lifetime (Hours)	2000 h
Light Technical	
Correlated Color Temperature (Nom)	2800 K
Color Rendering Index (Nom)	100
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16

## Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
924712536386	BC50TWISTLINE GU10/FL 6/6	50 W
924887136384	BC35 TWISTLINE GU10/FL25 TP	35 W
924887736301	BC25 TWISTLINE GU10 / FL25	25 W
925691836307	BC50TWISTLINE GU10/FL25 TP	50 W
925691836308	50TWISTERLINE/FL 120V5/6	50 W
925691836309	BC50GU10/HAL/TL 120V 6/3	50 W

## General Information

Order Code	Full Product Name	Philips Code
924712536386	BC50TWISTLINE GU10/FL 6/6	NA
924887136384	BC35 TWISTLINE GU10/FL25 TP	-
924887736301	BC25 TWISTLINE GU10 / FL25	-

Order Code	Full Product Name	Philips Code
925691836307	BC50TWISTLINE GU10/FL25 TP	-
925691836308	50TWISTERLINE/FL 120V5/6	-
925691836309	BC50GU10/HAL/TL 120V 6/3	-


## Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Luminous Intensity (Max)	Rated Beam Angle
924712536386	BC50TWISTLINE GU10/FL 6/6	40 °	400 cd	-


Order Code	Full Product Name	Beam Angle (Nom)	Luminous Intensity (Max)	Rated Beam Angle
924887136384	BC35 TWISTLINE GU10/FL25 TP	20 °	800 cd	-

# Twistline GU10

Order Code	Full Product Name	Beam Angle (Nom)	Luminous Intensity (Max)	Rated Beam Angle
924887736301	BC25 TWISTLINE GU10 / FL25	25 °	400 cd	25 °
925691836307	BC50TWISTLINE GU10/FL25 TP	25 °	700 cd	-
925691836308	50TWISTERLINE/FL 120V5/6	25 °	700 cd	-
925691836309	BC50GU10/HAL/TL 120V 6/3	25 °	700 cd	-




## Accent Diagrams



LDAC\_HTWIST\_Dichr\_25D-Accent diagram

## Beam Diagrams



LDBE\_HTWIST\_Dichr\_25D-Beam diagram

