



Product Description

Accentline

Low-voltage halogen burner optically positioned in a glass reflector with and without front glass

Benefits

- Good light quality, cool beam halogen light and a professional lifetime


Features

- Dichroic reflector coating is heat-transmitting towards the back and light-reflecting towards the front of the lamp
- UV-Block burner
- Excellent colour rendering
- GU5.3 base for extra retention in luminaire
- 3,000 hour lifetime

Application

- Accent, task lighting and decorative applications in homes, shops, hotels and restaurants

Dimensional drawing



Product	D (max)	C (max)
Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm
Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm
Accentline 20W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Voltage (Nom)	12 V
Starting Time (Nom)	0.0 s
Warm Up Time To 60% Light (Nom)	instant full light s

General Information

Cap-Base	GU5.3
Nominal Lifetime (Nom)	4000 h
Life To 50% Failures (Nom)	4000 h
Operating Position	UNIVERSAL
Rated Lifetime (Hours)	4000 h
Switching Cycle	16,000X

Light Technical

Beam Angle (Nom)	36 °
Correlated Colour Temperature (Nom)	3000 K
Colour Rendering Index (Nom)	100
Rated Beam Angle	36 °

Mechanical and Housing

Bulb Shape	MR16
------------	------

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
58842000	Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F	37 kWh
58845100	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	53 kWh

Operating and Electrical

Order Code	Full Product Name	Power (Nom)
58842000	Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F	35 W

Order Code	Full Product Name	Power (Nom)
58845100	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	50 W

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Intensity (Max)
58842000	Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F	430 lm	1000 cd

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Intensity (Max)
58845100	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	680 lm	1500 cd

