



# Product Description:

## ET-S transformer

High-Frequency electronic transformer for operation with 12V halogen lamps, available in 70W, 105W and 150W versions

### Benefits

- High efficiency compared with magnetic transformer
- Easy luminaire design-in with EMI compliance
- Dimmable with Philips-approved leading- and trailing-edge dimmers

### Features

- 30,000 hours lifetime
- EMI-compliant
- Screw connector
- CE, SELV approval
- Safe operation with overload, short circuit and overheating protection

### Application


- Indoor residential use including living rooms and decorative and accent lighting
- Professional applications including retail, offices, conference rooms and exhibitions

ET-S transformer

Versions



Dimensional drawing



Product	D1	C1	B2	A1	A2	B1
ET-S 15 LED 220-240V	3.4 mm	29.0 mm	23.4 in	115.0 mm	105.0 mm	45.0 mm

