



# Spot of crisp white light – modern alternative to conventional reflector lamps

## HalogenA PAR30S

Mains-voltage halogen reflector that is easy to install instead of conventional reflector lamps, putting your objects in a superior-quality spot light. Provides crisp halogen light over a long lifetime.

### Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Low replacement costs due to long lifetime

### Features

- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Universal burning position
- Instant start

### Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops

# HalogenA PAR30S

## Versions




E27, PAR30S, 30°


## Dimensional drawing

D

Product	D (max)	C (max)
HalogenA Par30s 75W E27 230V 25D 1CT/15	96 mm	99 mm




## Accent Diagrams



LDAC\_HPAR30S\_75W\_30D-Accent diagram

# HalogenA PAR30S

## Beam Diagrams



LDBE\_HPAR30S\_75W\_30D-Beam diagram

