



產品說明

HF-Selectalume II for TL-D lamps

價格合理、品質可靠、符合 CE 的 TL-D 螢光燈管專用高頻電子安定器，是電磁 (EM) 安定器的理想替代產品

优点

- Exceptional energy efficiency with striation-reduction technology in lighting systems at lower temperatures
- Maximum reliability in system operation
- Provides extended lamp life in frequent-switching applications

特点

- Highest CELMA Energy Efficiency Index A2 BAT*
- Complies with CE, ENEC, EL, VDE-EMC, CCC marks of conformity
- Average nominal service lifetime over 85,000 hours (at Ta 50°C) with a failure rate ≤ 0.1 % per 1,000 hours)
- Optimized lamp preheating for min 50,000 On/Off switch operations without replacement of lamps

应用





- 如欲降低每平方公尺瓦數或減少營運成本，即十分適用，常見的照明用途如下：
- 非常適合未安裝控制裝置的應用。
- 運作時數長的專業室內應用（例如辦公大樓、客服中心、教室和旅館）
- 百貨公司、商店、超市、便利商店和
- 運作時數長的工業場所（例如走廊和低隔間管道系統）
- 市區停車場

HF-Selectalume II for TL-D lamps

Versions



二维绘图



Product	D1	C1	A1	A2	B1
HF-S 258 TL-D II 220-240V 50/60Hz	4.1 mm	28.0 mm	280.0 mm	265.0 mm	30.0 mm

Product	A1	B1	C1	A2	B2	D1
HF-S 118/136 TL-D II 220-240V 50/60Hz	280 mm	30 mm	28 mm	265 mm		4.2 mm
HF-S 218/236 TL-D II 220-240V 50/60Hz	280 mm	30 mm	28 mm	265 mm		4.2 mm
HF-S 3/4 18 TL-D II 220-240V 50/60Hz	280 mm	39 mm	28 mm	265 mm		4.2 mm
HF-S 218 TL-D II 220-240V 50/60Hz	280 mm	30 mm	28 mm	265 mm		4.2 mm

運作和電氣

輸入頻率	50 至 60 Hz
輸入電壓	220-240 V

基本資訊

燈具類型	TL-D
------	------

應用

Order Code	Full Product Name	能源效益指數
913713032166	HF-S 118/136 TL-D II 220-240V 50/60Hz	A2 BAT
913713032366	HF-S 218 TL-D II 220-240V 50/60Hz	A2
913713032466	HF-S 218/236 TL-D II 220-240V 50/60Hz	A2 BAT

Order Code	Full Product Name	能源效益指數
913713032566	HF-S 258 TL-D II 220-240V 50/60Hz	A2 BAT
913713032666	HF-S 3/4 18 TL-D II 220-240V 50/60Hz	A2/A2BAT

HF-Selectalume II for TL-D lamps

緊急操作

Order Code	Full Product Name	備用安定器流明因數 (EBLF)(標稱)
913713032166	HF-S 118/136 TL-D II 220-240V 50/60Hz	100 %
913713032366	HF-S 218 TL-D II 220-240V 50/60Hz	0.7 %
913713032466	HF-S 218/236 TL-D II 220-240V 50/60Hz	100 %

Order Code	Full Product Name	備用安定器流明因數 (EBLF)(標稱)
913713032566	HF-S 258 TL-D II 220-240V 50/60Hz	100 %
913713032666	HF-S 3/4 18 TL-D II 220-240V 50/60Hz	100 %

基本資訊

Order Code	Full Product Name	MCB 產品數量 (16 A)	
		B 型)(標稱)	燈具數
913713032166	HF-S 118/136 TL-D II 220-240V 50/60Hz	28	1 piece/unit
913713032366	HF-S 218 TL-D II 220-240V 50/60Hz	-	2 piece/unit
913713032466	HF-S 218/236 TL-D II 220-240V 50/60Hz	28	2 piece/unit

Order Code	Full Product Name	MCB 產品數量 (16 A)	
		B 型)(標稱)	燈具數
913713032566	HF-S 258 TL-D II 220-240V 50/60Hz	12	2 piece/unit
913713032666	HF-S 3/4 18 TL-D II 220-240V 50/60Hz	28	3/4 piece/unit

機械和殼體

Order Code	Full Product Name	外罩
913713032166	HF-S 118/136 TL-D II 220-240V 50/60Hz	L 280x30x28
913713032366	HF-S 218 TL-D II 220-240V 50/60Hz	L 280x30x28
913713032466	HF-S 218/236 TL-D II 220-240V 50/60Hz	L 280x30x28

Order Code	Full Product Name	外罩
913713032566	HF-S 258 TL-D II 220-240V 50/60Hz	L 280x30x28
913713032666	HF-S 3/4 18 TL-D II 220-240V 50/60Hz	L 280x39x28

系統特性

Order Code	Full Product Name	PL-L 上的	TL-D 上的額定燈	額定安定器 -
		燈具功率	具功率	燈具功率
913713032166	HF-S 118/136 TL-D II 220-240V 50/60Hz	-	35 W	36 W
913713032366	HF-S 218 TL-D II 220-240V 50/60Hz	-	32.6 W	18 W
913713032466	HF-S 218/236 TL-D II 220-240V 50/60Hz	61.2 W	63.9/32.9 W	36/18 W

Order Code	Full Product Name	PL-L 上的	TL-D 上的額定燈	額定安定器 -
		燈具功率	具功率	燈具功率
913713032566	HF-S 258 TL-D II 220-240V 50/60Hz	-	102 W	58 W
913713032666	HF-S 3/4 18 TL-D II 220-240V 50/60Hz	-	52.3/66.0 W	18 W

