



Brighten your home with infinite possibilities

DuraMax Deco Bent Tip

Philips DuraMax® Long Life Decorative bent tip bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Philips Duramax decorative bent tip bulbs are available in a variety of wattages with clear and frost finishes. The clear bulbs provide decorative sparkle, while the frost bulbs add a soft glow to add a pleasant touch to home decor.

Benefits

- Philips DuraMax long life decorative bent tip light bulbs last longer than standard incandescent, significantly reducing the hassle of replacing light bulbs that burn out too quickly.
- Philips DuraMax decorative bent tip bulbs add a pleasant touch to home décor.

Features


- Lasts at Least OneYear!*
- Available in a variety of wattages.
- Frosted light bulbs provide soft white light.
- Clear light bulbs provide decorative sparkle.
- Candelabra base.
- Available in 15 watt clear and 25, 40, and 60 watt clear and frost.
- *Based on an average of hours usage per day/7 days per week. Hours differ between products, and there are exceptions. See individual products for detail

Application


- Ideal for general or ambient lighting in wall sconces, chandeliers, and other decorative light fixtures.

DuraMax Deco Bent Tip


Versions



E12, BA9, Frosted





E26, BA9 1/2, Clear



E12, BA9, Clear

Dimensional drawing



Product

BC40BA9C/3FLL 120V 6/2
 BC25BA9C/LL 120V 6/2
 BC25BA9C/CL/LL 6/4
 BC40BA9C/LL 120V 6/2
 BC60BA9C/CL/LL 6/4
 BC60BA9C/LL 120V 6/2
 BC40BA9C/CL/LL 6/4
 BC15BA9C/LL 120V 6/2

Product

BC40BA9-1/2/CL/LL 120V 6/4
 BC40BA9-1/2/CL/LL 6/2 TP

Operating and Electrical

Voltage (Nom) 120 V

General Information

Main Application Decorative
 Operating Position Base Down +/-
 90 D
 Rated Lifetime (Hours) 2000 h

Operating and Electrical

DuraMax Deco Bent Tip

Order Code	Full Product Name	Power (Rated) (Nom)
168096	BC40BA9C/3FLL 120V 6/2	40 W
167601	BC40BA9-1/2/CL/LL 120V 6/4	40 W
168203	BC40BA9-1/2/CL/LL 6/2 TP	40 W
168112	BC15BA9C/LL 120V 6/2	15 W
168062	BC25BA9C/LL 120V 6/2	25 W

Order Code	Full Product Name	Power (Rated) (Nom)
167197	BC25BA9C/CL/LL 6/4	25 W
168070	BC40BA9C/LL 120V 6/2	40 W
167205	BC40BA9C/CL/LL 6/4	40 W
168088	BC60BA9C/LL 120V 6/2	60 W
167213	BC60BA9C/CL/LL 6/4	60 W

General Information

Order Code	Full Product Name	Cap-Base
168096	BC40BA9C/3FLL 120V 6/2	E12
167601	BC40BA9-1/2/CL/LL 120V 6/4	E26
168203	BC40BA9-1/2/CL/LL 6/2 TP	E26
168112	BC15BA9C/LL 120V 6/2	E12
168062	BC25BA9C/LL 120V 6/2	E12

Order Code	Full Product Name	Cap-Base
167197	BC25BA9C/CL/LL 6/4	E12
168070	BC40BA9C/LL 120V 6/2	E12
167205	BC40BA9C/CL/LL 6/4	E12
168088	BC60BA9C/LL 120V 6/2	E12
167213	BC60BA9C/CL/LL 6/4	E12

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
168096	BC40BA9C/3FLL 120V 6/2	295 lm
167601	BC40BA9-1/2/CL/LL 120V 6/4	300 lm
168203	BC40BA9-1/2/CL/LL 6/2 TP	300 lm
168112	BC15BA9C/LL 120V 6/2	110 lm
168062	BC25BA9C/LL 120V 6/2	150 lm

Order Code	Full Product Name	Luminous Flux (Nom)
167197	BC25BA9C/CL/LL 6/4	150 lm
168070	BC40BA9C/LL 120V 6/2	300 lm
167205	BC40BA9C/CL/LL 6/4	300 lm
168088	BC60BA9C/LL 120V 6/2	550 lm
167213	BC60BA9C/CL/LL 6/4	550 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
168096	BC40BA9C/3FLL 120V 6/2	Frosted	BA9
167601	BC40BA9-1/2/CL/LL 120V 6/4	Clear	BA-9 1/2
168203	BC40BA9-1/2/CL/LL 6/2 TP	Clear	BA-9 1/2
168112	BC15BA9C/LL 120V 6/2	Clear	BA9
168062	BC25BA9C/LL 120V 6/2	Clear	BA9

Order Code	Full Product Name	Bulb Finish	Bulb Shape
167197	BC25BA9C/CL/LL 6/4	Clear	BA9
168070	BC40BA9C/LL 120V 6/2	Clear	BA9
167205	BC40BA9C/CL/LL 6/4	Clear	BA9
168088	BC60BA9C/LL 120V 6/2	Clear	BA9
167213	BC60BA9C/CL/LL 6/4	Clear	BA9

