



Reflector Flood

Reflector Flood

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.

Features

- For parties, holiday lighting and decorative effects.
- Available in BR, R and PAR shapes in 45W, 50W, 65W, 85W, 120W and 300W versions.

Application

- Ideal for indoor recessed and track fixtures and outdoor landscape fixtures.

Versions



E26, BR40, Flood, Frosted



E26, BR30, Frosted





E26, R20, Frosted



E26, BR40, Flood, Clear

Reflector Flood

Dimensional drawing



Product	C (max)
45R20 130V 12/1	3.94 in

Product
65BR/FL60 130V CDA 24/1
65BR/FL60 120V 24/1
300BR/FL 120/130V 24/1
65BR40/FL 130V 12/1 PRO

Product
65BR30/FL 130V 12/1 PRO
65BR30/FL55 120V 12/1
65BR30/FL55 CDA 130V
65BR30/FLVALUE PACK 1/12

General Information

Cap-Base	E26
Rated Lifetime (Hours)	2000 h

Light Technical

Beam Description	Flood
------------------	-------

Approval and Application

Order Code	Full Product Name	Estimated Energy Cost Per Year
389130	65BR/FL60 120V 24/1	7.83 \$
225375	65BR/FL60 130V CDA 24/1	7.83 \$
143438	300BR/FL 120/130V 24/1	-
248849	65BR30/FL55 CDA 130V	7.83 \$
248872	65BR30/FLVALUE PACK 1/12	7.83 \$

Order Code	Full Product Name	Estimated Energy Cost Per Year
248765	65BR30/FL55 120V 12/1	7.83 \$
140079	65BR30/FL 130V 12/1 PRO	7.83 \$
203224	45R20 130V 12/1	-
140087	65BR40/FL 130V 12/1 PRO	7.83 \$

Reflector Flood

Operating and Electrical

Order Code	Full Product Name	Lamp Wattage Rated@120V	Voltage (Nom)	Power (Rated) (Nom)
389130	65BR/FL60 120V 24/1	-	120 V	65 W
225375	65BR/FL60 130V CDA 24/1	55 W	130 V	65 W
143438	300BR/FL 120/130V 24/1	-	120 V	300 W
248849	65BR30/FL55 CDA 130V	55 W	130 V	65 W
248872	65BR30/FLVALUE PACK 1/12	-	120 V	65 W

Order Code	Full Product Name	Lamp Wattage Rated@120V	Voltage (Nom)	Power (Rated) (Nom)
248765	65BR30/FL55 120V 12/1	-	120 V	65 W
140079	65BR30/FL 130V 12/1 PRO	55 W	130 V	65 W
203224	45R20 130V 12/1	-	130 V	45 W
140087	65BR40/FL 130V 12/1 PRO	55 W	130 V	65 W

General Information

Order Code	Full Product Name	Life With 3		Operating Position
		Hour Per Day Use	Main Application	
389130	65BR/FL60 120V 24/1	1.8 a	Flood and Ambient Lighting	Base Up Horizontal (BUH)
225375	65BR/FL60 130V CDA 24/1	1.8 a	Indoor Reflector	Universal
143438	300BR/FL 120/130V 24/1	-	Indoor Reflector	Universal
248849	65BR30/FL55 CDA 130V	1.8 a	Indoor Reflector	Universal

Order Code	Full Product Name	Life With 3		Operating Position
		Hour Per Day Use	Main Application	
248872	65BR30/FLVALUE PACK 1/12	1.8 a	Indoor Reflector	Universal
248765	65BR30/FL55 120V 12/1	1.8 a	Indoor Reflector	Universal
140079	65BR30/FL 130V 12/1 PRO	1.8 a	Indoor Reflector	Universal
203224	45R20 130V 12/1	-	Indoor Reflector	Universal
140087	65BR40/FL 130V 12/1 PRO	1.8 a	Flood and Ambient Lighting	Universal

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Luminous	
				Flux Lamp @ 120V	Luminous Flux (Nom)
389130	65BR/FL60 120V 24/1	60 °	2710 K	-	620 lm
225375	65BR/FL60 130V CDA 24/1	60 °	2750 K	425 lm	565 lm
143438	300BR/FL 120/130V 24/1	55 °	-	-	2480 lm
248849	65BR30/FL55 CDA 130V	55 °	2680 K	450 lm	605 lm
248872	65BR30/FLVALUE PACK 1/12	55 °	2710 K	-	620 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Luminous	
				Flux Lamp @ 120V	Luminous Flux (Nom)
248765	65BR30/FL55 120V 12/1	55 °	2710 K	-	620 lm
140079	65BR30/FL 130V 12/1 PRO	300 °	2680 K	450 lm	605 lm
203224	45R20 130V 12/1	-	-	-	380 lm
140087	65BR40/FL 130V 12/1 PRO	55 °	2750 K	425 lm	565 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
389130	65BR/FL60 120V 24/1	Frosted	BR40
225375	65BR/FL60 130V CDA 24/1	Frosted	BR40
143438	300BR/FL 120/130V 24/1	Frosted	BR40
248849	65BR30/FL55 CDA 130V	Frosted	BR30

Order Code	Full Product Name	Bulb Finish	Bulb Shape
248872	65BR30/FLVALUE PACK 1/12	Frosted	BR30
248765	65BR30/FL55 120V 12/1	Frosted	BR30
140079	65BR30/FL 130V 12/1 PRO	Frosted	BR30
203224	45R20 130V 12/1	Frosted	R-20 (R20)

Reflector Flood

Order Code	Full Product Name	Bulb Finish	Bulb Shape
140087	65BR40/FL 130V 12/1 PRO	Clear	BR40

