



Product Description

Standard Candle B35 clear

Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with B- or E-base

Benefits

- At their best in decorative glass chandeliers and wall brackets with clear or textured glass bowls
- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

Features

- Slender, crystal-clear lamps designed for sparkling highlights
- Creates a classic sparkling atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches

Standard Candle B35 clear

Dimensional drawing

Product	D	C (max)
Standard 40W E14 220-240V B35 CL 1CT/5X10F	35 mm	100 mm
Standard 25W E14 220-240V B35 CL 1CT/5X10F	35 mm	100 mm

Approval and Application	
Energy Efficiency Label (EEL)	E
Operating and Electrical	
Voltage (Nom)	220-240 V
General Information	
Cap-Base	E14
Nominal Lifetime (Nom)	1000 h
Operating Position	UNIVERSAL
Rated Lifetime (Hours)	1000 h
Light Technical	
Colour Rendering Index (Nom)	100
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
921486543301	Standard 25W E14 220-240V B35 CL 1CT/5X10F	25 W
921491543301	Standard 40W E14 220-240V B35 CL 1CT/5X10F	40 W

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
921486543301	Standard 25W E14 220-240V B35 CL 1CT/5X10F	210 lm

Order Code	Full Product Name	Luminous Flux (Nom)
921491543301	Standard 40W E14 220-240V B35 CL 1CT/5X10F	410 lm

Controls and Dimming

Order Code	Full Product Name	Dimmable
921486543301	Standard 25W E14 220-240V B35 CL 1CT/5X10F	-

Order Code	Full Product Name	Dimmable
921491543301	Standard 40W E14 220-240V B35 CL 1CT/5X10F	Yes

Standard Candle B35 clear

