



# Lamp:

## Standard Candle B35 frosted

Flame-shaped bulb with clear or inside-frosted glass and vacuum- or gas-filled bulb

### Benefits

- Graceful lamps that enhance the elegance of classical chandeliers, candelabras, wall brackets etc.
- Set the scene for cosiness and comfort, used with or without lampshades

### Features

- Clear lamps:
  - slender, crystal-clear lamps designed for sparkling highlights
  - creates a classic sparkling atmosphere
- Frosted lamps:
  - slender, frosted lamps
  - creates a low-glare atmosphere
- Universal burning position except for some 60W types which must be operated vertically, base-down (tolerance 90°)

### Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches

# Standard Candle B35 frosted

## Versions



E14, B35, FR

## Dimensional drawing

Product	D	C (max)
Standard 40W E14 220-240V B35 FR 1CT/5X10F	35 mm	100 mm
Standard 25W E14 220-240V B35 FR 1CT/5X10F	35 mm	100 mm

Controls and Dimming	
Dimmable	Yes
Operating and Electrical	
Voltage (Nom)	220-240 V
General Information	
Cap-Base	E14
Nominal Lifetime (Nom)	1000 h
Operating Position	UNIVERSAL
Rated Lifetime (Hours)	1000 h
Light Technical	
Colour Rendering Index (Nom)	100
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35

## Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
921486643301	Standard 25W E14 220-240V B35 FR 1CT/5X10F	25 W
921491643301	Standard 40W E14 220-240V B35 FR 1CT/5X10F	40 W

## Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
921486643301	Standard 25W E14 220-240V B35 FR 1CT/5X10F	210 lm

Order Code	Full Product Name	Luminous Flux (Nom)
921491643301	Standard 40W E14 220-240V B35 FR 1CT/5X10F	410 lm

## Standard Candle B35 frosted

