



Product Description

Standard Extra Low Voltage A60

Clear lamp (A-bulb) for operation on voltages of 12, 24, 42 and 50 V

Benefits

- Provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications
- Gas-filled lamp has a clear glass are ideally suited for remote, isolated areas where energy has to be supplied by private generating plants, batteries or other low-voltage sources
- Used when brilliance is an advantage

Features

- Types till 42 V are safer in combination with a mains power supply transformer

Application

- Rural and isolated areas where mains power supplies are not available
- Emergency lighting installations

Versions



Standard Extra Low Voltage A60

Dimensional drawing

Product	D (max)	C (max)
Standard ELV 60W E27/BRC 12V A60 CL 1CT/20	60 mm	107.5 mm
Standard ELV 60W E27/BRC 24V A60 CL 1CT/20	60 mm	107.5 mm
Standard ELV 60W E27/BRC 50V A60 CL 1CT	60 mm	107.5 mm
Standard ELV 40W E27/BRC 24V A60 CL 1CT	60 mm	107.5 mm

Controls and Dimming	
Dimmable	Yes
Operating and Electrical	
Starting Time (Nom)	0.0 s
Warm Up Time To 60% Light (Nom)	instant full light
General Information	
Cap-Base	E27
Nominal Lifetime (Nom)	1000 h
Operating Position	UNIVERSAL
Rated Lifetime (Hours)	1000 h
Switching Cycle	4,000X
Light Technical	
Correlated Colour Temperature (Nom)	2700 K
Colour Rendering Index (Nom)	100
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h	Energy Efficiency Label (EEL)
02293684	STAN ELV 40W E27/BRC 24V A60 CL 1CT	40 kWh	D
09017105	STAN ELV 60W E27/BRC 12V A60 CL 1CT/20	60 kWh	C
09018805	STAN ELV 60W E27/BRC 24V A60 CL 1CT/20	60 kWh	D
10188484	STAN ELV 60W E27/BRC 50V A60 CL 1CT	60 kWh	D

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power (Rated) (Nom)
02293684	STAN ELV 40W E27/BRC 24V A60 CL 1CT	24 V	40 W
09017105	STAN ELV 60W E27/BRC 12V A60 CL 1CT/20	12 V	60.0 W
09018805	STAN ELV 60W E27/BRC 24V A60 CL 1CT/20	24 V	60.0 W

Order Code	Full Product Name	Voltage (Nom)	Power (Rated) (Nom)
10188484	STAN ELV 60W E27/BRC 50V A60 CL 1CT	50 V	60.0 W

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
02293684	STAN ELV 40W E27/BRC 24V A60 CL 1CT	580 lm	580 lm

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
09017105	STAN ELV 60W E27/BRC 12V A60 CL 1CT/20	990 lm	990 lm

Standard Extra Low Voltage A60

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
09018805	STAN ELV 60W E27/BRC 24V A60 CL 1CT/20	970 lm	970 lm

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
10188484	STAN ELV 60W E27/BRC 50V A60 CL 1CT	810 lm	810 lm

