



## Lampade:

### Bassa Tensione A60

Lampade ad incandescenza chiare da utilizzare a tensioni di 12, 24 e 50 V.

#### Vantaggi

- Provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications
- Gas-filled lamp has a clear glass are ideally suited for remote, isolated areas where energy has to be supplied by private generating plants, batteries or other low-voltage sources
- Used when brilliance is an advantage

#### Caratteristiche

- Classica forma a goccia, vetro chiaro e attacco a vite E27.

#### Applicazione


- Zone rurali e isolate in cui non sia disponibile l'alimentazione di rete.
- Impianti di illuminazione di emergenza.

#### Versions



## Bassa Tensione A60

### Disegno tecnico



Product	D (max)	C (max)
Stan ELV 60W E27/BRC 12V A60 CL 1CT/20	60 mm	107,5 mm

