



# Product Description

## Standard Lustre P45 clear

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E-base

### Benefits

- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

### Features



- Small, crystal-clear lamps designed for sparkling highlights
- At their best in decorative small luminaires such as table models and wall brackets with clear glass bowls
- Creates a sparkling atmosphere

### Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas

# Standard Lustre P45 clear

## Dimensional drawing



Product	D	C (max)
Stan 40W E14 230V P45 CL 1CT/10X10F	45 mm	78 mm

Product	D	C (max)
Stan 40W E27 230V P45 CL 1CT/10X10F	45 mm	73 mm
Stan 60W E27 230V P45 CL 1CT/10X10F	45 mm	73 mm

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45

## General Information

Order Code	Full Product Name	Cap-Base	Operating Position
06702950	STAN 60W E27 230V P45 CL 1CT/10X10F	E27	S90
01188650	STAN 40W E27 230V P45 CL 1CT/10X10F	E27	UNIVERSAL

Order Code	Full Product Name	Cap-Base	Operating Position
01186250	STAN 40W E14 230V P45 CL 1CT/10X10F	E14	UNIVERSAL

## Light Technical

Order Code	Full Product Name	Luminous Flux
06702950	STAN 60W E27 230V P45 CL 1CT/10X10F	640 lm

# Standard Lustre P45 clear

Order Code	Full Product Name	Luminous Flux
01188650	STAN 40W E27 230V P45 CL 1CT/10X10F	390 lm
01186250	STAN 40W E14 230V P45 CL 1CT/10X10F	405 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
06702950	STAN 60W E27 230V P45 CL 1CT/10X10F	60 W
01188650	STAN 40W E27 230V P45 CL 1CT/10X10F	40 W

Order Code	Full Product Name	Power Consumption
01186250	STAN 40W E14 230V P45 CL 1CT/10X10F	40 W

