

Product Description

Standard Lustre P45 frosted

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E-base

Benefits

- Softly diffused light sets the scene for cosiness and comfort, and meets both aesthetic and functional requirements

Features


- Lamps with reduced size and neat shape
- Extremely popular for use around mirrors or in chandeliers, candelabras, floor lamps and wall brackets, fitted with small, decorative shades
- Creates a pleasent low glare atmosphere

Application


- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas

Standard Lustre P45 frosted

Dimensional drawing



Product	D	C (max)
Stan 40W E14 230V P45 FR 1CT/10X10F	45 mm	78 mm
Stan 60W E14 230V P45 FR 1CT/10X10F	45 mm	78 mm



Product	D	C (max)
Stan 40W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm
Stan 60W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45

General Information

Order Code	Full Product Name	Cap-Base	Operating Position
03321550	STAN 60W E27 230V P45 FR 1CT/10X10F	E27	S90
06757950	STAN 60W E14 230V P45 FR 1CT/10X10F	E14	UNIVERSAL

Order Code	Full Product Name	Cap-Base	Operating Position
01197850	STAN 40W E14 230V P45 FR 1CT/10X10F	E14	UNIVERSAL
01122050	STAN 40W E27 230V P45 FR 1CT/10X10F	E27	UNIVERSAL

Light Technical

Standard Lustre P45 frosted

Order Code	Full Product Name	Luminous Flux
03321550	STAN 60W E27 230V P45 FR 1CT/10X10F	640 lm
06757950	STAN 60W E14 230V P45 FR 1CT/10X10F	650 lm

Order Code	Full Product Name	Luminous Flux
01197850	STAN 40W E14 230V P45 FR 1CT/10X10F	405 lm
01122050	STAN 40W E27 230V P45 FR 1CT/10X10F	390 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
03321550	STAN 60W E27 230V P45 FR 1CT/10X10F	60 W
06757950	STAN 60W E14 230V P45 FR 1CT/10X10F	60 W

Order Code	Full Product Name	Power Consumption
01197850	STAN 40W E14 230V P45 FR 1CT/10X10F	40 W
01122050	STAN 40W E27 230V P45 FR 1CT/10X10F	40 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
03321550	STAN 60W E27 230V P45 FR 1CT/10X10F	60 kWh
06757950	STAN 60W E14 230V P45 FR 1CT/10X10F	60 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
01197850	STAN 40W E14 230V P45 FR 1CT/10X10F	-
01122050	STAN 40W E27 230V P45 FR 1CT/10X10F	-

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.