



Product Description

Standard A-shape clear

Conventional pear-shaped incandescent lamps

Benefits

- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect


Features

- Vacuum-filled (15W) or gas-filled (25W and above)

Application

- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare

Dimensional drawing



Product	D (max)	D	C (max)
Stan 40W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm
Stan 60W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm
Stan 75W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm

Standard A-shape clear

General Information	
Cap-Base	E27
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55

Light Technical

Order Code	Full Product Name	Luminous Flux
35453284	Standard 40W E27 230V A55 CL 1CT/12X10F	415 lm
35459484	STAN 75W E27 230V A55 CL 1CT/12X10F	930 lm
35456384	STAN 60W E27 230V A55 CL 1CT/12X10F	710 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
35453284	Standard 40W E27 230V A55 CL 1CT/12X10F	40 W
35459484	STAN 75W E27 230V A55 CL 1CT/12X10F	75 W

Order Code	Full Product Name	Power Consumption
35456384	STAN 60W E27 230V A55 CL 1CT/12X10F	60 W

