



Product Description

Standard A-shape clear

Conventional pear-shaped incandescent lamps

Benefits

- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect
- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect

Features

- Vacuum-filled (15W) or gas-filled (25W and above)
- Vacuum-filled (15W) or gas-filled (25W and above)

Application

- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare
- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare

Versions



LPPR ISTDAE E27 A55 CL

Standard A-shape clear

Dimensional drawing



Product	D (max)	D	C (max)
Stan 100W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm
Stan 60W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm

General Information	
Cap-Base	E27
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55

Light Technical

Order Code	Full Product Name	Luminous Flux
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	710 lm
920056543301	Stan 100W E27 220-240V A55 CL 1CT/5X10F	1,340 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	60 W

Order Code	Full Product Name	Power Consumption
920056543301	Stan 100W E27 220-240V A55 CL 1CT/5X10F	100 W

