



Product Description

Softone Standard T-shape

T-shaped gas-filled lamps with a modern appearance

Benefits

- Enhances colours in the home and adds a new dimension to interior decoration
- Creates a pleasant, relaxed atmosphere with a high degree of visual comfort

Features

- Gives a delicate, glare-free light in a subtle white or pastel colour
- Glare free and soft white or soft pastel lighting effect

Application

- Home use in living and dining rooms, halls and studies
- Offices
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs, social areas and public accommodation
- Shops and boutiques
- Other similar areas


Versions



B22, T55, Soft White

Softone Standard T-shape

Dimensional drawing



Product

Softone 100W B22 230V T55 WH U 1CT/100

Softone 40W B22 230V T55 WH U 1CT/100

Softone 60W B22 230V T55 WH U 1CT/100

Controls and Dimming

Dimmable Yes

Operating and Electrical

Voltage (Nom) 230 V

General Information

Cap-Base B22

Nominal Lifetime (Nom) 1000 h

Operating Position UNIVERSAL

Rated Lifetime (Hours) 1000 h

Light Technical

Color Rendering Index (Nom) 100

Mechanical and Housing

Bulb Finish Soft White

Bulb Shape T17

Operating and Electrical

| Order Code | Full Product Name | Power (Rated) (Nom) |
|--------------|--|---------------------|
| 926000205012 | Softone 60W B22 230V T55 WH U 1CT/100 | 60 W |
| 926000205013 | Softone 40W B22 230V T55 WH U 1CT/100 | 40 W |
| 926000205014 | Softone 100W B22 230V T55 WH U 1CT/100 | 100 W |

Light Technical

| Order Code | Full Product Name | Luminous Flux (Nom) | Order Code | Full Product Name | Luminous Flux (Nom) |
|--------------|---------------------------------------|---------------------|--------------|--|---------------------|
| 926000205012 | Softone 60W B22 230V T55 WH U 1CT/100 | 630 lm | 926000205014 | Softone 100W B22 230V T55 WH U 1CT/100 | 1200 lm |
| 926000205013 | Softone 40W B22 230V T55 WH U 1CT/100 | 370 lm | | | |

