



Smart Modular Downlight LBX300C – Cool... light your environment in a safe and smart way

Basic Modular LBX300

Our Smart Modular Downlight is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

Benefits

- Durable and safe
- Flexible and convenient
- Trendy and professional design

Features

- IEC60598 and CCC-compliant
- Electronic and electromagnetic ballast
- Robust housing
- High-quality lamp holders and connectors
- Emergency-lighting version available

Application

- Retail

Specifications

Basic Modular LBX300

Type	LBX300 (Halogen Accentline lamp version)
	LBX301 (Halogen Capsuleline lamp version)
	CBX301 (HID CDM-T / Halogen Capsuleline lamps version)
Light source	Halogen:
	- 1, 2 or 3 x Capsuleline / GY6.35 / 50 W
	- 1, 2, 3 or 4 x Accentline / GU5.3 / 50 W
	HID:
	- 1 x MASTERColour CDM-T / G12 / 70 W
Lamp included	No
Lamp position	Vertical

Light distribution	Direct
Ballast	Electronic, High Frequency 220-240 V / 50-60 Hz:
	- Electronic
Transformer	Electronic for halogen lamp version, 220-240 V
Optic	Wide beam (for CDM-T lamp version only)
	Narrow beam (for Capsuleline lamp version only)
Connection	SCREW connector
Material	Housing: anodised aluminum with matt surface
Color	Frame: white (WH) and grey (GR)
Installation	Fixation by means of spring fasteners

Versions



LBX300 2xMAX50W

