



MASTER LEDcandles – Eye-catching design for chandeliers and other decorative fixtures

MASTER Plastic LEDcandles & lusters

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles

Benefits

- Sparkling warm white light
- Up to 80% energy saving
- Lower maintenance costs

MASTER Plastic LEDcandles & lusters

Features

- Retrofittable with existing E14 holder
- Lifetime of 20000 hours
- Available in clear and frosted versions
- Free of mercury and hazardous materials

Application

- Hotels, restaurants, bars, cafés
- Chandelier, wall sconce or modern luminaire

Versions



LEDcandle MAS SLR1 BA38 E14 CL



LEDcandle MAS SLR1 B40 E14 CL



LEDluster MAS SLR1 P48 B22 CL



LEDluster MAS SLR1 P50 E14 CL




LEDcandle MAS SLR1 B38 B15 CL



LEDcandle MAS SLR1 B38 E14 CL




Dimensional drawing



Product	D	C
MAS LEDcandle DT 2.8-25W E14 BA38 CL	38 mm	129 mm
MAS LEDcandle DT 5.5-40W E14 BA38 CL	38 mm	129 mm

MASTER Plastic LEDcandles & lusters

Dimensional drawing



Product	D	C
MAS LEDlustre DT 5.5-40W B22 P48 CL	50 mm	93 mm





Product	D	C
MAS LEDlustre DT 8-60W P50 E14 827 CL	54 mm	109 mm

Product	D	C
MAS LEDcandle DT 5.5-40W E14 B38 CL	38 mm	113 mm

Product	D	C
MAS LEDcandle DT 2.8-25W B22 B38 CL	38 mm	111 mm
MAS LEDcandle DT 5.5-40W B22 B38 CL	38 mm	111 mm

MASTER Plastic LEDcandles & lusters

Dimensional drawing



Product	D	C
MAS LEDcandle DT 8-60W B40 E14 827 CL	42 mm	127 mm

Product	D	C
MAS LEDlustre DT 2.8-25W E27 P48 CL	50 mm	93 mm
MAS LEDlustre DT 5.5-40W E27 P48 CL	50 mm	93 mm

Product	D	C
MAS LEDcandle DT 5.5-40W B15 B38 CL	38 mm	113 mm

Product	D	C
MAS LEDlustre DT 2.8-25W E14 P48 CL	50 mm	95 mm
MAS LEDlustre DT 5.5-40W E14 P48 CL	50 mm	95 mm

MASTER Plastic LEDcandles & lusters

General Information	
Switching Cycle	50,000
Nominal lifetime	25,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	2200 K
Color rendering index (CRI)	80
Color Code	822-827
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear

General Information

Order Code	Full Product Name	Cap-Base
30604200	MASTER LEDcandle DT 2.8-25W E14 BA38 CL	E14
30616500	MASTER LEDcandle DT 5.5-40W E14 BA38 CL	E14
30640000	MASTER LEDcandle DT 8-60W B40 E14 827 CL	E14
30608000	MASTER LEDlustre DT 2.8-25W E27 P48 CL	E27
30620200	MASTER LEDlustre DT 5.5-40W E27 P48 CL	E27
30636300	MASTER LEDlustre DT 5.5-40W B22 P48 CL	B22
30642400	MASTER LEDlustre DT 8-60W P50 E14 827 CL	E14
30610300	MASTER LEDcandle DT 2.8-25W B22 B38 CL	B22
30622600	MASTER LEDcandle DT 5.5-40W B22 B38 CL	B22
30612700	MASTER LEDcandle DT 5.5-40W B15 B38 CL	B15
30614100	MASTER LEDcandle DT 5.5-40W E14 B38 CL	E14
30606600	MASTER LEDlustre DT 2.8-25W E14 P48 CL	E14
30618900	MASTER LEDlustre DT 5.5-40W E14 P48 CL	E14

Light Technical

Order Code	Full Product Name	Luminous Flux
30604200	MASTER LEDcandle DT 2.8-25W E14 BA38 CL	250 lm
30616500	MASTER LEDcandle DT 5.5-40W E14 BA38 CL	470 lm
30640000	MASTER LEDcandle DT 8-60W B40 E14 827 CL	806 lm
30608000	MASTER LEDlustre DT 2.8-25W E27 P48 CL	250 lm
30620200	MASTER LEDlustre DT 5.5-40W E27 P48 CL	470 lm
30636300	MASTER LEDlustre DT 5.5-40W B22 P48 CL	470 lm
30642400	MASTER LEDlustre DT 8-60W P50 E14 827 CL	806 lm

Order Code	Full Product Name	Luminous Flux
30610300	MASTER LEDcandle DT 2.8-25W B22 B38 CL	250 lm
30622600	MASTER LEDcandle DT 5.5-40W B22 B38 CL	470 lm
30612700	MASTER LEDcandle DT 5.5-40W B15 B38 CL	470 lm
30614100	MASTER LEDcandle DT 5.5-40W E14 B38 CL	470 lm
30606600	MASTER LEDlustre DT 2.8-25W E14 P48 CL	250 lm
30618900	MASTER LEDlustre DT 5.5-40W E14 P48 CL	470 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
30604200	MASTER LEDcandle DT 2.8-25W E14 BA38 CL	2.8 W	25 W
30616500	MASTER LEDcandle DT 5.5-40W E14 BA38 CL	5.5 W	40 W
30640000	MASTER LEDcandle DT 8-60W B40 E14 827 CL	8 W	60 W
30608000	MASTER LEDlustre DT 2.8-25W E27 P48 CL	2.8 W	25 W
30620200	MASTER LEDlustre DT 5.5-40W E27 P48 CL	5.5 W	40 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
30636300	MASTER LEDlustre DT 5.5-40W B22 P48 CL	5.5 W	40 W
30642400	MASTER LEDlustre DT 8-60W P50 E14 827 CL	8 W	60 W
30610300	MASTER LEDcandle DT 2.8-25W B22 B38 CL	2.8 W	25 W
30622600	MASTER LEDcandle DT 5.5-40W B22 B38 CL	5.5 W	40 W
30612700	MASTER LEDcandle DT 5.5-40W B15 B38 CL	5.5 W	40 W

MASTER Plastic LEDcandles & lusters

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
30614100	MASTER LEDcandle DT 5.5-40W E14 B38 CL	5.5 W	40 W
30606600	MASTER LEDlustre DT 2.8-25W E14 P48 CL	2.8 W	25 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
30618900	MASTER LEDlustre DT 5.5-40W E14 P48 CL	5.5 W	40 W





Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
30604200	MASTER LEDcandle DT 2.8-25W E14 BA38 CL	BA38
30616500	MASTER LEDcandle DT 5.5-40W E14 BA38 CL	BA38
30640000	MASTER LEDcandle DT 8-60W B40 E14 827 CL	B40
30608000	MASTER LEDlustre DT 2.8-25W E27 P48 CL	P48
30620200	MASTER LEDlustre DT 5.5-40W E27 P48 CL	P48
30636300	MASTER LEDlustre DT 5.5-40W B22 P48 CL	P48
30642400	MASTER LEDlustre DT 8-60W P50 E14 827 CL	P50










Order Code	Full Product Name	Bulb Shape
30610300	MASTER LEDcandle DT 2.8-25W B22 B38 CL	B38
30622600	MASTER LEDcandle DT 5.5-40W B22 B38 CL	B38
30612700	MASTER LEDcandle DT 5.5-40W B15 B38 CL	B38
30614100	MASTER LEDcandle DT 5.5-40W E14 B38 CL	B38
30606600	MASTER LEDlustre DT 2.8-25W E14 P48 CL	P48
30618900	MASTER LEDlustre DT 5.5-40W E14 P48 CL	P48

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
30604200	MASTER LEDcandle DT 2.8-25W E14 BA38 CL	3 kWh
30616500	MASTER LEDcandle DT 5.5-40W E14 BA38 CL	6 kWh
30640000	MASTER LEDcandle DT 8-60W B40 E14 827 CL	8 kWh
30608000	MASTER LEDlustre DT 2.8-25W E27 P48 CL	3 kWh
30620200	MASTER LEDlustre DT 5.5-40W E27 P48 CL	6 kWh
30636300	MASTER LEDlustre DT 5.5-40W B22 P48 CL	6 kWh
30642400	MASTER LEDlustre DT 8-60W P50 E14 827 CL	8 kWh
30610300	MASTER LEDcandle DT 2.8-25W B22 B38 CL	3 kWh
30622600	MASTER LEDcandle DT 5.5-40W B22 B38 CL	6 kWh
30612700	MASTER LEDcandle DT 5.5-40W B15 B38 CL	6 kWh
30614100	MASTER LEDcandle DT 5.5-40W E14 B38 CL	6 kWh
30606600	MASTER LEDlustre DT 2.8-25W E14 P48 CL	3 kWh
30618900	MASTER LEDlustre DT 5.5-40W E14 P48 CL	6 kWh



MASTER Plastic LEDcandles & lusters



MASTER Plastic LEDcandles & lusters

