



MASTER LEDcandles – Eye-catching design for chandeliers and other decorative fixtures

MASTER LEDcandle

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps come in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

Benefits

- Sparkling warm white light
- Up to 80% energy saving
- Lower maintenance costs

MASTER LEDcandle

Features

- Retrofittable with existing E14 and B15 holders
- Lifetime of 20,000 hours
- Available in clear and frosted versions
- Free of mercury and hazardous materials

Application

- Hotels, restaurants, bars, cafés
- Chandelier, wall sconce or modern luminaire

Versions



E27 P48 CL

Dimensional drawing

D

Product	D	C
MASTER LEDlustre DT 6-40W E27 P48 CL	48 mm	93 mm
MASTER LEDlustre DT 4-25W E27 P48 CL	48 mm	93 mm

MASTER LEDcandle

Approval and Application	
Energy Efficiency Label (EEL)	A+
Controls and Dimming	
Dimmable	Yes
Operating and Electrical	
Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.5 s
General Information	
Cap-Base	E27
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Light Technical	
Color Code	822-827
Color Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P48

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
304006	MASTER LEDlustre DT 4-25W E27 P48 CL	4 kWh
304022	MASTER LEDlustre DT 6-40W E27 P48 CL	6 kWh

Operating and Electrical

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
304006	MASTER LEDlustre DT 4-25W E27 P48 CL	25 W	4 W

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
304022	MASTER LEDlustre DT 6-40W E27 P48 CL	40 W	6 W


Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
304006	MASTER LEDlustre DT 4-25W E27 P48 CL	250 lm

Order Code	Full Product Name	Luminous Flux (Nom)
304022	MASTER LEDlustre DT 6-40W E27 P48 CL	470 lm

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
304006	MASTER LEDlustre DT 4-25W E27 P48 CL	85 °C
304022	MASTER LEDlustre DT 6-40W E27 P48 CL	95 °C



MASTER LEDcandle

