



MASTER LEDspot LV AR111 – Ideal solution for spot lighting in shops

MASTER LEDspot LV AR111

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimises maintenance cost without any reduction in brightness.

Benefits

- \cdot Up to 80% energy saving compared with halogen lamps
- Up to 80% energy saving compared with halogen lamps
- · Broad compatibility with transformers
- Broad compatibility with transformers
- · Retrofittable
- · Retrofittable


Features

- · Patented intelligent driver
- · Patented intelligent driver
- · Lifetime of 45,000 hours
- · Lifetime of 45,000 hours
- · Low energy consumption
- · Low energy consumption
- · Clearly defined beam spread
- · Clearly defined beam spread
- \cdot UV- and IR-free light for less heat and protection for heat-sensitive objects
- UV- and IR-free light for less heat and protection for heat-sensitive objects

Application

- · Shops, hotels, restaurants, bars, cafés
- · Shops, hotels, restaurants, bars, cafés
- Gallieres, museums, exhibitions, lobbies, corridors, stairwells, washrooms, reception areas
- Gallieres, museums, exhibitions, lobbies, corridors, stairwells, washrooms, reception areas

Dimensional drawing



Product	D	С
MAS LED ExpertColor 15-75W 927 AR111 24D	111 mm	62 mm
MAS LED ExpertColor 15-75W 927 AR111 40D	111 mm	62 mm
MAS LED ExpertColor 15-75W 930 AR111 24D	111 mm	62 mm
MAS LED ExpertColor 15-75W 930 AR111 40D	111 mm	62 mm


Cap-Base	G53
Switching Cycle	50,000
Nominal lifetime	40,000 hour(s
Light Technical	
Color rendering index (CRI)	97
LMF At End Of Nominal Lifetime 70 %	
(Nom)	
Operating and Electrical	
Input Frequency	- Hz
Line Frequency	- Hz
Power Consumption	15 W
Starting Time (Nom)	0.5 s
Wattage Equivalent	75 W
Temperature	
T-Case Maximum (Nom)	74 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	AR111
Approval and Application	


Light Technical (1/2)


			Correlated Color		
		Beam Angle	Temperature	Color	
Order Code	Full Product Name	(Nom)	(Nom)	Code	Luminous Flux
929002239008	MAS LED ExpertColor	24 degree(s)	2700 K	927	950 lm
	15-75W 927 AR111 24D				
929002239108	MAS LED ExpertColor	24 degree(s)	3000 K	930	1,000 lm
	15-75W 930 AR111 24D				
929002239308	MAS LED ExpertColor	40 degree(s)	2700 K	927	950 lm
	15-75W 927 AR111 40D				
929002239408	MAS LED ExpertColor	40 degree(s)	3000 K	930	1,000 lm
	15-75W 930 AR111 40D				

Light Technical (2/2)


		Luminous Intensity
Order Code	Full Product Name	(Nom)
929002239008	MAS LED ExpertColor 15-75W 927 AR111 24D	3,500 cd
929002239108	MAS LED ExpertColor 15-75W 930 AR111 24D	3,500 cd
929002239308	MAS LED ExpertColor 15-75W 927 AR111 40D	1,400 cd
929002239408	MAS LED ExpertColor 15-75W 930 AR111 40D	1,400 cd









Accent Diagrams




Accent Diagram - MAS LED ExpertColor 15-75W 927 AR111 40D



Accent Diagram - MAS LED ExpertColor 15-75W 927 AR111 24D





Accent Diagram - MAS LED ExpertColor 15-75W 930 AR111 24D




Accent Diagram - MAS LED ExpertColor 15-75W 930 AR111 40D


Beam Diagrams







Beam diagram - MAS LED ExpertColor 15-75W 927 AR111 24D Beam diagram - MAS LED ExpertColor 15-75W 930 AR111 40D Beam diagram - MAS LED ExpertColor 15-75W 930 AR111 24D



Beam diagram - MAS LED ExpertColor 15-75W 927 AR111 40D

