



The new generation of energy saving tube lighting

MASTER LEDtube EM/Mains T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Benefits

Features

Application

Warnings and Safety

Versions



MASTER LEDtube Starter EMP
050 CP



MASTER LEDtube EM/Mains T8

Versions



G13




G13



LEDtube G13



G13



Medium Bi-Pin Fluorescent Tube,
single-ended




G13



Medium Bi-Pin Fluorescent

MASTER LEDtube EM/Mains T8

Dimensional drawing



Product	D1	D2	C1
MASTER LEDtube Starter EMP	3 mm	21.5 mm	34.5 mm
MASTER LEDtube Starter EMP GenII OP	3 mm	21.5 mm	34.5 mm

Product	D1	D2	A1	A2	A3
MASTER LEDtube 600mm HO 8W865 T8	25.78 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
MASTER LEDtube 1200mm UO 16W 840 T8	25.78 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 600mm HO 8W840 T8	25.78 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
MASTER LEDtube 1500mm UO 24W 865 T8	25.78 mm	28 mm	1498.7 mm	1505.8 mm	1512.9 mm
MASTER LEDtube 1200mm UO 16W 830 T8	25.78 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1500mm UO 24W 840 T8	25.78 mm	28 mm	1498.7 mm	1505.8 mm	1512.9 mm
MASTER LEDtube 1500mm UO 23W 865 T8	25.8 mm	28 mm	1498.7 mm	1505.8 mm	1512.9 mm
MASTER LEDtube 1500mm UO 23W 840 T8	25.8 mm	28 mm	1498.7 mm	1505.8 mm	1512.9 mm
MASTER LEDtube 1500mm UO 23W 830 T8	25.8 mm	28 mm	1498.7 mm	1505.8 mm	1512.9 mm
MASTER LEDtube STD 1200mm 10.5W840 T8 I	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube STD 1200mm 10.5W865 T8 I	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
Master LEDTube 1200 mm 18W 840 T8 I W	25.6 mm	27.8 mm	1198.1 mm	1205.2 mm	1212.3 mm
MASTER LEDtube 1200mm UO 16W 830 T8 FF RCA	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1198.2 mm
MASTER LEDtube 1200mm UO 16W 865 T8 FF RCA	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1198.2 mm
MASTER LEDtube 1500mm UO 24W 830 T8 FF RCA	25.8 mm	28 mm	1498.7 mm	1505.8 mm	1498.7 mm
MASTER LEDtube 1500mm UO 24W 840 T8 FF RCA	25.8 mm	28 mm	1498.7 mm	1505.8 mm	1498.7 mm


MASTER LEDtube EM/Mains T8

Dimensional drawing

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1500mm UO 24W 865 T8 FF RCA	25.8 mm	28 mm	1498.7 mm	1505.8 mm	1498.7 mm
MASTER LEDtube 1200mm UO 16W 840 T8 FF RCA	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1198.2 mm
MASTER LEDtube 1200mm UO 15.5W 865 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1200mm UO 15.5W 840 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1200mm UO 15.5W 830 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1200mm 14W 840 T8 THD	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1200mm 14W 865 T8 THD	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 900mm HO 12W 840 T8	25.78 mm	28 mm	893.3 mm	900.4 mm	907.5 mm
MASTER LEDtube 900mm HO 12W 865 T8	25.78 mm	28 mm	893.3 mm	900.4 mm	907.5 mm
MASTER LEDtube 600mm HO 8W830 T8	25.78 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Master LEDTube 1200 mm 18W 865 T8 I W	25.6 mm	27.8 mm	1198.1 mm	1205.2 mm	1212.3 mm
Master LEDTube 1200 mm 18W 840 T8 I W	25.6 mm	27.8 mm	1198.1 mm	1205.2 mm	1212.3 mm
MASTER LEDtube Sensor 1500mm HO 24W865 T8	25.8 mm	28 mm	1500 mm	1507.1 mm	1514.2 mm
MASTER LEDtube Sensor 1200mm HO 16.5W865 T8	25.8 mm	28 mm	1199.4 mm	1206.5 mm	1213.6 mm
MASTER LEDtube Sensor 1200mm HO 16.5W840 T8	25.8 mm	28 mm	1199.4 mm	1206.5 mm	1213.6 mm
MASTER LEDtube Sensor 1500mm HO 24W840 T8	25.8 mm	28 mm	1500 mm	1507.1 mm	1514.2 mm
MASTER LEDtube 1050mm 16W 830 T8	25.8 mm	28 mm	1045.8 mm	1052.9 mm	1060 mm
Master LEDTube 600 mm 10W 865 T8 I W	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm
Master LEDTube 600 mm 10W 840 T8 I W	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm

MASTER LEDtube EM/Mains T8

Product	D1	D2	A1	A2	A3
Master LEDTube 1200 mm 18W 865 T8 I W	25.6 mm	27.8 mm	1198.1 mm	1205.2 mm	1212.3 mm
Master LEDTube 600 mm 10W 865 T8 I W	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm
Master LEDTube 600 mm 10W 840 T8 I W	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm
Master LEDTube 1200 mm 18W 865 T8 I W	25.6 mm	27.8 mm	1198.1 mm	1205.2 mm	1212.3 mm
Master LEDTube 1200 mm 18W 840 T8 I W	25.6 mm	27.8 mm	1198.1 mm	1205.2 mm	1212.3 mm
MASTER LEDtube 1800mm 25W 840 T8 ROT	25.68 mm	28 mm	1762.5 mm	1770 mm	1776.7 mm
MASTER LEDtube 1500mm UO 24W 830 T8	25.78 mm	28 mm	1498.7 mm	1505.8 mm	1512.9 mm
MASTER LEDtube 1200mm UO 16W 865 T8	25.78 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm



Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm HO VWV 18W 840 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 600mm HO VWV 10W 865 T8	25.8 mm	28 mm	588.6 mm	595.6 mm	602.6 mm
MASTER LEDtube 600mm HO VWV 10W 840 T8	25.8 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
MASTER LEDtube 1200mm HO VWV 18W 865 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MAS LEDtube STD 1200mm 14W865 T8 I W	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube STD 1200mm 14W840 T8 I W	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 900mm 8.5W833 T8 FOOD	25.7 mm	28 mm	893.3 mm	900.4 mm	907.5 mm
MASTER LEDtube 1200mm 12W833 T8 FOOD	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1500mm 20W833 T8 FOOD	25.7 mm	28 mm	1500 mm	1507.1 mm	1514.2 mm
MASTER LEDtube 1500mm UO 24W 865 T8 G	25.8 mm	28 mm	1498.7 mm	1505.8 mm	1512.9 mm
MASTER LEDtube 1050mm 16W 840 T8	25.8 mm	28 mm	1045.8 mm	1052.9 mm	1060 mm

MASTER LEDtube EM/Mains T8

Dimensional drawing

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1500mm HO 18.2W 830 T8	25.8 mm	28 mm	1498.8 mm	1505.9 mm	1513 mm
MASTER LEDtube 1500mm HO 18.2W 840 T8	25.8 mm	28 mm	1498.8 mm	1505.9 mm	1513 mm
MASTER LEDtube 1500mm HO 18.2W 865 T8	25.8 mm	28 mm	1498.8 mm	1505.9 mm	1513 mm
MASTER LEDtube 1200mm HO 12.5W 830 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1200mm HO 12.5W 840 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1200mm HO 12.5W 865 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
Master LEDTube 8ft 33W 4000lm 865 T8 BR	25.7 mm	28 mm	2373.1 mm	2380.2 mm	2387.3 mm
MASTER LEDtube 1500mm UE 21.5W 840 T8	25.8 mm	28 mm	1498.8 mm	1505.9 mm	1513 mm
MASTER LEDtube 1200mm UE 14.5W 865 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1500mm UE 21.5W 865 T8	25.8 mm	28 mm	1498.8 mm	1505.9 mm	1513 mm
MASTER LEDtube 1200mm UE 14.5W 840 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1200mm UO 16W 830 T8 G I	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1500mm UO 24W 830 T8 G I	25.8 mm	28 mm	1498.7 mm	1505.8 mm	1512.9 mm
MASTER LEDtube 1500mm UO 24W 830 T8 G	25.8 mm	28 mm	1498.7 mm	1505.8 mm	1512.9 mm
MASTER LEDtube 1200mm UO 16W 865 T8 G	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1200mm UO 16W 840 T8 G	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
MASTER LEDtube 1500mm UO 24W 840 T8 G	25.8 mm	28 mm	1498.7 mm	1505.8 mm	1512.9 mm

MASTER LEDtube EM/Mains T8

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm UO 16W 830 T8 G	25,8 mm	28 mm	1198,2 mm	1205,3 mm	1212,4 mm
MASTER LEDtube STD 1200mm 14W840 T8 I W	25,7 mm	28 mm	1198,2 mm	1205,3 mm	1212,4 mm
MASTER LEDtube 1200mm HO 14W840 T8	25,8 mm	28 mm	1198,2 mm	1205,3 mm	1212,4 mm
MASTER LEDtube 1200mm HO 14W865 T8	25,8 mm	28 mm	1198,2 mm	1205,3 mm	1212,4 mm
MASTER LEDtube 1200mm HO 14W830 T8	25,8 mm	28 mm	1198,2 mm	1205,3 mm	1212,4 mm
Master LEDTube 8ft 33W 4000lm 865 T8	25,7 mm	28 mm	2373,1 mm	2380,2 mm	2387,3 mm

A3

Product	D1	D2	A1	A2	A3
MASTER LEDtube DC72-110V 450mm 6W 840 T8	25,7 mm	28 mm	437 mm	442 mm	452 mm
MASTER LEDtube DC72-110V 1200mm 18W 840 T8	25,7 mm	28 mm	1198 mm	1205 mm	1212 mm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929000299902	MASTER LEDtube Starter EMP	50 to 60 Hz	-	-	-
929001801432	MASTER LEDtube Starter EMP GenII OP	-	-	-	-
929001161102	MASTER LEDtube 1800mm 25W 840 T8 ROT	50 to 60 Hz	220-240 V	25 W	0,5 s
929001187912	Master LEDTube 600 mm 10W 840 T8 I W	50 to 60 Hz	100-240 V	10 W	0,5 s
929001187972	Master LEDTube 600 mm 10W 840 T8 I W	50 to 60 Hz	100-240 V	10 W	0,5 s
929001188012	Master LEDTube 600 mm 10W 865 T8 I W	50 to 60 Hz	100-240 V	10 W	0,5 s

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929001188072	Master LEDTube 600 mm 10W 865 T8 I W	50 to 60 Hz	100-240 V	10 W	0,5 s
929001187712	Master LEDTube 1200 mm 18W 840 T8 I W	50 to 60 Hz	100-240 V	18 W	0,5 s
929001187772	Master LEDTube 1200 mm 18W 840 T8 I W	50 to 60 Hz	100-240 V	18 W	0,5 s
929001187782	Master LEDTube 1200 mm 18W 840 T8 I W	50 to 60 Hz	100-240 V	18 W	0,5 s
929001187812	Master LEDTube 1200 mm 18W 865 T8 I W	50 to 60 Hz	100-240 V	18 W	0,5 s
929001187872	Master LEDTube 1200 mm 18W 865 T8 I W	50 to 60 Hz	100-240 V	18 W	0,5 s

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929001187882	Master LEDTube 1200 mm 18W 865 T8 I W	50 to 60 Hz	100-240 V	18 W	0.5 s
929001297608	MASTER LEDtube STD 1200mm 10.5W840 T8 I	50 to 60 Hz	220-240 V	10.5 W	0.5 s
929001297708	MASTER LEDtube STD 1200mm 10.5W865 T8 I	50 to 60 Hz	220-240 V	10.5 W	0.5 s
929001375208	MASTER LEDtube 1200mm 14W 840 T8 THD	50 to 60 Hz	220-240 V	14 W	0.5 s
929001375308	MASTER LEDtube 1200mm 14W 865 T8 THD	50 to 60 Hz	220-240 V	14 W	0.5 s
929001375602	MASTER LEDtube 1050mm 16W 830 T8	50 to 60 Hz	220-240 V	16 W	0.5 s
929001297802	MASTER LEDtube 1200mm UO 16W 830 T8	50 to 60 Hz	220-240 V	16 W	0.5 s
929001297902	MASTER LEDtube 1200mm UO 16W 840 T8	50 to 60 Hz	220-240 V	16 W	0.5 s
929001298002	MASTER LEDtube 1200mm UO 16W 865 T8	50 to 60 Hz	220-240 V	16 W	0.5 s
929001298102	MASTER LEDtube 1500mm UO 24W 830 T8	50 to 60 Hz	220-240 V	24 W	0.5 s
929001298202	MASTER LEDtube 1500mm UO 24W 840 T8	50 to 60 Hz	220-240 V	24 W	0.5 s
929001298302	MASTER LEDtube 1500mm UO 24W 865 T8	50 to 60 Hz	220-240 V	24 W	0.5 s
929002020502	MASTER LEDtube 1200mm UO 15.5W 830 T8	50 to 60 Hz	220-240 V	15.5 W	0.5 s
929002020602	MASTER LEDtube 1200mm UO 15.5W 840 T8	50 to 60 Hz	220-240 V	15.5 W	0.5 s
929002020702	MASTER LEDtube 1200mm UO 15.5W 865 T8	50 to 60 Hz	220-240 V	15.5 W	0.5 s
929002020802	MASTER LEDtube 1500mm UO 23W 830 T8	50 to 60 Hz	220-240 V	23 W	0.5 s

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929002020902	MASTER LEDtube 1500mm UO 23W 840 T8	50 to 60 Hz	220-240 V	23 W	0.5 s
929002021002	MASTER LEDtube 1500mm UO 23W 865 T8	50 to 60 Hz	220-240 V	23 W	0.5 s
929001298402	MASTER LEDtube 900mm HO 12W 840 T8	50 to 60 Hz	220-240 V	12 W	0.5 s
929001298502	MASTER LEDtube 900mm HO 12W 865 T8	50 to 60 Hz	220-240 V	12 W	0.5 s
929001307002	MASTER LEDtube 600mm HO 8W830 T8	50 to 60 Hz	220-240 V	8 W	0.5 s
929001307102	MASTER LEDtube 600mm HO 8W840 T8	50 to 60 Hz	220-240 V	8 W	0.5 s
929001307202	MASTER LEDtube 600mm HO 8W865 T8	50 to 60 Hz	220-240 V	8 W	0.5 s
929001812202	MASTER LEDtube 1200mm 12W833 T8 FOOD	50 to 60 Hz	220-240 V	12 W	0.5 s
929001907908	MASTER LEDtube 1200mm UO 16W 830 T8 FF RCA	50 to 60 Hz	220-240 V	16 W	0.5 s
929001908008	MASTER LEDtube 1200mm UO 16W 840 T8 FF RCA	50 to 60 Hz	220-240 V	16 W	0.5 s
929001908108	MASTER LEDtube 1200mm UO 16W 865 T8 FF RCA	50 to 60 Hz	220-240 V	16 W	0.5 s
929001908208	MASTER LEDtube 1500mm UO 24W 830 T8 FF RCA	50 to 60 Hz	220-240 V	24 W	0.5 s
929001908308	MASTER LEDtube 1500mm UO 24W 840 T8 FF RCA	50 to 60 Hz	220-240 V	24 W	0.5 s
929001908408	MASTER LEDtube 1500mm UO 24W 865 T8 FF RCA	50 to 60 Hz	220-240 V	24 W	0.5 s
929001299208	MASTER LEDtube 1200mm HO 14W830 T8	50 to 60 Hz	220-240 V	14 W	0.5 s
929001299308	MASTER LEDtube 1200mm HO 14W840 T8	50 to 60 Hz	220-240 V	14 W	0.5 s

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929001299408	MASTER LEDtube 1200mm HO 14W865 T8	50 to 60 Hz	220-240 V	14 W	0.5 s
929001368112	Master LEDTube 8ft 33W 4000lm 865 T8	50 to 60 Hz	100-277 V	33 W	0.5 s
929001368172	Master LEDTube 8ft 33W 4000lm 865 T8 BR	50 to 60 Hz	100-277 V	33 W	0.5 s
929001375412	MASTER LEDtube STD 1200mm 14W840 T8 I W	50 to 60 Hz	100-277 V	14 W	0.5 s
929001375442	MASTER LEDtube STD 1200mm 14W840 T8 I W	50 to 60 Hz	100-277 V	14 W	0.5 s
929001375542	MASTER LEDtube STD 1200mm 14W865 T8 I W	50 to 60 Hz	100-277 V	14 W	0.5 s
929001376802	MASTER LEDtube 1200mm UE 14.5W 840 T8	50 to 60 Hz	220-240 V	14.5 W	0.5 s
929001376902	MASTER LEDtube 1200mm UE 14.5W 865 T8	50 to 60 Hz	220-240 V	14.5 W	0.5 s
929001377002	MASTER LEDtube 1500mm UE 21.5W 840 T8	50 to 60 Hz	220-240 V	21.5 W	0.5 s
929001377102	MASTER LEDtube 1500mm UE 21.5W 865 T8	50 to 60 Hz	220-240 V	21.5 W	0.5 s
929001812102	MASTER LEDtube 900mm 8.5W833 T8 FOOD	50 to 60 Hz	220-240 V	8.5 W	0.5 s
929001812302	MASTER LEDtube 1500mm 20W833 T8 FOOD	50 to 60 Hz	220-240 V	20 W	0.5 s
929001877312	MASTER LEDtube 1200mm HO VWV 18W 840 T8	50 to 60 Hz	100-277 V	18 W	0.5 s
929001877412	MASTER LEDtube 1200mm HO VWV 18W 865 T8	50 to 60 Hz	100-277 V	18 W	0.5 s
929001877512	MASTER LEDtube 600mm HO VWV 10W 840 T8	50 to 60 Hz	100-277 V	10 W	0.5 s
929001877612	MASTER LEDtube 600mm HO VWV 10W 865 T8	50 to 60 Hz	100-277 V	10 W	0.5 s

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929001878502	MASTER LEDtube Sensor 1200mm HO 16.5W840 T8	50 to 60 Hz	220-240 V	16.5 W	0.5 s
929001878602	MASTER LEDtube Sensor 1200mm HO 16.5W865 T8	50 to 60 Hz	220-240 V	16.5 W	0.5 s
929001878702	MASTER LEDtube Sensor 1500mm HO 24W840 T8	50 to 60 Hz	220-240 V	24 W	0.5 s
929001878802	MASTER LEDtube Sensor 1500mm HO 24W865 T8	50 to 60 Hz	220-240 V	24 W	0.5 s
929001922602	MASTER LEDtube 1200mm HO 12.5W 830 T8	50 to 60 Hz	220-240 V	12.5 W	0.5 s
929001922702	MASTER LEDtube 1200mm HO 12.5W 840 T8	50 to 60 Hz	220-240 V	12.5 W	0.5 s
929001922802	MASTER LEDtube 1200mm HO 12.5W 865 T8	50 to 60 Hz	220-240 V	12.5 W	0.5 s
929001922902	MASTER LEDtube 1500mm HO 18.2W 830 T8	50 to 60 Hz	220-240 V	18.2 W	0.5 s
929001923002	MASTER LEDtube 1500mm HO 18.2W 840 T8	50 to 60 Hz	220-240 V	18.2 W	0.5 s
929001923102	MASTER LEDtube 1500mm HO 18.2W 865 T8	50 to 60 Hz	220-240 V	18.2 W	0.5 s
929001923402	MASTER LEDtube 1200mm UO 16W 830 T8 G	50 to 60 Hz	220-240 V	16 W	0.5 s
929001923432	MASTER LEDtube 1200mm UO 16W 830 T8 G I	50 to 60 Hz	220-240 V	16 W	0.5 s
929001923502	MASTER LEDtube 1200mm UO 16W 840 T8 G	50 to 60 Hz	220-240 V	16 W	0.5 s
929001923602	MASTER LEDtube 1200mm UO 16W 865 T8 G	50 to 60 Hz	220-240 V	16 W	0.5 s
929001923702	MASTER LEDtube 1500mm UO 24W 830 T8 G	50 to 60 Hz	220-240 V	24 W	0.5 s
929001923732	MASTER LEDtube 1500mm UO 24W 830 T8 G I	50 to 60 Hz	220-240 V	24 W	0.5 s

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929001923802	MASTER LEDtube 1500mm UO 24W 840 T8 G	50 to 60 Hz	220-240 V	24 W	0.5 s
929001923902	MASTER LEDtube 1500mm UO 24W 865 T8 G	50 to 60 Hz	220-240 V	24 W	0.5 s
929001961102	MASTER LEDtube 1050mm 16W 840 T8	50 to 60 Hz	220-240 V	16 W	0.5 s

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929002329702	MASTER LEDtube DC72-110V 1200mm 18W 840 T8	-	72-110 V	18 W	0.5 s
929002329802	MASTER LEDtube DC72-110V 450mm 6W 840 T8	-	72-110 V	6 W	0.5 s

General Information

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
929000299902	MASTER LEDtube Starter EMP	-	-	-
929001801432	MASTER LEDtube Starter EMP GenII OP	-	-	-
929001161102	MASTER LEDtube 1800mm 25W 840 T8 ROT	G13	50000 h	50000X
929001187912	Master LEDTube 600 mm 10W 840 T8 I W	G13	40000 h	50000X
929001187972	Master LEDTube 600 mm 10W 840 T8 I W	G13	25000 h	50000X
929001188012	Master LEDTube 600 mm 10W 865 T8 I W	G13	40000 h	50000X
929001188072	Master LEDTube 600 mm 10W 865 T8 I W	G13	25000 h	50000X
929001187712	Master LEDTube 1200 mm 18W 840 T8 I W	G13	40000 h	50000X
929001187772	Master LEDTube 1200 mm 18W 840 T8 I W	G13	25000 h	50000X
929001187782	Master LEDTube 1200 mm 18W 840 T8 I W	G13	50000 h	50000X
929001187812	Master LEDTube 1200 mm 18W 865 T8 I W	G13	40000 h	50000X
929001187872	Master LEDTube 1200 mm 18W 865 T8 I W	G13	25000 h	50000X
929001187882	Master LEDTube 1200 mm 18W 865 T8 I W	G13	50000 h	50000X
929001297608	MASTER LEDtube STD 1200mm 10.5W840 T8 I	G13	50000 h	200000X
929001297708	MASTER LEDtube STD 1200mm 10.5W865 T8 I	G13	50000 h	200000X
929001375208	MASTER LEDtube 1200mm 14W 840 T8 THD	G13	50000 h	50000X
929001375308	MASTER LEDtube 1200mm 14W 865 T8 THD	G13	50000 h	50000X
929001375602	MASTER LEDtube 1050mm 16W 830 T8	G13	50000 h	200000X

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
929001297802	MASTER LEDtube 1200mm UO 16W 830 T8	G13	50000 h	200000X
929001297902	MASTER LEDtube 1200mm UO 16W 840 T8	G13	50000 h	200000X
929001298002	MASTER LEDtube 1200mm UO 16W 865 T8	G13	50000 h	200000X
929001298102	MASTER LEDtube 1500mm UO 24W 830 T8	G13	50000 h	200000X
929001298202	MASTER LEDtube 1500mm UO 24W 840 T8	G13	50000 h	200000X
929001298302	MASTER LEDtube 1500mm UO 24W 865 T8	G13	50000 h	200000X
929002020502	MASTER LEDtube 1200mm UO 15.5W 830 T8	G13	60000 h	200000X
929002020602	MASTER LEDtube 1200mm UO 15.5W 840 T8	G13	60000 h	200000X
929002020702	MASTER LEDtube 1200mm UO 15.5W 865 T8	G13	60000 h	200000X
929002020802	MASTER LEDtube 1500mm UO 23W 830 T8	G13	60000 h	200000X
929002020902	MASTER LEDtube 1500mm UO 23W 840 T8	G13	60000 h	200000X
929002021002	MASTER LEDtube 1500mm UO 23W 865 T8	G13	60000 h	200000X
929001298402	MASTER LEDtube 900mm HO 12W 840 T8	G13	50000 h	200000X
929001298502	MASTER LEDtube 900mm HO 12W 865 T8	G13	50000 h	200000X
929001307002	MASTER LEDtube 600mm HO 8W830 T8	G13	60000 h	200000X
929001307102	MASTER LEDtube 600mm HO 8W840 T8	G13	60000 h	200000X
929001307202	MASTER LEDtube 600mm HO 8W865 T8	G13	60000 h	200000X

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
929001812202	MASTER LEDtube 1200mm 12W833 T8 FOOD	G13	50000 h	50000X
929001907908	MASTER LEDtube 1200mm UO 16W 830 T8 FF RCA	G13	50000 h	200000X
929001908008	MASTER LEDtube 1200mm UO 16W 840 T8 FF RCA	G13	50000 h	200000X
929001908108	MASTER LEDtube 1200mm UO 16W 865 T8 FF RCA	G13	50000 h	200000X
929001908208	MASTER LEDtube 1500mm UO 24W 830 T8 FF RCA	G13	50000 h	200000X
929001908308	MASTER LEDtube 1500mm UO 24W 840 T8 FF RCA	G13	50000 h	200000X
929001908408	MASTER LEDtube 1500mm UO 24W 865 T8 FF RCA	G13	50000 h	200000X
929001299208	MASTER LEDtube 1200mm HO 14W830 T8	G13	50000 h	200000X
929001299308	MASTER LEDtube 1200mm HO 14W840 T8	G13	50000 h	200000X
929001299408	MASTER LEDtube 1200mm HO 14W865 T8	G13	50000 h	200000X
929001368112	Master LEDTube 8ft 33W 4000lm 865 T8	G13	30000 h	50000X
929001368172	Master LEDTube 8ft 33W 4000lm 865 T8 BR	G13	25000 h	50000X
929001375412	MASTER LEDtube STD 1200mm 14W840 T8 I W	G13	50000 h	200000X
929001375442	MASTER LEDtube STD 1200mm 14W840 T8 I W	G13	50000 h	200000X
929001375542	MASTER LEDtube STD 1200mm 14W865 T8 I W	G13	50000 h	200000X
929001376802	MASTER LEDtube 1200mm UE 14.5W 840 T8	G13	70000 h	200000X
929001376902	MASTER LEDtube 1200mm UE 14.5W 865 T8	G13	70000 h	200000X
929001377002	MASTER LEDtube 1500mm UE 21.5W 840 T8	G13	70000 h	200000X
929001377102	MASTER LEDtube 1500mm UE 21.5W 865 T8	G13	70000 h	200000X
929001812102	MASTER LEDtube 900mm 8.5W833 T8 FOOD	G13	50000 h	50000X
929001812302	MASTER LEDtube 1500mm 20W833 T8 FOOD	G13	50000 h	50000X
929001877312	MASTER LEDtube 1200mm HO VWV 18W 840 T8	G13	60000 h	200000X
929001877412	MASTER LEDtube 1200mm HO VWV 18W 865 T8	G13	60000 h	200000X

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
929001877512	MASTER LEDtube 600mm HO VWV 10W 840 T8	G13	60000 h	200000X
929001877612	MASTER LEDtube 600mm HO VWV 10W 865 T8	G13	60000 h	200000X
929001878502	MASTER LEDtube Sensor 1200mm HO 16.5W840 T8	G13	50000 h	200000X
929001878602	MASTER LEDtube Sensor 1200mm HO 16.5W865 T8	G13	50000 h	200000X
929001878702	MASTER LEDtube Sensor 1500mm HO 24W840 T8	G13	50000 h	200000X
929001878802	MASTER LEDtube Sensor 1500mm HO 24W865 T8	G13	50000 h	200000X
929001922602	MASTER LEDtube 1200mm HO 12.5W 830 T8	G13	60000 h	200000X
929001922702	MASTER LEDtube 1200mm HO 12.5W 840 T8	G13	60000 h	200000X
929001922802	MASTER LEDtube 1200mm HO 12.5W 865 T8	G13	60000 h	200000X
929001922902	MASTER LEDtube 1500mm HO 18.2W 830 T8	G13	60000 h	200000X
929001923002	MASTER LEDtube 1500mm HO 18.2W 840 T8	G13	60000 h	200000X
929001923102	MASTER LEDtube 1500mm HO 18.2W 865 T8	G13	60000 h	200000X
929001923402	MASTER LEDtube 1200mm UO 16W 830 T8 G	G13	50000 h	200000X
929001923432	MASTER LEDtube 1200mm UO 16W 830 T8 G I	G13	50000 h	200000X
929001923502	MASTER LEDtube 1200mm UO 16W 840 T8 G	G13	50000 h	200000X
929001923602	MASTER LEDtube 1200mm UO 16W 865 T8 G	G13	50000 h	200000X
929001923702	MASTER LEDtube 1500mm UO 24W 830 T8 G	G13	50000 h	200000X
929001923732	MASTER LEDtube 1500mm UO 24W 830 T8 G I	G13	50000 h	200000X
929001923802	MASTER LEDtube 1500mm UO 24W 840 T8 G	G13	50000 h	200000X
929001923902	MASTER LEDtube 1500mm UO 24W 865 T8 G	G13	50000 h	200000X
929001961102	MASTER LEDtube 1050mm 16W 840 T8	G13	50000 h	200000X
929002329702	MASTER LEDtube DC72-110V 1200mm 18W 840 T8	G13	50000 h	50000X
929002329802	MASTER LEDtube DC72-110V 450mm 6W 840 T8	G13	50000 h	50000X

Approval and Application

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929000299902	MASTER LEDtube Starter EMP	-	-
929001801432	MASTER LEDtube Starter EMP GenII OP	-	-
929001161102	MASTER LEDtube 1800mm 25W 840 T8 ROT	25 kWh	A++
929001187912	Master LEDTube 600 mm 10W 840 T8 I W	10 kWh	A+
929001187972	Master LEDTube 600 mm 10W 840 T8 I W	10 kWh	A+
929001188012	Master LEDTube 600 mm 10W 865 T8 I W	10 kWh	A+
929001188072	Master LEDTube 600 mm 10W 865 T8 I W	10 kWh	A+
929001187712	Master LEDTube 1200 mm 18W 840 T8 I W	18 kWh	A+
929001187772	Master LEDTube 1200 mm 18W 840 T8 I W	18 kWh	A+
929001187782	Master LEDTube 1200 mm 18W 840 T8 I W	18 kWh	A+
929001187812	Master LEDTube 1200 mm 18W 865 T8 I W	18 kWh	A+
929001187872	Master LEDTube 1200 mm 18W 865 T8 I W	18 kWh	A+
929001187882	Master LEDTube 1200 mm 18W 865 T8 I W	18 kWh	A+
929001297608	MASTER LEDtube STD 1200mm 10.5W840 T8 I	11 kWh	A++
929001297708	MASTER LEDtube STD 1200mm 10.5W865 T8 I	11 kWh	A++
929001375208	MASTER LEDtube 1200mm 14W 840 T8 THD	14 kWh	A++
929001375308	MASTER LEDtube 1200mm 14W 865 T8 THD	14 kWh	A++
929001375602	MASTER LEDtube 1050mm 16W 830 T8	16 kWh	A++
929001297802	MASTER LEDtube 1200mm UO 16W 830 T8	16 kWh	A++
929001297902	MASTER LEDtube 1200mm UO 16W 840 T8	16 kWh	A++
929001298002	MASTER LEDtube 1200mm UO 16W 865 T8	16 kWh	A++
929001298102	MASTER LEDtube 1500mm UO 24W 830 T8	24 kWh	A++
929001298202	MASTER LEDtube 1500mm UO 24W 840 T8	24 kWh	A++
929001298302	MASTER LEDtube 1500mm UO 24W 865 T8	24 kWh	A++
929002020502	MASTER LEDtube 1200mm UO 15.5W 830 T8	16 kWh	A++

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929002020602	MASTER LEDtube 1200mm UO 15.5W 840 T8	16 kWh	A++
929002020702	MASTER LEDtube 1200mm UO 15.5W 865 T8	16 kWh	A++
929002020802	MASTER LEDtube 1500mm UO 23W 830 T8	23 kWh	A++
929002020902	MASTER LEDtube 1500mm UO 23W 840 T8	23 kWh	A++
929002021002	MASTER LEDtube 1500mm UO 23W 865 T8	23 kWh	A++
929001298402	MASTER LEDtube 900mm HO 12W 840 T8	12 kWh	A++
929001298502	MASTER LEDtube 900mm HO 12W 865 T8	12 kWh	A++
929001307002	MASTER LEDtube 600mm HO 8W830 T8	8 kWh	A++
929001307102	MASTER LEDtube 600mm HO 8W840 T8	8 kWh	A++
929001307202	MASTER LEDtube 600mm HO 8W865 T8	8 kWh	A++
929001812202	MASTER LEDtube 1200mm 12W833 T8 FOOD	12 kWh	A+
929001907908	MASTER LEDtube 1200mm UO 16W 830 T8 FF RCA	16 kWh	A++
929001908008	MASTER LEDtube 1200mm UO 16W 840 T8 FF RCA	16 kWh	A++
929001908108	MASTER LEDtube 1200mm UO 16W 865 T8 FF RCA	16 kWh	A++
929001908208	MASTER LEDtube 1500mm UO 24W 830 T8 FF RCA	24 kWh	A++
929001908308	MASTER LEDtube 1500mm UO 24W 840 T8 FF RCA	24 kWh	A++
929001908408	MASTER LEDtube 1500mm UO 24W 865 T8 FF RCA	24 kWh	A++
929001299208	MASTER LEDtube 1200mm HO 14W830 T8	14 kWh	A++
929001299308	MASTER LEDtube 1200mm HO 14W840 T8	14 kWh	A++
929001299408	MASTER LEDtube 1200mm HO 14W865 T8	14 kWh	A++
929001368112	Master LEDTube 8ft 33W 4000lm 865 T8	-	A+
929001368172	Master LEDTube 8ft 33W 4000lm 865 T8 BR	-	A+
929001375412	MASTER LEDtube STD 1200mm 14W840 T8 I W	14 kWh	A++
929001375442	MASTER LEDtube STD 1200mm 14W840 T8 I W	14 kWh	A++
929001375542	MASTER LEDtube STD 1200mm 14W865 T8 I W	14 kWh	A++

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001376802	MASTER LEDtube 1200mm UE 14.5W 840 T8	15 kWh	A++
929001376902	MASTER LEDtube 1200mm UE 14.5W 865 T8	15 kWh	A++
929001377002	MASTER LEDtube 1500mm UE 21.5W 840 T8	22 kWh	A++
929001377102	MASTER LEDtube 1500mm UE 21.5W 865 T8	22 kWh	A++
929001812102	MASTER LEDtube 900mm 8.5W833 T8 FOOD	9 kWh	A+
929001812302	MASTER LEDtube 1500mm 20W833 T8 FOOD	20 kWh	A+
929001877312	MASTER LEDtube 1200mm HO VWV 18W 840 T8	18 kWh	A+
929001877412	MASTER LEDtube 1200mm HO VWV 18W 865 T8	18 kWh	A+
929001877512	MASTER LEDtube 600mm HO VWV 10W 840 T8	10 kWh	A+
929001877612	MASTER LEDtube 600mm HO VWV 10W 865 T8	10 kWh	A+
929001878502	MASTER LEDtube Sensor 1200mm HO 16.5W840 T8	17 kWh	A++
929001878602	MASTER LEDtube Sensor 1200mm HO 16.5W865 T8	17 kWh	A++
929001878702	MASTER LEDtube Sensor 1500mm HO 24W840 T8	24 kWh	A++
929001878802	MASTER LEDtube Sensor 1500mm HO 24W865 T8	24 kWh	A++
929001922602	MASTER LEDtube 1200mm HO 12.5W 830 T8	13 kWh	A++
929001922702	MASTER LEDtube 1200mm HO 12.5W 840 T8	13 kWh	A++

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001922802	MASTER LEDtube 1200mm HO 12.5W 865 T8	13 kWh	A++
929001922902	MASTER LEDtube 1500mm HO 18.2W 830 T8	19 kWh	A++
929001923002	MASTER LEDtube 1500mm HO 18.2W 840 T8	19 kWh	A++
929001923102	MASTER LEDtube 1500mm HO 18.2W 865 T8	19 kWh	A++
929001923402	MASTER LEDtube 1200mm UO 16W 830 T8 G	16 kWh	A++
929001923432	MASTER LEDtube 1200mm UO 16W 830 T8 G I	16 kWh	A++
929001923502	MASTER LEDtube 1200mm UO 16W 840 T8 G	16 kWh	A++
929001923602	MASTER LEDtube 1200mm UO 16W 865 T8 G	16 kWh	A++
929001923702	MASTER LEDtube 1500mm UO 24W 830 T8 G	24 kWh	A++
929001923732	MASTER LEDtube 1500mm UO 24W 830 T8 G I	24 kWh	A++
929001923802	MASTER LEDtube 1500mm UO 24W 840 T8 G	24 kWh	A++
929001923902	MASTER LEDtube 1500mm UO 24W 865 T8 G	24 kWh	A++
929001961102	MASTER LEDtube 1050mm 16W 840 T8	16 kWh	A++
929002329702	MASTER LEDtube DC72-110V 1200mm 18W 840 T8	20 kWh	A++
929002329802	MASTER LEDtube DC72-110V 450mm 6W 840 T8	7 kWh	A++

Controls and Dimming

Order Code	Full Product Name	Dimmable
929000299902	MASTER LEDtube Starter EMP	-
929001801432	MASTER LEDtube Starter EMP GenII OP	-
929001161102	MASTER LEDtube 1800mm 25W 840 T8 ROT	No
929001187912	Master LEDTube 600 mm 10W 840 T8 I W	No
929001187972	Master LEDTube 600 mm 10W 840 T8 I W	No
929001188012	Master LEDTube 600 mm 10W 865 T8 I W	No
929001188072	Master LEDTube 600 mm 10W 865 T8 I W	No
929001187712	Master LEDTube 1200 mm 18W 840 T8 I W	No
929001187772	Master LEDTube 1200 mm 18W 840 T8 I W	No
929001187782	Master LEDTube 1200 mm 18W 840 T8 I W	No
929001187812	Master LEDTube 1200 mm 18W 865 T8 I W	No
929001187872	Master LEDTube 1200 mm 18W 865 T8 I W	No
929001187882	Master LEDTube 1200 mm 18W 865 T8 I W	No
929001297608	MASTER LEDtube STD 1200mm 10.5W840 T8 I	No

Order Code	Full Product Name	Dimmable
929001297708	MASTER LEDtube STD 1200mm 10.5W865 T8 I	No
929001375208	MASTER LEDtube 1200mm 14W 840 T8 THD	No
929001375308	MASTER LEDtube 1200mm 14W 865 T8 THD	No
929001375602	MASTER LEDtube 1050mm 16W 830 T8	No
929001297802	MASTER LEDtube 1200mm UO 16W 830 T8	No
929001297902	MASTER LEDtube 1200mm UO 16W 840 T8	No
929001298002	MASTER LEDtube 1200mm UO 16W 865 T8	No
929001298102	MASTER LEDtube 1500mm UO 24W 830 T8	No
929001298202	MASTER LEDtube 1500mm UO 24W 840 T8	No
929001298302	MASTER LEDtube 1500mm UO 24W 865 T8	No
929002020502	MASTER LEDtube 1200mm UO 15.5W 830 T8	No
929002020602	MASTER LEDtube 1200mm UO 15.5W 840 T8	No
929002020702	MASTER LEDtube 1200mm UO 15.5W 865 T8	No
929002020802	MASTER LEDtube 1500mm UO 23W 830 T8	No

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
929002020902	MASTER LEDtube 1500mm UO 23W 840 T8	No	929001812302	MASTER LEDtube 1500mm 20W833 T8 FOOD	No
929002021002	MASTER LEDtube 1500mm UO 23W 865 T8	No	929001877312	MASTER LEDtube 1200mm HO VWV 18W 840 T8	No
929001298402	MASTER LEDtube 900mm HO 12W 840 T8	No	929001877412	MASTER LEDtube 1200mm HO VWV 18W 865 T8	No
929001298502	MASTER LEDtube 900mm HO 12W 865 T8	No	929001877512	MASTER LEDtube 600mm HO VWV 10W 840 T8	No
929001307002	MASTER LEDtube 600mm HO 8W830 T8	No	929001877612	MASTER LEDtube 600mm HO VWV 10W 865 T8	No
929001307102	MASTER LEDtube 600mm HO 8W840 T8	No	929001878502	MASTER LEDtube Sensor 1200mm HO 16.5W840 T8	Yes
929001307202	MASTER LEDtube 600mm HO 8W865 T8	No	929001878602	MASTER LEDtube Sensor 1200mm HO 16.5W865 T8	Yes
929001812202	MASTER LEDtube 1200mm 12W833 T8 FOOD	No	929001878702	MASTER LEDtube Sensor 1500mm HO 24W840 T8	Yes
929001907908	MASTER LEDtube 1200mm UO 16W 830 T8 FF RCA	No	929001878802	MASTER LEDtube Sensor 1500mm HO 24W865 T8	Yes
929001908008	MASTER LEDtube 1200mm UO 16W 840 T8 FF RCA	No	929001922602	MASTER LEDtube 1200mm HO 12.5W 830 T8	No
929001908108	MASTER LEDtube 1200mm UO 16W 865 T8 FF RCA	No	929001922702	MASTER LEDtube 1200mm HO 12.5W 840 T8	No
929001908208	MASTER LEDtube 1500mm UO 24W 830 T8 FF RCA	No	929001922802	MASTER LEDtube 1200mm HO 12.5W 865 T8	No
929001908308	MASTER LEDtube 1500mm UO 24W 840 T8 FF RCA	No	929001922902	MASTER LEDtube 1500mm HO 18.2W 830 T8	No
929001908408	MASTER LEDtube 1500mm UO 24W 865 T8 FF RCA	No	929001923002	MASTER LEDtube 1500mm HO 18.2W 840 T8	No
929001299208	MASTER LEDtube 1200mm HO 14W830 T8	No	929001923102	MASTER LEDtube 1500mm HO 18.2W 865 T8	No
929001299308	MASTER LEDtube 1200mm HO 14W840 T8	No	929001923402	MASTER LEDtube 1200mm UO 16W 830 T8 G	No
929001299408	MASTER LEDtube 1200mm HO 14W865 T8	No	929001923432	MASTER LEDtube 1200mm UO 16W 830 T8 G I	No
929001368112	Master LEDTube 8ft 33W 4000lm 865 T8	No	929001923502	MASTER LEDtube 1200mm UO 16W 840 T8 G	No
929001368172	Master LEDTube 8ft 33W 4000lm 865 T8 BR	No	929001923602	MASTER LEDtube 1200mm UO 16W 865 T8 G	No
929001375412	MASTER LEDtube STD 1200mm 14W840 T8 I W	No	929001923702	MASTER LEDtube 1500mm UO 24W 830 T8 G	No
929001375442	MASTER LEDtube STD 1200mm 14W840 T8 I W	No	929001923732	MASTER LEDtube 1500mm UO 24W 830 T8 G I	No
929001375542	MASTER LEDtube STD 1200mm 14W865 T8 I W	No	929001923802	MASTER LEDtube 1500mm UO 24W 840 T8 G	No
929001376802	MASTER LEDtube 1200mm UE 14.5W 840 T8	No	929001923902	MASTER LEDtube 1500mm UO 24W 865 T8 G	No
929001376902	MASTER LEDtube 1200mm UE 14.5W 865 T8	No	929001961102	MASTER LEDtube 1050mm 16W 840 T8	No
929001377002	MASTER LEDtube 1500mm UE 21.5W 840 T8	No	929002329702	MASTER LEDtube DC72-110V 1200mm 18W 840 T8	No
929001377102	MASTER LEDtube 1500mm UE 21.5W 865 T8	No	929002329802	MASTER LEDtube DC72-110V 450mm 6W 840 T8	No
929001812102	MASTER LEDtube 900mm 8.5W833 T8 FOOD	No			

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color		Llmf At End Of		Luminous Flux (Rated) (Nom)
					Rendering Index (Nom)	Nominal	Luminous Flux (Nom)	Lifetime (Nom)	
929000299902	MASTER LEDtube Starter EMP	-	-	-	-	-	-	-	-
929001801432	MASTER LEDtube Starter EMP GenII OP	-	-	-	-	-	-	-	-
929001161102	MASTER LEDtube 1800mm 25W 840 T8 ROT	160 °	840	4000 K	83	70 %	3700 lm	-	-
929001187912	Master LEDTube 600 mm 10W 840 T8 I W	160 °	840	4000 K	82	70 %	1050 lm	-	-
929001187972	Master LEDTube 600 mm 10W 840 T8 I W	160 °	840	4000 K	82	70 %	1050 lm	-	-
929001188012	Master LEDTube 600 mm 10W 865 T8 I W	160 °	865	6500 K	82	70 %	1050 lm	-	-
929001188072	Master LEDTube 600 mm 10W 865 T8 I W	160 °	865	6500 K	82	70 %	1050 lm	-	-
929001187712	Master LEDTube 1200 mm 18W 840 T8 I W	160 °	840	4000 K	82	70 %	2100 lm	-	-
929001187772	Master LEDTube 1200 mm 18W 840 T8 I W	160 °	840	4000 K	82	70 %	2100 lm	-	-
929001187782	Master LEDTube 1200 mm 18W 840 T8 I W	160 °	840	4000 K	82	70 %	2100 lm	-	-
929001187812	Master LEDTube 1200 mm 18W 865 T8 I W	160 °	865	6500 K	82	70 %	2100 lm	-	-
929001187872	Master LEDTube 1200 mm 18W 865 T8 I W	160 °	865	6500 K	82	70 %	2100 lm	-	-
929001187882	Master LEDTube 1200 mm 18W 865 T8 I W	160 °	865	6500 K	82	70 %	2100 lm	-	-
929001297608	MASTER LEDtube STD 1200mm 10.5W840 T8 I	-	840	4000 K	83	70 %	1600 lm	-	-
929001297708	MASTER LEDtube STD 1200mm 10.5W865 T8 I	-	865	6500 K	83	70 %	1600 lm	-	-

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color		Llmf At End Of		Luminous Flux (Rated) (Nom)
					Rendering Index (Nom)	Nominal Lifetime (Nom)	Luminous Flux (Nom)		
929001375208	MASTER LEDtube 1200mm 14W 840 T8 THD	-	840	4000 K	83	70 %	2100 lm	-	
929001375308	MASTER LEDtube 1200mm 14W 865 T8 THD	-	865	6500 K	83	70 %	2100 lm	-	
929001375602	MASTER LEDtube 1050mm 16W 830 T8	-	830	3000 K	80	70 %	2300 lm	-	
929001297802	MASTER LEDtube 1200mm UO 16W 830 T8	160 °	830	3000 K	83	70 %	2300 lm	-	
929001297902	MASTER LEDtube 1200mm UO 16W 840 T8	160 °	840	4000 K	83	70 %	2500 lm	-	
929001298002	MASTER LEDtube 1200mm UO 16W 865 T8	160 °	865	6500 K	83	70 %	2500 lm	-	
929001298102	MASTER LEDtube 1500mm UO 24W 830 T8	160 °	830	3000 K	83	70 %	3400 lm	-	
929001298202	MASTER LEDtube 1500mm UO 24W 840 T8	160 °	840	4000 K	83	70 %	3700 lm	-	
929001298302	MASTER LEDtube 1500mm UO 24W 865 T8	160 °	865	6500 K	83	70 %	3700 lm	-	
929002020502	MASTER LEDtube 1200mm UO 15.5W 830 T8	160 °	830	3000 K	83	70 %	2300 lm	-	
929002020602	MASTER LEDtube 1200mm UO 15.5W 840 T8	160 °	840	4000 K	83	70 %	2500 lm	-	
929002020702	MASTER LEDtube 1200mm UO 15.5W 865 T8	160 °	865	6500 K	83	70 %	2500 lm	-	
929002020802	MASTER LEDtube 1500mm UO 23W 830 T8	160 °	830	3000 K	83	70 %	3400 lm	-	
929002020902	MASTER LEDtube 1500mm UO 23W 840 T8	160 °	840	4000 K	83	70 %	3700 lm	-	
929002021002	MASTER LEDtube 1500mm UO 23W 865 T8	160 °	865	6500 K	83	70 %	3700 lm	-	
929001298402	MASTER LEDtube 900mm HO 12W 840 T8	160 °	840	4000 K	83	70 %	1575 lm	-	
929001298502	MASTER LEDtube 900mm HO 12W 865 T8	160 °	865	6500 K	83	70 %	1575 lm	-	
929001307002	MASTER LEDtube 600mm HO 8W830 T8	160 °	830	3000 K	83	70 %	1000 lm	-	
929001307102	MASTER LEDtube 600mm HO 8W840 T8	160 °	840	4000 K	83	70 %	1050 lm	-	
929001307202	MASTER LEDtube 600mm HO 8W865 T8	160 °	865	6500 K	83	70 %	1050 lm	-	
929001812202	MASTER LEDtube 1200mm 12W833 T8 FOOD	-	833	3300 K	83	70 %	1000 lm	-	
929001907908	MASTER LEDtube 1200mm UO 16W 830 T8 FF RCA	160 °	830	3000 K	83	70 %	2300 lm	-	
929001908008	MASTER LEDtube 1200mm UO 16W 840 T8 FF RCA	160 °	840	4000 K	83	70 %	2500 lm	-	
929001908108	MASTER LEDtube 1200mm UO 16W 865 T8 FF RCA	160 °	865	6500 K	83	70 %	2500 lm	-	
929001908208	MASTER LEDtube 1500mm UO 24W 830 T8 FF RCA	160 °	830	3000 K	83	70 %	3400 lm	-	
929001908308	MASTER LEDtube 1500mm UO 24W 840 T8 FF RCA	160 °	840	4000 K	83	70 %	3700 lm	-	
929001908408	MASTER LEDtube 1500mm UO 24W 865 T8 FF RCA	160 °	865	6500 K	83	70 %	3700 lm	-	
929001299208	MASTER LEDtube 1200mm HO 14W830 T8	-	830	3000 K	83	70 %	2000 lm	-	
929001299308	MASTER LEDtube 1200mm HO 14W840 T8	-	840	4000 K	83	70 %	2100 lm	-	

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color	Llmf At End Of	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
					Rendering Index (Nom)	Nominal Lifetime (Nom)		
929001299408	MASTER LEDtube 1200mm HO 14W865 T8	-	865	6500 K	83	70 %	2100 lm	-
929001368112	Master LEDTube 8ft 33W 4000lm 865 T8	-	865	6500 K	80	70 %	4000 lm	-
929001368172	Master LEDTube 8ft 33W 4000lm 865 T8 BR	-	865	6500 K	80	70 %	4000 lm	-
929001375412	MASTER LEDtube STD 1200mm 14W840 T8 I W	-	840	4000 K	80	70 %	2100 lm	-
929001375442	MASTER LEDtube STD 1200mm 14W840 T8 I W	-	840	4000 K	80	70 %	2100 lm	2100 lm
929001375542	MASTER LEDtube STD 1200mm 14W865 T8 I W	-	865	6500 K	80	70 %	2100 lm	2100 lm
929001376802	MASTER LEDtube 1200mm UE 14.5W 840 T8	160 °	840	4000 K	83	70 %	2500 lm	-
929001376902	MASTER LEDtube 1200mm UE 14.5W 865 T8	160 °	865	6500 K	83	70 %	2500 lm	-
929001377002	MASTER LEDtube 1500mm UE 21.5W 840 T8	160 °	840	4000 K	83	70 %	3700 lm	-
929001377102	MASTER LEDtube 1500mm UE 21.5W 865 T8	160 °	865	6500 K	83	70 %	3700 lm	-
929001812102	MASTER LEDtube 900mm 8.5W833 T8 FOOD	-	833	3300 K	83	70 %	750 lm	-
929001812302	MASTER LEDtube 1500mm 20W833 T8 FOOD	-	833	3300 K	83	70 %	1680 lm	-
929001877312	MASTER LEDtube 1200mm HO VWV 18W 840 T8	160 °	840	4000 K	80	70 %	2100 lm	-
929001877412	MASTER LEDtube 1200mm HO VWV 18W 865 T8	160 °	865	6500 K	80	70 %	2100 lm	-
929001877512	MASTER LEDtube 600mm HO VWV 10W 840 T8	160 °	840	4000 K	80	70 %	1050 lm	-
929001877612	MASTER LEDtube 600mm HO VWV 10W 865 T8	160 °	865	6500 K	80	70 %	1050 lm	-
929001878502	MASTER LEDtube Sensor 1200mm HO 16.5W840 T8	240 °	840	4000 K	83	70 %	2100 lm	-
929001878602	MASTER LEDtube Sensor 1200mm HO 16.5W865 T8	240 °	865	6500 K	83	70 %	2100 lm	-
929001878702	MASTER LEDtube Sensor 1500mm HO 24W840 T8	240 °	840	4000 K	83	70 %	3100 lm	-
929001878802	MASTER LEDtube Sensor 1500mm HO 24W865 T8	240 °	865	6500 K	83	70 %	3100 lm	-
929001922602	MASTER LEDtube 1200mm HO 12.5W 830 T8	160 °	830	3000 K	83	70 %	2000 lm	-
929001922702	MASTER LEDtube 1200mm HO 12.5W 840 T8	160 °	840	4000 K	83	70 %	2100 lm	-
929001922802	MASTER LEDtube 1200mm HO 12.5W 865 T8	160 °	865	6500 K	83	70 %	2100 lm	-
929001922902	MASTER LEDtube 1500mm HO 18.2W 830 T8	160 °	830	3000 K	83	70 %	2900 lm	-
929001923002	MASTER LEDtube 1500mm HO 18.2W 840 T8	160 °	840	4000 K	83	70 %	3100 lm	-
929001923102	MASTER LEDtube 1500mm HO 18.2W 865 T8	160 °	865	6500 K	83	70 %	3100 lm	-

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color	Llmf At End Of		Luminous Flux (Rated) (Nom)
					Rendering Index (Nom)	Nominal Lifetime (Nom)	Luminous Flux (Nom)	
929001923402	MASTER LEDtube 1200mm UO 16W 830 T8 G	240 °	830	3000 K	83	70 %	2300 lm	-
929001923432	MASTER LEDtube 1200mm UO 16W 830 T8 G I	240 °	830	3000 K	83	70 %	2300 lm	-
929001923502	MASTER LEDtube 1200mm UO 16W 840 T8 G	240 °	840	4000 K	83	70 %	2500 lm	-
929001923602	MASTER LEDtube 1200mm UO 16W 865 T8 G	240 °	865	6500 K	83	70 %	2500 lm	-
929001923702	MASTER LEDtube 1500mm UO 24W 830 T8 G	240 °	830	3000 K	83	70 %	3400 lm	-
929001923732	MASTER LEDtube 1500mm UO 24W 830 T8 G I	240 °	830	3000 K	83	70 %	3400 lm	-
929001923802	MASTER LEDtube 1500mm UO 24W 840 T8 G	240 °	840	4000 K	83	70 %	3700 lm	-
929001923902	MASTER LEDtube 1500mm UO 24W 865 T8 G	240 °	865	6500 K	83	70 %	3700 lm	-
929001961102	MASTER LEDtube 1050mm 16W 840 T8	160 °	840	4000 K	83	70 %	2500 lm	-
929002329702	MASTER LEDtube DC72-110V 1200mm 18W 840 T8	240 °	840	4000 K	80	70 %	2700 lm	-
929002329802	MASTER LEDtube DC72-110V 450mm 6W 840 T8	240 °	840	4000 K	80	70 %	850 lm	-

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape	Order Code	Full Product Name	Bulb Finish	Bulb Shape
929000299902	MASTER LEDtube Starter EMP	-	-	929001298202	MASTER LEDtube 1500mm UO 24W 840 T8	-	-
929001801432	MASTER LEDtube Starter EMP GenII OP	-	-	929001298302	MASTER LEDtube 1500mm UO 24W 865 T8	-	-
929001161102	MASTER LEDtube 1800mm 25W 840 T8 ROT	-	-	929002020502	MASTER LEDtube 1200mm UO 15.5W 830 T8	-	-
929001187912	Master LEDTube 600 mm 10W 840 T8 I W	-	-	929002020602	MASTER LEDtube 1200mm UO 15.5W 840 T8	-	-
929001187972	Master LEDTube 600 mm 10W 840 T8 I W	-	-	929002020702	MASTER LEDtube 1200mm UO 15.5W 865 T8	-	-
929001188012	Master LEDTube 600 mm 10W 865 T8 I W	-	-	929002020802	MASTER LEDtube 1500mm UO 23W 830 T8	-	-
929001188072	Master LEDTube 600 mm 10W 865 T8 I W	-	-	929002020902	MASTER LEDtube 1500mm UO 23W 840 T8	-	-
929001187712	Master LEDTube 1200 mm 18W 840 T8 I W	-	-	929002021002	MASTER LEDtube 1500mm UO 23W 865 T8	-	-
929001187772	Master LEDTube 1200 mm 18W 840 T8 I W	-	-	929001298402	MASTER LEDtube 900mm HO 12W 840 T8	-	-
929001187782	Master LEDTube 1200 mm 18W 840 T8 I W	-	-	929001298502	MASTER LEDtube 900mm HO 12W 865 T8	-	-
929001187812	Master LEDTube 1200 mm 18W 865 T8 I W	-	-	929001307002	MASTER LEDtube 600mm HO 8W830 T8	Frosted	-
929001187872	Master LEDTube 1200 mm 18W 865 T8 I W	-	-	929001307102	MASTER LEDtube 600mm HO 8W840 T8	Frosted	-
929001187882	Master LEDTube 1200 mm 18W 865 T8 I W	-	-	929001307202	MASTER LEDtube 600mm HO 8W865 T8	Frosted	-
929001297608	MASTER LEDtube STD 1200mm 10.5W840 T8 I	-	-	929001812202	MASTER LEDtube 1200mm 12W833 T8 FOOD	-	-
929001297708	MASTER LEDtube STD 1200mm 10.5W865 T8 I	-	-	929001907908	MASTER LEDtube 1200mm UO 16W 830 T8 FF RCA	-	-
929001375208	MASTER LEDtube 1200mm 14W 840 T8 THD	-	-	929001908008	MASTER LEDtube 1200mm UO 16W 840 T8 FF RCA	-	-
929001375308	MASTER LEDtube 1200mm 14W 865 T8 THD	-	-	929001908108	MASTER LEDtube 1200mm UO 16W 865 T8 FF RCA	-	-
929001375602	MASTER LEDtube 1050mm 16W 830 T8	-	-				
929001297802	MASTER LEDtube 1200mm UO 16W 830 T8	-	-				
929001297902	MASTER LEDtube 1200mm UO 16W 840 T8	-	-				
929001298002	MASTER LEDtube 1200mm UO 16W 865 T8	-	-				
929001298102	MASTER LEDtube 1500mm UO 24W 830 T8	-	-				

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	Bulb Finish	Bulb Shape	Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001908208	MASTER LEDtube 1500mm UO 24W 830 T8 FF RCA	-	-	929001878602	MASTER LEDtube Sensor 1200mm HO 16.5W865 T8	-	-
929001908308	MASTER LEDtube 1500mm UO 24W 840 T8 FF RCA	-	-	929001878702	MASTER LEDtube Sensor 1500mm HO 24W840 T8	-	-
929001908408	MASTER LEDtube 1500mm UO 24W 865 T8 FF RCA	-	-	929001878802	MASTER LEDtube Sensor 1500mm HO 24W865 T8	-	-
929001299208	MASTER LEDtube 1200mm HO 14W830 T8	-	-	929001922602	MASTER LEDtube 1200mm HO 12.5W 830 T8	-	-
929001299308	MASTER LEDtube 1200mm HO 14W840 T8	-	-	929001922702	MASTER LEDtube 1200mm HO 12.5W 840 T8	-	-
929001299408	MASTER LEDtube 1200mm HO 14W865 T8	-	-	929001922802	MASTER LEDtube 1200mm HO 12.5W 865 T8	-	-
929001368112	Master LEDTube 8ft 33W 4000lm 865 T8	-	-	929001922902	MASTER LEDtube 1500mm HO 18.2W 830 T8	-	-
929001368172	Master LEDTube 8ft 33W 4000lm 865 T8 BR	-	-	929001923002	MASTER LEDtube 1500mm HO 18.2W 840 T8	-	-
929001375412	MASTER LEDtube STD 1200mm 14W840 T8 I W	-	-	929001923102	MASTER LEDtube 1500mm HO 18.2W 865 T8	-	-
929001375442	MASTER LEDtube STD 1200mm 14W840 T8 I W	Frosted	-	929001923402	MASTER LEDtube 1200mm UO 16W 830 T8 G	-	-
929001375542	MASTER LEDtube STD 1200mm 14W865 T8 I W	Frosted	-	929001923432	MASTER LEDtube 1200mm UO 16W 830 T8 G I	-	-
929001376802	MASTER LEDtube 1200mm UE 14.5W 840 T8	-	-	929001923502	MASTER LEDtube 1200mm UO 16W 840 T8 G	-	-
929001376902	MASTER LEDtube 1200mm UE 14.5W 865 T8	-	-	929001923602	MASTER LEDtube 1200mm UO 16W 865 T8 G	-	-
929001377002	MASTER LEDtube 1500mm UE 21.5W 840 T8	-	-	929001923702	MASTER LEDtube 1500mm UO 24W 830 T8 G	-	-
929001377102	MASTER LEDtube 1500mm UE 21.5W 865 T8	-	-	929001923732	MASTER LEDtube 1500mm UO 24W 830 T8 G I	-	-
929001812102	MASTER LEDtube 900mm 8.5W833 T8 FOOD	-	-	929001923802	MASTER LEDtube 1500mm UO 24W 840 T8 G	-	-
929001812302	MASTER LEDtube 1500mm 20W833 T8 FOOD	-	-	929001923902	MASTER LEDtube 1500mm UO 24W 865 T8 G	-	-
929001877312	MASTER LEDtube 1200mm HO VWV 18W 840 T8	-	Tube, single- ended	929001961102	MASTER LEDtube 1050mm 16W 840 T8	-	-
929001877412	MASTER LEDtube 1200mm HO VWV 18W 865 T8	-	Tube, single- ended	929002329702	MASTER LEDtube DC72-110V 1200mm 18W 840 T8	Frosted	-
929001877512	MASTER LEDtube 600mm HO VWV 10W 840 T8	Frosted	Tube, single- ended	929002329802	MASTER LEDtube DC72-110V 450mm 6W 840 T8	Frosted	-
929001877612	MASTER LEDtube 600mm HO VWV 10W 865 T8	Frosted	Tube, single- ended				
929001878502	MASTER LEDtube Sensor 1200mm HO 16.5W840 T8	-	-				

Temperature







Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)	T-Storage (Max)	T-Storage (Min)
929000299902	MASTER LEDtube Starter EMP	-	-	-	-	-
929001801432	MASTER LEDtube Starter EMP GenII OP	-	-	-	-	-
929001161102	MASTER LEDtube 1800mm 25W 840 T8 ROT	30 °C	-5 °C	61 °C	65 °C	-40 °C
929001187912	Master LEDTube 600 mm 10W 840 T8 I W	45 °C	-20 °C	70 °C	65 °C	-40 °C
929001187972	Master LEDTube 600 mm 10W 840 T8 I W	45 °C	-20 °C	70 °C	65 °C	-40 °C
929001188012	Master LEDTube 600 mm 10W 865 T8 I W	45 °C	-20 °C	70 °C	65 °C	-40 °C
929001188072	Master LEDTube 600 mm 10W 865 T8 I W	45 °C	-20 °C	70 °C	65 °C	-40 °C
929001187712	Master LEDTube 1200 mm 18W 840 T8 I W	45 °C	-20 °C	70 °C	65 °C	-40 °C

MASTER LEDtube EM/Mains T8













Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)	T-Storage (Max)	T-Storage (Min)
929001187772	Master LEDTube 1200 mm 18W 840 T8 I W	45 °C	-20 °C	70 °C	65 °C	-40 °C
929001187782	Master LEDTube 1200 mm 18W 840 T8 I W	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001187812	Master LEDTube 1200 mm 18W 865 T8 I W	45 °C	-20 °C	70 °C	65 °C	-40 °C
929001187872	Master LEDTube 1200 mm 18W 865 T8 I W	45 °C	-20 °C	70 °C	65 °C	-40 °C
929001187882	Master LEDTube 1200 mm 18W 865 T8 I W	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001297608	MASTER LEDtube STD 1200mm 10.5W840 T8 I	45 °C	-20 °C	50 °C	65 °C	-40 °C
929001297708	MASTER LEDtube STD 1200mm 10.5W865 T8 I	45 °C	-20 °C	50 °C	65 °C	-40 °C
929001375208	MASTER LEDtube 1200mm 14W 840 T8 THD	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001375308	MASTER LEDtube 1200mm 14W 865 T8 THD	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001375602	MASTER LEDtube 1050mm 16W 830 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001297802	MASTER LEDtube 1200mm UO 16W 830 T8	35 °C	-20 °C	55 °C	65 °C	-40 °C
929001297902	MASTER LEDtube 1200mm UO 16W 840 T8	35 °C	-20 °C	55 °C	65 °C	-40 °C
929001298002	MASTER LEDtube 1200mm UO 16W 865 T8	35 °C	-20 °C	55 °C	65 °C	-40 °C
929001298102	MASTER LEDtube 1500mm UO 24W 830 T8	35 °C	-20 °C	60 °C	65 °C	-40 °C
929001298202	MASTER LEDtube 1500mm UO 24W 840 T8	35 °C	-20 °C	60 °C	65 °C	-40 °C
929001298302	MASTER LEDtube 1500mm UO 24W 865 T8	35 °C	-20 °C	60 °C	65 °C	-40 °C
929002020502	MASTER LEDtube 1200mm UO 15.5W 830 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929002020602	MASTER LEDtube 1200mm UO 15.5W 840 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929002020702	MASTER LEDtube 1200mm UO 15.5W 865 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929002020802	MASTER LEDtube 1500mm UO 23W 830 T8	45 °C	-20 °C	60 °C	65 °C	-40 °C
929002020902	MASTER LEDtube 1500mm UO 23W 840 T8	45 °C	-20 °C	60 °C	65 °C	-40 °C
929002021002	MASTER LEDtube 1500mm UO 23W 865 T8	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001298402	MASTER LEDtube 900mm HO 12W 840 T8	45 °C	-20 °C	50 °C	65 °C	-40 °C
929001298502	MASTER LEDtube 900mm HO 12W 865 T8	45 °C	-20 °C	50 °C	65 °C	-40 °C
929001307002	MASTER LEDtube 600mm HO 8W830 T8	35 °C	-20 °C	50 °C	65 °C	-40 °C
929001307102	MASTER LEDtube 600mm HO 8W840 T8	35 °C	-20 °C	50 °C	65 °C	-40 °C
929001307202	MASTER LEDtube 600mm HO 8W865 T8	35 °C	-20 °C	50 °C	65 °C	-40 °C
929001812202	MASTER LEDtube 1200mm 12W833 T8 FOOD	45 °C	-20 °C	45 °C	65 °C	-40 °C
929001907908	MASTER LEDtube 1200mm UO 16W 830 T8 FF RCA	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001908008	MASTER LEDtube 1200mm UO 16W 840 T8 FF RCA	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001908108	MASTER LEDtube 1200mm UO 16W 865 T8 FF RCA	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001908208	MASTER LEDtube 1500mm UO 24W 830 T8 FF RCA	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001908308	MASTER LEDtube 1500mm UO 24W 840 T8 FF RCA	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001908408	MASTER LEDtube 1500mm UO 24W 865 T8 FF RCA	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001299208	MASTER LEDtube 1200mm HO 14W830 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001299308	MASTER LEDtube 1200mm HO 14W840 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001299408	MASTER LEDtube 1200mm HO 14W865 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001368112	Master LEDTube 8ft 33W 4000lm 865 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001368172	Master LEDTube 8ft 33W 4000lm 865 T8 BR	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001375412	MASTER LEDtube STD 1200mm 14W840 T8 I W	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001375442	MASTER LEDtube STD 1200mm 14W840 T8 I W	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001375542	MASTER LEDtube STD 1200mm 14W865 T8 I W	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001376802	MASTER LEDtube 1200mm UE 14.5W 840 T8	35 °C	-20 °C	55 °C	65 °C	-40 °C
929001376902	MASTER LEDtube 1200mm UE 14.5W 865 T8	35 °C	-20 °C	55 °C	65 °C	-40 °C
929001377002	MASTER LEDtube 1500mm UE 21.5W 840 T8	35 °C	-20 °C	60 °C	65 °C	-40 °C
929001377102	MASTER LEDtube 1500mm UE 21.5W 865 T8	35 °C	-20 °C	60 °C	65 °C	-40 °C
929001812102	MASTER LEDtube 900mm 8.5W833 T8 FOOD	45 °C	-20 °C	45 °C	65 °C	-40 °C
929001812302	MASTER LEDtube 1500mm 20W833 T8 FOOD	45 °C	-20 °C	50 °C	65 °C	-40 °C
929001877312	MASTER LEDtube 1200mm HO VWV 18W 840 T8	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001877412	MASTER LEDtube 1200mm HO VWV 18W 865 T8	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001877512	MASTER LEDtube 600mm HO VWV 10W 840 T8	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001877612	MASTER LEDtube 600mm HO VWV 10W 865 T8	45 °C	-20 °C	60 °C	65 °C	-40 °C

MASTER LEDtube EM/Mains T8

Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)	T-Storage (Max)	T-Storage (Min)
929001878502	MASTER LEDtube Sensor 1200mm HO 16.5W840 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001878602	MASTER LEDtube Sensor 1200mm HO 16.5W865 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001878702	MASTER LEDtube Sensor 1500mm HO 24W840 T8	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001878802	MASTER LEDtube Sensor 1500mm HO 24W865 T8	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001922602	MASTER LEDtube 1200mm HO 12.5W 830 T8	45 °C	-20 °C	50 °C	65 °C	-40 °C
929001922702	MASTER LEDtube 1200mm HO 12.5W 840 T8	45 °C	-20 °C	50 °C	65 °C	-40 °C
929001922802	MASTER LEDtube 1200mm HO 12.5W 865 T8	45 °C	-20 °C	50 °C	65 °C	-40 °C
929001922902	MASTER LEDtube 1500mm HO 18.2W 830 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001923002	MASTER LEDtube 1500mm HO 18.2W 840 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001923102	MASTER LEDtube 1500mm HO 18.2W 865 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001923402	MASTER LEDtube 1200mm UO 16W 830 T8 G	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001923432	MASTER LEDtube 1200mm UO 16W 830 T8 G I	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001923502	MASTER LEDtube 1200mm UO 16W 840 T8 G	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001923602	MASTER LEDtube 1200mm UO 16W 865 T8 G	45 °C	-20 °C	55 °C	65 °C	-40 °C
929001923702	MASTER LEDtube 1500mm UO 24W 830 T8 G	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001923732	MASTER LEDtube 1500mm UO 24W 830 T8 G I	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001923802	MASTER LEDtube 1500mm UO 24W 840 T8 G	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001923902	MASTER LEDtube 1500mm UO 24W 865 T8 G	45 °C	-20 °C	60 °C	65 °C	-40 °C
929001961102	MASTER LEDtube 1050mm 16W 840 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929002329702	MASTER LEDtube DC72-110V 1200mm 18W 840 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C
929002329802	MASTER LEDtube DC72-110V 450mm 6W 840 T8	45 °C	-20 °C	55 °C	65 °C	-40 °C



MASTER LEDtube EM/Mains T8



MASTER LEDtube EM/Mains T8

