



The new generation of energy saving tube lighting

MASTER LEDtube InstantFit HF T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Benefits

- Reduced operational cost thanks to lower energy consumption
- Reduced operational cost thanks to lower energy consumption
- Lower maintenance cost thanks to 2-3 times longer lifetime than normal fluorescent tubes
- Lower maintenance cost thanks to 2-3 times longer lifetime than normal fluorescent tubes
- Fastest and easiest way to upgrade existing luminaire to LED technology; 100%-safe installation process
- Fastest and easiest way to upgrade existing luminaire to LED technology; 100%-safe installation process

Features

- Only 50% energy consumption compared to fluorescent tubes
- Only 50% energy consumption compared to fluorescent tubes
- Extra-long life of 50,000 hours
- Extra-long life of 50,000 hours
- Retrofit to existing T8 lamps on HF ballast installations
- Retrofit to existing T8 lamps on EM ballast installations
- No mercury
- Full safety features and EM Protector safety device
- No mercury

MASTER LEDtube InstantFit HF T8

Application

- Parking lots / covered car parks
- Parking lots / covered car parks
- Warehouses / coldrooms / signage
- Warehouses / coldrooms / signage
- Transport and distribution areas
- Transport and distribution areas

Warnings and Safety

- NOTES: The overall energy efficiency and light distribution of any installation that uses these lamps are determined by the design of the installation.

