



MASTER LEDbulb – Elegance meets efficiency

MASTER Plastic LEDbulbs

The MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. They are particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimizes maintenance cost without any compromise on light quality. They can be used together with most leading-edge dimmers, enabling further efficiencies while helping to create the desired atmosphere.

Benefits

- Up to 80% energy saving compared with traditional incandescent lamps
- Easy (retrofit) replacement
- Lower maintenance costs

Features

- Dimmable
- Compatible with an extensive range of dimmers
- Warm white light
- Lifetime of 25,000 to 45,000 hours
- UV- and IR-free light

Application

- Hotels, restaurants, bars, cafés
- Lobbies, corridors, stairwells, reception areas

MASTER Plastic LEDbulbs

Warnings and Safety


- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Versions



LEDbulb MAS SLR1 A60 E27 CL 1

Dimensional drawing



Product	D	C
MAS LEDbulb DT 8-60W E27 A60 CL	60.5 mm	110 mm



MASTER Plastic LEDbulbs

