



Your idea bulb with the best performance

MASTER Plastic LEDbulbs

The MASTER Plastic LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to incandescent lamps. They are particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of incandescent bulbs, MASTER Plastic LEDbulb delivers huge energy savings of up to 80% compared with traditional incandescent lamps and provides excellent quality of light. By offering a lifetime of 25,000 hours it lowers maintenance costs. They can be used together with most leading-edge dimmers, enabling further efficiencies while helping to create the desired atmosphere.

Benefits

- Easy (retrofit) replacement ideal for general lighting applications
- Unique design and light effect that mimics the light quality of incandescent lamps
- \cdot Up to 80% energy saving compared with traditional incandescent lamps

Features

- The gradual dimming feature enables light levels to dim to warm tones of traditional lamps
- · Dimmable range that is compatible with an extensive range of dimmers
- · Lifetime of 25,000 hours
- · UV- and IR-free light

Application

- ${}^{\centerdot} \text{ Hotels, restaurants, bars, caf\'es}$
- · Lobbies, corridors, stairwells, reception areas

MASTER Plastic LEDbulbs

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- · Not intended for use with emergency light fixtures or exit lights

Versions









LEDbulb MAS SLR1 A60 B22 CL 1

Dimensional drawing





| Product | D | С |
|------------------------------------|---------|--------|
| MAS LEDbulb DT 8-60W B22 A60 CL UK | 60.5 mm | 110 mm |

| Product | D | С |
|------------------------------------|---------|--------|
| MAS LEDbulb DT 5.5-40W E27 A60 CL | 60.5 mm | 109 mm |
| MAS LEDbulb DT 8-60W E27 A60 CL | 60.5 mm | 110 mm |
| MAS LEDbulb DT 8-60W E27 A60 CL | 60.5 mm | 110 mm |
| MAS LEDbulb DT 8-60W E27 A60 CL UK | 60.5 mm | 110 mm |

MASTER Plastic LEDbulbs

| General Information | |
|------------------------------------|----------------|
| Switching Cycle | 50,000 |
| Nominal lifetime | 25,000 hour(s) |
| | |
| Light Technical | |
| Correlated Color Temperature (Nom) | 2200 K |
| Color rendering index (CRI) | 80 |
| Color Code | 822-827 |
| LLMF At End Of Nominal Lifetime | 70 % |
| (Nom) | |
| | |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |
| Line Frequency | 50 to 60 Hz |
| Starting Time (Nom) | 0.5 s |
| | |
| Temperature | |
| T-Case Maximum (Nom) | 80 °C |
| | |
| Management and Discourse | |
| Mechanical and Housing | |
| Bulb Finish | Clear |

General Information

| Order Code | Full Product Name | Cap-Base |
|--------------|------------------------------------|----------|
| 929002490002 | MAS LEDbulb DT 5.5-40W E27 A60 CL | E27 |
| 929002490399 | MAS LEDbulb DT 8-60W B22 A60 CL UK | B22 |
| 929002490221 | MAS LEDbulb DT 8-60W E27 A60 CL | E27 |
| 929002490232 | MAS LEDbulb DT 8-60W E27 A60 CL | E27 |
| 929002490299 | MAS LEDbulb DT 8-60W E27 A60 CL UK | E27 |

Light Technical

| Order Code | Full Product Name | Luminous Flux |
|--------------|------------------------------------|---------------|
| 929002490002 | MAS LEDbulb DT 5.5-40W E27 A60 CL | 470 lm |
| 929002490399 | MAS LEDbulb DT 8-60W B22 A60 CL UK | 806 lm |
| 929002490221 | MAS LEDbulb DT 8-60W E27 A60 CL | 806 lm |

| Order Code | Full Product Name | Luminous Flux |
|--------------|------------------------------------|---------------|
| 929002490232 | MAS LEDbulb DT 8-60W E27 A60 CL | 806 lm |
| 929002490299 | MAS LEDbulb DT 8-60W E27 A60 CL UK | 806 lm |
| | | |

Operating and Electrical

| | | Power | Wattage |
|--------------|--------------------------|-------------|------------|
| Order Code | Full Product Name | Consumption | Equivalent |
| 929002490002 | MAS LEDbulb DT 5.5-40W | 5.5 W | 40 W |
| | E27 A60 CL | | |
| 929002490399 | MAS LEDbulb DT 8-60W B22 | 8 W | 60 W |
| | A60 CL UK | | |
| 929002490221 | MAS LEDbulb DT 8-60W E27 | 8 W | 60 W |
| | A60 CL | | |

| | | Power | Wattage |
|--------------|--------------------------|-------------|------------|
| Order Code | Full Product Name | Consumption | Equivalent |
| 929002490232 | MAS LEDbulb DT 8-60W E27 | 8 W | 60 W |
| | A60 CL | | |
| 929002490299 | MAS LEDbulb DT 8-60W E27 | 8 W | 60 W |
| | A60 CL UK | | |
| | | | |

Temperature

| Order Code | Full Product Name | Ambient temperature range |
|--------------|------------------------------------|---------------------------|
| 929002490002 | MAS LEDbulb DT 5.5-40W E27 A60 CL | - |
| 929002490399 | MAS LEDbulb DT 8-60W B22 A60 CL UK | - |
| 929002490221 | MAS LEDbulb DT 8-60W E27 A60 CL | -20 °C to 45 °C |

| Order Code | Full Product Name | Ambient temperature range |
|--------------|------------------------------------|---------------------------|
| 929002490232 | MAS LEDbulb DT 8-60W E27 A60 CL | - |
| 929002490299 | MAS LEDbulb DT 8-60W E27 A60 CL UK | - |

Controls and Dimming

| Order Code | Full Product Name | Dimmable |
|--------------|-----------------------------------|----------------------------|
| 929002490002 | MAS LEDbulb DT 5.5-40W E27 A60 CL | Only with specific dimmers |

| Order Code | Full Product Name | Dimmable |
|--------------|------------------------------------|----------|
| 929002490399 | MAS LEDbulb DT 8-60W B22 A60 CL UK | Yes |


MASTER Plastic LEDbulbs


| Order Code | Full Product Name | Dimmable |
|--------------|---------------------------------|----------------------------|
| 929002490221 | MAS LEDbulb DT 8-60W E27 A60 CL | Only with specific dimmers |
| 929002490232 | MAS LEDbulb DT 8-60W E27 A60 CL | Only with specific dimmers |

| Order Code | Full Product Name | Dimmable |
|--------------|------------------------------------|----------|
| 929002490299 | MAS LEDbulb DT 8-60W E27 A60 CL UK | Yes |

Approval and Application

| | | Energy Consumption kWh/ |
|--------------|------------------------------------|-------------------------|
| Order Code | Full Product Name | 1000 h |
| 929002490002 | MAS LEDbulb DT 5.5-40W E27 A60 CL | 6 kWh |
| 929002490399 | MAS LEDbulb DT 8-60W B22 A60 CL UK | 8 kWh |
| 929002490221 | MAS LEDbulb DT 8-60W E27 A60 CL | - |
| 929002490232 | MAS LEDbulb DT 8-60W E27 A60 CL | 8 kWh |
| 929002490299 | MAS LEDbulb DT 8-60W E27 A60 CL UK | 8 kWh |







© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.