

Eleganța întâlnește eficiența

MASTER LEDbulb

Gama MASTER LEDbulb oferă un efect de reglare a intensității incandescenței pentru o atmosferă primitoare, caldă, ceea ce o face ideală pentru aplicații de iluminat general în industria hotelieră. Designul unic radiază lumină caldă în toate direcțiile, oferind o adevărată alternativă pentru lămpile cu incandescență. Aceste lămpi sunt adecvate în special pentru zonele publice, cum ar fi holurile, coridoarele, casa scârilor, unde lumina este permanent aprinsă. Compatibile cu corpurile de iluminat existente cu dulie de tip E27 și concepute pentru înlocuirea pe vechile instalații a becurilor incandescente, MASTER LEDbulb oferă economii uriașe de energie și minimizează costurile de întreținere, fără niciun compromis în privința calității luminii. Pot fi folosite împreună cu cele mai multe variatoare „leading edge”, asigurând un randament și mai mare și în același timp ajutând la crearea atmosferei dorite.

Beneficii

Caracteristici

Cerere



Warnings and safety

MASTER LEDbulb

Versions



Cote






Product	D	C
MASTERLEDbulb DT 14-100WE27 927-922 A67FR	77 mm	142 mm

Product	D	C
MASTER LED bulb DT 5.5-40WE27 927-922 A60FR	60 mm	110 mm
MASTER LEDbulb DT 8.5-60W E27 A60 CL	60 mm	110 mm

MASTER LEDbulb

Cote



Product	D	C
MASTER LED bulb DT 9-60W E27 927-922 A60 FR	60 mm	110 mm

Product
MASTER LEDbulb DT 6-40W B22 A60 CL

Product
MASTER LEDbulb DT 6-40W E27 A60 CL

Product	D	C
MASTER LED bulb DT 12-75WE27 927-922 A67 FR	77 mm	142 mm

MASTER LEDbulb

Approval and Application

Etichetă de eficiență energetică (EEL) A+

Controls and Dimming

Cu reglarea intensității luminoase Da

Operating and Electrical

Frecvență de intrare De la 50 până la
60 Hz

Tensiune (nom.) 220-240 V

General Information

Durată de viață nominală (nom.) 25000 h

Light Technical

Factorul de menținere a fluxului
luminos al lămpii la sfârșitul duratei de
viață nominale (nom.) 70 %

Approval and Application

Order Code	Full Product Name	Consum de energie kWh/1000 h
48130100	MASTER LEDbulb DT 6-40W B22 A60 CL	6 kWh
48128800	MASTER LEDbulb DT 6-40W E27 A60 CL	6 kWh
48132500	MASTER LEDbulb DT 8.5-60W E27 A60 CL	9 kWh
70709800	MASTER LED bulb DT 5.5-40WE27 927-922 A60FR	6 kWh

Order Code	Full Product Name	Consum de energie kWh/1000 h
70711100	MASTER LED bulb DT 9-60W E27 927-922 A60 FR	9 kWh
82618800	MASTER LED bulb DT 12-75WE27 927-922 A67 FR	12 kWh
69564400	MASTERLEDbulb DT 14-100WE27 927-922 A67FR	14 kWh

Operating and Electrical

Order Code	Full Product Name	Echivalent putere	Putere (Evaluată) (nom.)	Timp de pornire (nom.)
48130100	MASTER LEDbulb DT 6-40W B22 A60 CL	40 W	6 W	0,5 s
48128800	MASTER LEDbulb DT 6-40W E27 A60 CL	40 W	6 W	0,5 s
48132500	MASTER LEDbulb DT 8.5-60W E27 A60 CL	60 W	8,5 W	0,5 s
70709800	MASTER LED bulb DT 5.5-40WE27 927-922 A60FR	40 W	5,5 W	0,3 s

Order Code	Full Product Name	Echivalent putere	Putere (Evaluată) (nom.)	Timp de pornire (nom.)
70711100	MASTER LED bulb DT 9-60W E27 927-922 A60 FR	60 W	9 W	0,3 s
82618800	MASTER LED bulb DT 12-75WE27 927-922 A67 FR	75 W	12 W	0,1 s
69564400	MASTERLEDbulb DT 14-100WE27 927-922 A67FR	100 W	14 W	0,5 s

General Information

Order Code	Full Product Name	Baza elementului de fixare	Ciclu de comutare
48130100	MASTER LEDbulb DT 6-40W B22 A60 CL	B22	50000X
48128800	MASTER LEDbulb DT 6-40W E27 A60 CL	E27	50000X
48132500	MASTER LEDbulb DT 8.5-60W E27 A60 CL	E27	50000X
70709800	MASTER LED bulb DT 5.5-40WE27 927-922 A60FR	E27	100000X

Order Code	Full Product Name	Baza elementului de fixare	Ciclu de comutare
70711100	MASTER LED bulb DT 9-60W E27 927-922 A60 FR	E27	100000X
82618800	MASTER LED bulb DT 12-75WE27 927-922 A67 FR	E27	100000X

MASTER LEDbulb

Order Code	Full Product Name	Baza elementului de fixare	Ciclu de comutare
69564400	MASTERLEDbulb DT 14-100WE27 927-922 A67FR	E27	100000X

Light Technical

Order Code	Full Product Name	Unghi de distribu ie luminoasă (nom.)	Cod culoare	Indice de redare a culorii (nom.)	Flux luminos (nom.)
48130100	MASTER LEDbulb DT 6-40W B22 A60 CL	-	822-827	80	470 lm
48128800	MASTER LEDbulb DT 6-40W E27 A60 CL	-	822-827	80	470 lm
48132500	MASTER LEDbulb DT 8.5-60W E27 A60 CL	-	822-827	80	806 lm
70709800	MASTER LED bulb DT 5.5-40WE27 927-922 A60FR	200 °	922-927	90	470 lm

Order Code	Full Product Name	Unghi de distribu ie luminoasă (nom.)	Cod culoare	Indice de redare a culorii (nom.)	Flux luminos (nom.)
70711100	MASTER LED bulb DT 9-60W E27 927-922 A60 FR	200 °	922-927	90	806 lm
82618800	MASTER LED bulb DT 12-75WE27 927-922 A67 FR	200 °	922-927	90	1055 lm
69564400	MASTERLEDbulb DT 14-100WE27 927-922 A67FR	200 °	922-927	90	1521 lm

Mechanical and Housing

Order Code	Full Product Name	Finisaj bec	Formă bec
48130100	MASTER LEDbulb DT 6-40W B22 A60 CL	Clar	A60
48128800	MASTER LEDbulb DT 6-40W E27 A60 CL	Clar	A60
48132500	MASTER LEDbulb DT 8.5-60W E27 A60 CL	Clar	A60
70709800	MASTER LED bulb DT 5.5-40WE27 927-922 A60FR	Mat	A60

Order Code	Full Product Name	Finisaj bec	Formă bec
70711100	MASTER LED bulb DT 9-60W E27 927-922 A60 FR	Mat	A60
82618800	MASTER LED bulb DT 12-75WE27 927-922 A67 FR	Mat	A67
69564400	MASTERLEDbulb DT 14-100WE27 927-922 A67FR	Mat	A67

Temperature

Order Code	Full Product Name	Maximum T-case (nom.)
48130100	MASTER LEDbulb DT 6-40W B22 A60 CL	85 °C
48128800	MASTER LEDbulb DT 6-40W E27 A60 CL	85 °C
48132500	MASTER LEDbulb DT 8.5-60W E27 A60 CL	110 °C
70709800	MASTER LED bulb DT 5.5-40WE27 927-922 A60FR	70 °C
70711100	MASTER LED bulb DT 9-60W E27 927-922 A60 FR	85 °C
82618800	MASTER LED bulb DT 12-75WE27 927-922 A67 FR	80 °C
69564400	MASTERLEDbulb DT 14-100WE27 927-922 A67FR	90 °C



MASTER LEDbulb

