



# The energy-saving alternative for lighting in public areas

## MASTER LEDspot PAR

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on.

### Benefits

- Up to 80% energy saving compared to halogen lamps
- Retrofittable and compatible with existing fixtures with E27 holder
- Lower maintenance costs

### Features

- Lifetime of 45,000 hours
- Dimmable (except PAR38 OD)
- UV- and IR-free light for less heat and protection for heat-sensitive objects
- Free of mercury and hazardous materials – RoHS compliant

### Application


- Hotels, restaurants, bars, cafés, museums, shops, musea, art. galleries, lobbies, corridors, stairwells, washrooms, reception areas, exhibitions, display cabinets

# MASTER LEDspot PAR


## Versions




E27 PAR20




E27 PAR38




E27 PAR30S



LEDspot E27 PAR30s




LEDspot E27 PAR30L




LEDspot E27 PAR20

# MASTER LEDspot PAR

## Dimensional drawing







Product	D	C
Master LED PAR30L 40W 30D 840	95.5 mm	129 mm
Master LED PAR30L 40W 15D 857	95.5 mm	129 mm
Master LED PAR30L 40W 30D 857	95.5 mm	129 mm
Master LED PAR30L 40W 30D 827	95.5 mm	129 mm
Master LED PAR30L 40W 15D 827	95.5 mm	129 mm
Master LED PAR30L 40W 15D 830	95.5 mm	129 mm
Master LED PAR30L 40W 30D 830	95.5 mm	129 mm
MAS LED spot ND 20W PAR30L E27 830 15D	95.5 mm	129 mm
MAS LED spot ND 37W PAR30L E27 830 15D	95.5 mm	129 mm
MAS LED spot ND 20W PAR30L E27 830 30D	95.5 mm	129 mm
MAS LED spot ND 37W PAR30L E27 827 15D	95.5 mm	129 mm
Master LED PAR30L 32W 30D 857	95.5 mm	129 mm
Master LED PAR30L 32W 30D 840	95.5 mm	129 mm
Master LED PAR30L 32W 30D 840 CN	95.5 mm	129 mm
Master LED PAR30L 32W 30D 860 CN	95.5 mm	129 mm
Master LED PAR30L 40W 30D 830 CN	95.5 mm	129 mm
Master LED PAR30L 40W 30D 827 CN	95.5 mm	129 mm
Master LED PAR30L 40W 15D 830 CN	95.5 mm	129 mm
Master LED PAR30L 40W 15D 827 CN	95.5 mm	129 mm
Master LED PAR30L 40W 15D 840 CN	95.5 mm	129 mm
Master LED PAR30L 40W 30D 840 CN	95.5 mm	129 mm
Master LED PAR30L 40W 30D 860 CN	95.5 mm	129 mm
Master LED PAR30L 40W 15D 860 CN	95.5 mm	129 mm
Master LED PAR30L 28W 15D 840 100-277V	95.5 mm	129 mm
Master LED PAR30L 28W 30D 840 100-277V	95.5 mm	129 mm
Master LED PAR30L 28W 15D 830 100-277V	95.5 mm	129 mm
Master LED PAR30L 28W 30D 830 100-277V	95.5 mm	129 mm
MAS LED spot ND 41W PAR30L E27 830 30D	95.5 mm	129 mm
MAS LED spot ND 41W PAR30L E27 827 30D	95.5 mm	129 mm
Master LED PAR30L 40W 15D 840	95.5 mm	129 mm



Product	D	C
MAS LEDspot D 6-50W E27 827 PAR20 25D	64 mm	85 mm
MAS LEDspot CLA D 6-50W 840 PAR20 40D	64 mm	85 mm
MAS LEDspot CLA D 6-50W 827 PAR20 40D	64 mm	85 mm
MAS LEDspot CLA D 6-50W 830 PAR20 25D	64 mm	85 mm
MAS LEDspot CLA D 6-50W 840 PAR20 25D	64 mm	85 mm
MAS LEDspot CLA D 6-50W 827 PAR20 25D	64 mm	85 mm
MAS LEDspot CLA D 6-50W 830 PAR20 40D	64 mm	85 mm

# MASTER LEDspot PAR

## Dimensional drawing



Product	D	C
MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D	95 mm	86 mm
MAS LEDspot CLA D 9.5-75W 827 PAR30S 25D	95 mm	86 mm
MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D	95 mm	86 mm
MAS LEDspot D 9-70W E27 927 PAR30S 25D	95 mm	86 mm

Product	D	C
MAS LEDspot CLA ND 9-60W 827 PAR38 25D	122 mm	134 mm
MAS LEDspot CLA D 13-100W 827 PAR38 25D	122 mm	134 mm
MAS LEDspot D 13-100W E27 927 PAR38 25D	122 mm	134 mm

Product	D	C
LEDspot 90W PAR30S 830 100-277V 25D ND	93 mm	91 mm

Product	D	C
LEDspot 50W PAR20 2700K WV 25D ND SO	63 mm	89 mm

# MASTER LEDspot PAR

## Operating and Electrical

Starting Time (Nom) 0.5 s

## General Information

Cap-Base E27

## Light Technical

Llmf At End Of Nominal Lifetime (Nom) 70 %

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001317402	MAS LEDspot CLA D 6-50W 827 PAR20 25D	6 kWh	A+
929001317408	MAS LEDspot D 6-50W E27 827 PAR20 25D	6 kWh	A+
929001317502	MAS LEDspot CLA D 6-50W 830 PAR20 25D	6 kWh	A+
929001317602	MAS LEDspot CLA D 6-50W 840 PAR20 25D	6 kWh	A+
929001317702	MAS LEDspot CLA D 6-50W 827 PAR20 40D	6 kWh	A+
929001317802	MAS LEDspot CLA D 6-50W 830 PAR20 40D	6 kWh	A+
929001317902	MAS LEDspot CLA D 6-50W 840 PAR20 40D	6 kWh	A+
929001322502	MAS LEDspot CLA D 13-100W 827 PAR38 25D	13 kWh	A+
929001322508	MAS LEDspot D 13-100W E27 927 PAR38 25D	13 kWh	A+
929001322702	MAS LEDspot CLA ND 9-60W 827 PAR38 25D	9 kWh	A+
929001322902	MAS LEDspot CLA D 9.5-75W 827 PAR30S 25D	10 kWh	A+
929001323002	MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D	10 kWh	A+
929001323108	MAS LEDspot D 9-70W E27 927 PAR30S 25D	9 kWh	A+
929001342902	MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D	10 kWh	A+
929001343912	LEDspot 90W PAR30S 830 100-277V 25D ND	-	-
929001353802	MAS LED spot ND 20W PAR30L E27 830 15D	20 kWh	A+
929001354002	MAS LED spot ND 20W PAR30L E27 830 30D	20 kWh	A+
929001354808	Master LED PAR30L 32W 30D 840	32 kWh	A+
929001354810	Master LED PAR30L 32W 30D 840 CN	32 kWh	A+

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001354908	Master LED PAR30L 32W 30D 857	32 kWh	A+
929001354910	Master LED PAR30L 32W 30D 860 CN	32 kWh	A+
929001374302	MAS LED spot ND 37W PAR30L E27 827 15D	37 kWh	A+
929001374308	Master LED PAR30L 40W 15D 827	40 kWh	A+
929001374310	Master LED PAR30L 40W 15D 827 CN	40 kWh	A+
929001374402	MAS LED spot ND 37W PAR30L E27 830 15D	37 kWh	A+
929001374408	Master LED PAR30L 40W 15D 830	40 kWh	A+
929001374410	Master LED PAR30L 40W 15D 830 CN	40 kWh	A+
929001374508	Master LED PAR30L 40W 15D 840	40 kWh	A+
929001374510	Master LED PAR30L 40W 15D 840 CN	40 kWh	A+
929001374608	Master LED PAR30L 40W 15D 857	40 kWh	A+
929001374610	Master LED PAR30L 40W 15D 860 CN	40 kWh	A+
929001374702	MAS LED spot ND 41W PAR30L E27 827 30D	41 kWh	A+
929001374708	Master LED PAR30L 40W 30D 827	40 kWh	A+
929001374710	Master LED PAR30L 40W 30D 827 CN	40 kWh	A+
929001374802	MAS LED spot ND 41W PAR30L E27 830 30D	41 kWh	A+
929001374808	Master LED PAR30L 40W 30D 830	40 kWh	A+
929001374810	Master LED PAR30L 40W 30D 830 CN	40 kWh	A+
929001374908	Master LED PAR30L 40W 30D 840	40 kWh	A+

# MASTER LEDspot PAR

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001374910	Master LED PAR30L 40W 30D 840 CN	40 kWh	A+
929001375008	Master LED PAR30L 40W 30D 857	40 kWh	A+
929001375010	Master LED PAR30L 40W 30D 860 CN	40 kWh	A+
929001941912	Master LED PAR30L 28W 15D 830 100-277V	-	-

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001942012	Master LED PAR30L 28W 30D 830 100-277V	-	-
929001942112	Master LED PAR30L 28W 15D 840 100-277V	-	-
929001942212	Master LED PAR30L 28W 30D 840 100-277V	-	-
929001358112	LEDspot 50W PAR20 2700K WV 25D ND SO	-	-

## Controls and Dimming

Order Code	Full Product Name	Dimmable
929001317402	MAS LEDspot CLA D 6-50W 827 PAR20 25D	Yes
929001317408	MAS LEDspot D 6-50W E27 827 PAR20 25D	Yes
929001317502	MAS LEDspot CLA D 6-50W 830 PAR20 25D	Yes
929001317602	MAS LEDspot CLA D 6-50W 840 PAR20 25D	Yes
929001317702	MAS LEDspot CLA D 6-50W 827 PAR20 40D	Yes
929001317802	MAS LEDspot CLA D 6-50W 830 PAR20 40D	Yes
929001317902	MAS LEDspot CLA D 6-50W 840 PAR20 40D	Yes
929001322502	MAS LEDspot CLA D 13-100W 827 PAR38 25D	Yes
929001322508	MAS LEDspot D 13-100W E27 927 PAR38 25D	Yes
929001322702	MAS LEDspot CLA ND 9-60W 827 PAR38 25D	No
929001322902	MAS LEDspot CLA D 9.5-75W 827 PAR30S 25D	Yes
929001323002	MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D	Yes
929001323108	MAS LEDspot D 9-70W E27 927 PAR30S 25D	Yes
929001342902	MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D	Yes
929001343912	LEDspot 90W PAR30S 830 100-277V 25D ND	No
929001353802	MAS LED spot ND 20W PAR30L E27 830 15D	No
929001354002	MAS LED spot ND 20W PAR30L E27 830 30D	No
929001354808	Master LED PAR30L 32W 30D 840	No
929001354810	Master LED PAR30L 32W 30D 840 CN	No
929001354908	Master LED PAR30L 32W 30D 857	No
929001354910	Master LED PAR30L 32W 30D 860 CN	No
929001374302	MAS LED spot ND 37W PAR30L E27 827 15D	No
929001374308	Master LED PAR30L 40W 15D 827	No

Order Code	Full Product Name	Dimmable
929001374310	Master LED PAR30L 40W 15D 827 CN	No
929001374402	MAS LED spot ND 37W PAR30L E27 830 15D	No
929001374408	Master LED PAR30L 40W 15D 830	No
929001374410	Master LED PAR30L 40W 15D 830 CN	No
929001374508	Master LED PAR30L 40W 15D 840	No
929001374510	Master LED PAR30L 40W 15D 840 CN	No
929001374608	Master LED PAR30L 40W 15D 857	No
929001374610	Master LED PAR30L 40W 15D 860 CN	No
929001374702	MAS LED spot ND 41W PAR30L E27 827 30D	No
929001374708	Master LED PAR30L 40W 30D 827	No
929001374710	Master LED PAR30L 40W 30D 827 CN	No
929001374802	MAS LED spot ND 41W PAR30L E27 830 30D	No
929001374808	Master LED PAR30L 40W 30D 830	No
929001374810	Master LED PAR30L 40W 30D 830 CN	No
929001374908	Master LED PAR30L 40W 30D 840	No
929001374910	Master LED PAR30L 40W 30D 840 CN	No
929001375008	Master LED PAR30L 40W 30D 857	No
929001375010	Master LED PAR30L 40W 30D 860 CN	No
929001941912	Master LED PAR30L 28W 15D 830 100-277V	No
929001942012	Master LED PAR30L 28W 30D 830 100-277V	No
929001942112	Master LED PAR30L 28W 15D 840 100-277V	No
929001942212	Master LED PAR30L 28W 30D 840 100-277V	No
929001358112	LEDspot 50W PAR20 2700K WV 25D ND SO	No

## Operating and Electrical

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated)
929001317402	MAS LEDspot CLA D 6-50W 827 PAR20 25D	50 Hz	220-240 V	50 W	6 W
929001317408	MAS LEDspot D 6-50W E27 827 PAR20 25D	50 to 60 Hz	220-240 V	50 W	6 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated)
929001317502	MAS LEDspot CLA D 6-50W 830 PAR20 25D	50 Hz	220-240 V	50 W	6 W
929001317602	MAS LEDspot CLA D 6-50W 840 PAR20 25D	50 Hz	220-240 V	50 W	6 W

## MASTER LEDspot PAR

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001317702	MAS LEDspot CLA D 6-50W 827 PAR20 40D	50 Hz	220-240 V	50 W	6 W
929001317802	MAS LEDspot CLA D 6-50W 830 PAR20 40D	50 Hz	220-240 V	50 W	6 W
929001317902	MAS LEDspot CLA D 6-50W 840 PAR20 40D	50 Hz	220-240 V	50 W	6 W
929001322502	MAS LEDspot CLA D 13-100W 827 PAR38 25D	50 Hz	220-240 V	100 W	13 W
929001322508	MAS LEDspot D 13-100W E27 927 PAR38 25D	50 to 60 Hz	220-240 V	100 W	13 W
929001322702	MAS LEDspot CLA ND 9-60W 827 PAR38 25D	50 Hz	220-240 V	60 W	9 W
929001322902	MAS LEDspot CLA D 9.5-75W 827 PAR30S 25D	50 Hz	220-240 V	75 W	9.5 W
929001323002	MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D	50 Hz	220-240 V	75 W	9.5 W
929001323108	MAS LEDspot D 9-70W E27 927 PAR30S 25D	50 to 60 Hz	220-240 V	70 W	9 W
929001342902	MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D	50 Hz	220-240 V	75 W	9.5 W
929001343912	LEDspot 90W PAR30S 830 100-277V 25D ND	50 to 60 Hz	100-277 V	75 W	9 W
929001353802	MAS LED spot ND 20W PAR30L E27 830 15D	50 to 60 Hz	220-240 V	35 W	20 W
929001354002	MAS LED spot ND 20W PAR30L E27 830 30D	50 to 60 Hz	220-240 V	35 W	20 W
929001354808	Master LED PAR30L 32W 30D 840	50 to 60 Hz	220-240 V	50 W	32 W
929001354810	Master LED PAR30L 32W 30D 840 CN	50 to 60 Hz	220-240 V	50 W	32 W
929001354908	Master LED PAR30L 32W 30D 857	50 to 60 Hz	220-240 V	50 W	32 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001354910	Master LED PAR30L 32W 30D 860 CN	50 to 60 Hz	220-240 V	50 W	32 W
929001374302	MAS LED spot ND 37W PAR30L E27 827 15D	50 to 60 Hz	220-240 V	70 W	37 W
929001374308	Master LED PAR30L 40W 15D 827	50 to 60 Hz	220-240 V	70 W	40 W
929001374310	Master LED PAR30L 40W 15D 827 CN	50 to 60 Hz	220-240 V	70 W	40 W
929001374402	MAS LED spot ND 37W PAR30L E27 830 15D	50 to 60 Hz	220-240 V	70 W	37 W
929001374408	Master LED PAR30L 40W 15D 830	50 to 60 Hz	220-240 V	70 W	40 W
929001374410	Master LED PAR30L 40W 15D 830 CN	50 to 60 Hz	220-240 V	70 W	40 W
929001374508	Master LED PAR30L 40W 15D 840	50 to 60 Hz	220-240 V	70 W	40 W
929001374510	Master LED PAR30L 40W 15D 840 CN	50 to 60 Hz	220-240 V	70 W	40 W
929001374608	Master LED PAR30L 40W 15D 857	50 to 60 Hz	220-240 V	70 W	40 W
929001374610	Master LED PAR30L 40W 15D 860 CN	50 to 60 Hz	220-240 V	70 W	40 W
929001374702	MAS LED spot ND 41W PAR30L E27 827 30D	50 to 60 Hz	220-240 V	70 W	41 W
929001374708	Master LED PAR30L 40W 30D 827	50 to 60 Hz	220-240 V	70 W	40 W
929001374710	Master LED PAR30L 40W 30D 827 CN	50 to 60 Hz	220-240 V	70 W	40 W
929001374802	MAS LED spot ND 41W PAR30L E27 830 30D	50 to 60 Hz	220-240 V	70 W	41 W
929001374808	Master LED PAR30L 40W 30D 830	50 to 60 Hz	220-240 V	70 W	40 W

## MASTER LEDspot PAR

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001374810	Master LED PAR30L 40W 30D 830 CN	50 to 60 Hz	220-240 V	70 W	40 W
929001374908	Master LED PAR30L 40W 30D 840	50 to 60 Hz	220-240 V	70 W	40 W
929001374910	Master LED PAR30L 40W 30D 840 CN	50 to 60 Hz	220-240 V	70 W	40 W
929001375008	Master LED PAR30L 40W 30D 857	50 to 60 Hz	220-240 V	70 W	40 W
929001375010	Master LED PAR30L 40W 30D 860 CN	50 to 60 Hz	220-240 V	70 W	40 W
929001941912	Master LED PAR30L 28W 15D 830 100-277V	50 to 60 Hz	100-277 V	50 W	28 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001942012	Master LED PAR30L 28W 30D 830 100-277V	50 to 60 Hz	100-277 V	50 W	28 W
929001942112	Master LED PAR30L 28W 15D 840 100-277V	50 to 60 Hz	100-277 V	50 W	28 W
929001942212	Master LED PAR30L 28W 30D 840 100-277V	50 to 60 Hz	100-277 V	50 W	28 W
929001358112	LEDspot 50W PAR20 2700K WV 25D ND SO	50 to 60 Hz	100-240 V	50 W	6.5 W

### General Information

Order Code	Full Product Name	Nominal Lifetime (Nom)	Rated Lifetime (Hours)	Switching Cycle
929001317402	MAS LEDspot CLA D 6-50W 827 PAR20 25D	25000 h	25000 h	25000X
929001317408	MAS LEDspot D 6-50W E27 827 PAR20 25D	25000 h	25000 h	25000X
929001317502	MAS LEDspot CLA D 6-50W 830 PAR20 25D	25000 h	25000 h	25000X
929001317602	MAS LEDspot CLA D 6-50W 840 PAR20 25D	25000 h	25000 h	25000X
929001317702	MAS LEDspot CLA D 6-50W 827 PAR20 40D	25000 h	25000 h	25000X
929001317802	MAS LEDspot CLA D 6-50W 830 PAR20 40D	25000 h	25000 h	25000X
929001317902	MAS LEDspot CLA D 6-50W 840 PAR20 40D	25000 h	25000 h	25000X
929001322502	MAS LEDspot CLA D 13-100W 827 PAR38 25D	25000 h	25000 h	25000X
929001322508	MAS LEDspot D 13-100W E27 927 PAR38 25D	25000 h	25000 h	25000X
929001322702	MAS LEDspot CLA ND 9-60W 827 PAR38 25D	15000 h	15000 h	25000X
929001322902	MAS LEDspot CLA D 9.5-75W 827 PAR30S 25D	25000 h	25000 h	25000X
929001323002	MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D	25000 h	25000 h	25000X
929001323108	MAS LEDspot D 9-70W E27 927 PAR30S 25D	25000 h	25000 h	25000X

Order Code	Full Product Name	Nominal Lifetime (Nom)	Rated Lifetime (Hours)	Switching Cycle
929001342902	MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D	25000 h	25000 h	25000X
929001343912	LEDspot 90W PAR30S 830 100-277V 25D ND	25000 h	25000 h	25000X
929001353802	MAS LED spot ND 20W PAR30L E27 830 15D	25000 h	25000 h	50000X
929001354002	MAS LED spot ND 20W PAR30L E27 830 30D	25000 h	25000 h	50000X
929001354808	Master LED PAR30L 32W 30D 840	25000 h	25000 h	50000X
929001354810	Master LED PAR30L 32W 30D 840 CN	25000 h	25000 h	50000X
929001354908	Master LED PAR30L 32W 30D 857	25000 h	25000 h	50000X
929001354910	Master LED PAR30L 32W 30D 860 CN	25000 h	25000 h	50000X
929001374302	MAS LED spot ND 37W PAR30L E27 827 15D	25000 h	25000 h	50000X
929001374308	Master LED PAR30L 40W 15D 827	25000 h	25000 h	50000X
929001374310	Master LED PAR30L 40W 15D 827 CN	25000 h	25000 h	50000X
929001374402	MAS LED spot ND 37W PAR30L E27 830 15D	25000 h	25000 h	50000X
929001374408	Master LED PAR30L 40W 15D 830	25000 h	25000 h	50000X



## MASTER LEDspot PAR

Order Code	Full Product Name	Nominal Lifetime (Nom)	Rated Lifetime (Hours)	Switching Cycle	Order Code	Full Product Name	Nominal Lifetime (Nom)	Rated Lifetime (Hours)	Switching Cycle
929001374410	Master LED PAR30L 40W 15D 830 CN	25000 h	25000 h	50000X	929001374810	Master LED PAR30L 40W 30D 830 CN	25000 h	25000 h	50000X
929001374508	Master LED PAR30L 40W 15D 840	25000 h	25000 h	50000X	929001374908	Master LED PAR30L 40W 30D 840	25000 h	25000 h	50000X
929001374510	Master LED PAR30L 40W 15D 840 CN	25000 h	25000 h	50000X	929001374910	Master LED PAR30L 40W 30D 840 CN	25000 h	25000 h	50000X
929001374608	Master LED PAR30L 40W 15D 857	25000 h	25000 h	50000X	929001375008	Master LED PAR30L 40W 30D 857	25000 h	25000 h	50000X
929001374610	Master LED PAR30L 40W 15D 860 CN	25000 h	25000 h	50000X	929001375010	Master LED PAR30L 40W 30D 860 CN	25000 h	25000 h	50000X
929001374702	MAS LED spot ND 41W PAR30L E27 827 30D	25000 h	25000 h	50000X	929001941912	Master LED PAR30L 28W 15D 830 100-277V	25000 h	25000 h	50000X
929001374708	Master LED PAR30L 40W 30D 827	25000 h	25000 h	50000X	929001942012	Master LED PAR30L 28W 30D 830 100-277V	25000 h	25000 h	50000X
929001374710	Master LED PAR30L 40W 30D 827 CN	25000 h	25000 h	50000X	929001942112	Master LED PAR30L 28W 15D 840 100-277V	25000 h	25000 h	50000X
929001374802	MAS LED spot ND 41W PAR30L E27 830 30D	25000 h	25000 h	50000X	929001942212	Master LED PAR30L 28W 30D 840 100-277V	25000 h	25000 h	50000X
929001374808	Master LED PAR30L 40W 30D 830	25000 h	25000 h	50000X	929001358112	LEDspot 50W PAR20 2700K WV 25D ND SO	25000 h	25000 h	25000X

### Light Technical (1/2)

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color			
					Rendering Index (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)	Luminous Intensity (Nom)
929001317402	MAS LEDspot CLA D 6-50W 827 PAR20 25D	25 °	827	2700 K	80	500 lm	500 lm	1500 cd
929001317408	MAS LEDspot D 6-50W E27 827 PAR20 25D	25 °	827	2700 K	80	520 lm	520 lm	1500 cd
929001317502	MAS LEDspot CLA D 6-50W 830 PAR20 25D	25 °	830	3000 K	80	515 lm	515 lm	1500 cd
929001317602	MAS LEDspot CLA D 6-50W 840 PAR20 25D	25 °	840	4000 K	80	540 lm	540 lm	1500 cd
929001317702	MAS LEDspot CLA D 6-50W 827 PAR20 40D	40 °	827	2700 K	80	500 lm	500 lm	800 cd
929001317802	MAS LEDspot CLA D 6-50W 830 PAR20 40D	40 °	830	3000 K	80	515 lm	515 lm	800 cd
929001317902	MAS LEDspot CLA D 6-50W 840 PAR20 40D	40 °	840	4000 K	80	540 lm	540 lm	800 cd
929001322502	MAS LEDspot CLA D 13-100W 827 PAR38 25D	25 °	827	2700 K	80	875 lm	875 lm	4000 cd
929001322508	MAS LEDspot D 13-100W E27 927 PAR38 25D	25 °	927	2700 K	90	1000 lm	1000 lm	4000 cd
929001322702	MAS LEDspot CLA ND 9-60W 827 PAR38 25D	25 °	827	2700 K	80	750 lm	750 lm	1800 cd
929001322902	MAS LEDspot CLA D 9.5-75W 827 PAR30S 25D	25 °	827	2700 K	80	740 lm	740 lm	3500 cd
929001323002	MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D	25 °	840	4000 K	80	820 lm	820 lm	3500 cd

## MASTER LEDspot PAR

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color		Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)	Luminous Intensity (Nom)
					Rendering Index (Nom)				
929001323108	MAS LEDspot D 9-70W E27 927 PAR30S 25D	25 °	927	2700 K	90		630 lm	630 lm	3000 cd
929001342902	MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D	25 °	830	3000 K	80		760 lm	760 lm	3500 cd
929001343912	LEDspot 90W PAR30S 830 100-277V 25D ND	25 °	830	3000 K	80		950 lm	950 lm	3300 cd
929001353802	MAS LED spot ND 20W PAR30L E27 830 15D	15 °	830	3000 K	80		1700 lm	1700 lm	19000 cd
929001354002	MAS LED spot ND 20W PAR30L E27 830 30D	30 °	830	3000 K	80		1650 lm	1650 lm	7000 cd
929001354808	Master LED PAR30L 32W 30D 840	30 °	840	4000 K	82		3000 lm	3000 lm	9600 cd
929001354810	Master LED PAR30L 32W 30D 840 CN	30 °	840	4000 K	82		3000 lm	3000 lm	9600 cd
929001354908	Master LED PAR30L 32W 30D 857	30 °	857	5700 K	82		3000 lm	3000 lm	9600 cd
929001354910	Master LED PAR30L 32W 30D 860 CN	30 °	860	6000 K	82		3000 lm	3000 lm	9600 cd
929001374302	MAS LED spot ND 37W PAR30L E27 827 15D	15 °	827	2700 K	80		3500 lm	3500 lm	35000 cd
929001374308	Master LED PAR30L 40W 15D 827	15 °	827	2700 K	82		3850 lm	3850 lm	38500 cd
929001374310	Master LED PAR30L 40W 15D 827 CN	15 °	827	2700 K	82		3850 lm	3850 lm	38500 cd
929001374402	MAS LED spot ND 37W PAR30L E27 830 15D	15 °	830	3000 K	80		3600 lm	3600 lm	36000 cd
929001374408	Master LED PAR30L 40W 15D 830	15 °	830	3000 K	82		4000 lm	4000 lm	40000 cd
929001374410	Master LED PAR30L 40W 15D 830 CN	15 °	830	3000 K	82		4000 lm	4000 lm	40000 cd
929001374508	Master LED PAR30L 40W 15D 840	15 °	840	4000 K	82		4200 lm	4200 lm	42000 cd
929001374510	Master LED PAR30L 40W 15D 840 CN	15 °	840	4000 K	82		4200 lm	4200 lm	42000 cd
929001374608	Master LED PAR30L 40W 15D 857	15 °	857	5700 K	82		4200 lm	4200 lm	42000 cd
929001374610	Master LED PAR30L 40W 15D 860 CN	15 °	860	6000 K	82		4200 lm	4200 lm	42000 cd
929001374702	MAS LED spot ND 41W PAR30L E27 827 30D	30 °	827	2700 K	80		3900 lm	3900 lm	12500 cd
929001374708	Master LED PAR30L 40W 30D 827	30 °	827	2700 K	82		4300 lm	4300 lm	13000 cd
929001374710	Master LED PAR30L 40W 30D 827 CN	30 °	827	2700 K	82		4300 lm	4300 lm	13000 cd
929001374802	MAS LED spot ND 41W PAR30L E27 830 30D	30 °	830	3000 K	80		4000 lm	4000 lm	13000 cd
929001374808	Master LED PAR30L 40W 30D 830	30 °	830	3000 K	82		4500 lm	4500 lm	13500 cd
929001374810	Master LED PAR30L 40W 30D 830 CN	30 °	830	3000 K	82		4500 lm	4500 lm	13500 cd
929001374908	Master LED PAR30L 40W 30D 840	30 °	840	4000 K	82		4600 lm	4600 lm	14000 cd
929001374910	Master LED PAR30L 40W 30D 840 CN	30 °	840	4000 K	82		4600 lm	4600 lm	14000 cd
929001375008	Master LED PAR30L 40W 30D 857	30 °	857	5700 K	82		4600 lm	4600 lm	14000 cd
929001375010	Master LED PAR30L 40W 30D 860 CN	30 °	860	6000 K	82		4600 lm	4600 lm	14000 cd
929001941912	Master LED PAR30L 28W 15D 830 100-277V	15 °	830	3000 K	80		3000 lm	3000 lm	27000 cd
929001942012	Master LED PAR30L 28W 30D 830 100-277V	30 °	830	3000 K	80		3000 lm	3000 lm	9600 cd
929001942112	Master LED PAR30L 28W 15D 840 100-277V	15 °	840	4000 K	80		3000 lm	3000 lm	27000 cd
929001942212	Master LED PAR30L 28W 30D 840 100-277V	30 °	840	4000 K	80		3000 lm	3000 lm	9600 cd
929001358112	LEDspot 50W PAR20 2700K WV 25D ND SO	25 °	827	2700 K	80		525 lm	525 lm	1500 cd

### Light Technical (2/2)

# MASTER LEDspot PAR

Order Code	Full Product Name	Rated Beam Angle
929001317402	MAS LEDspot CLA D 6-50W 827 PAR20 25D	25 °
929001317408	MAS LEDspot D 6-50W E27 827 PAR20 25D	25 °
929001317502	MAS LEDspot CLA D 6-50W 830 PAR20 25D	25 °
929001317602	MAS LEDspot CLA D 6-50W 840 PAR20 25D	25 °
929001317702	MAS LEDspot CLA D 6-50W 827 PAR20 40D	40 °
929001317802	MAS LEDspot CLA D 6-50W 830 PAR20 40D	40 °
929001317902	MAS LEDspot CLA D 6-50W 840 PAR20 40D	40 °
929001322502	MAS LEDspot CLA D 13-100W 827 PAR38 25D	25 °
929001322508	MAS LEDspot D 13-100W E27 927 PAR38 25D	25 °
929001322702	MAS LEDspot CLA ND 9-60W 827 PAR38 25D	25 °
929001322902	MAS LEDspot CLA D 9.5-75W 827 PAR30S 25D	25 °
929001323002	MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D	25 °
929001323108	MAS LEDspot D 9-70W E27 927 PAR30S 25D	25 °
929001342902	MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D	25 °
929001343912	LEDspot 90W PAR30S 830 100-277V 25D ND	25 °
929001353802	MAS LED spot ND 20W PAR30L E27 830 15D	15 °
929001354002	MAS LED spot ND 20W PAR30L E27 830 30D	30 °
929001354808	Master LED PAR30L 32W 30D 840	30 °
929001354810	Master LED PAR30L 32W 30D 840 CN	30 °
929001354908	Master LED PAR30L 32W 30D 857	30 °
929001354910	Master LED PAR30L 32W 30D 860 CN	30 °
929001374302	MAS LED spot ND 37W PAR30L E27 827 15D	15 °
929001374308	Master LED PAR30L 40W 15D 827	15 °

Order Code	Full Product Name	Rated Beam Angle
929001374310	Master LED PAR30L 40W 15D 827 CN	15 °
929001374402	MAS LED spot ND 37W PAR30L E27 830 15D	15 °
929001374408	Master LED PAR30L 40W 15D 830	15 °
929001374410	Master LED PAR30L 40W 15D 830 CN	15 °
929001374508	Master LED PAR30L 40W 15D 840	15 °
929001374510	Master LED PAR30L 40W 15D 840 CN	15 °
929001374608	Master LED PAR30L 40W 15D 857	15 °
929001374610	Master LED PAR30L 40W 15D 860 CN	15 °
929001374702	MAS LED spot ND 41W PAR30L E27 827 30D	30 °
929001374708	Master LED PAR30L 40W 30D 827	30 °
929001374710	Master LED PAR30L 40W 30D 827 CN	30 °
929001374802	MAS LED spot ND 41W PAR30L E27 830 30D	30 °
929001374808	Master LED PAR30L 40W 30D 830	30 °
929001374810	Master LED PAR30L 40W 30D 830 CN	30 °
929001374908	Master LED PAR30L 40W 30D 840	30 °
929001374910	Master LED PAR30L 40W 30D 840 CN	30 °
929001375008	Master LED PAR30L 40W 30D 857	30 °
929001375010	Master LED PAR30L 40W 30D 860 CN	30 °
929001941912	Master LED PAR30L 28W 15D 830 100-277V	15 °
929001942012	Master LED PAR30L 28W 30D 830 100-277V	30 °
929001942112	Master LED PAR30L 28W 15D 840 100-277V	15 °
929001942212	Master LED PAR30L 28W 30D 840 100-277V	30 °
929001358112	LEDspot 50W PAR20 2700K WV 25D ND SO	25 °

## Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929001317402	MAS LEDspot CLA D 6-50W 827 PAR20 25D	PAR20
929001317408	MAS LEDspot D 6-50W E27 827 PAR20 25D	PAR20
929001317502	MAS LEDspot CLA D 6-50W 830 PAR20 25D	PAR20
929001317602	MAS LEDspot CLA D 6-50W 840 PAR20 25D	PAR20
929001317702	MAS LEDspot CLA D 6-50W 827 PAR20 40D	PAR20
929001317802	MAS LEDspot CLA D 6-50W 830 PAR20 40D	PAR20
929001317902	MAS LEDspot CLA D 6-50W 840 PAR20 40D	PAR20
929001322502	MAS LEDspot CLA D 13-100W 827 PAR38 25D	PAR38
929001322508	MAS LEDspot D 13-100W E27 927 PAR38 25D	PAR38
929001322702	MAS LEDspot CLA ND 9-60W 827 PAR38 25D	PAR38
929001322902	MAS LEDspot CLA D 9.5-75W 827 PAR30S 25D	PAR30S
929001323002	MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D	PAR30S
929001323108	MAS LEDspot D 9-70W E27 927 PAR30S 25D	PAR30S
929001342902	MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D	PAR30S
929001343912	LEDspot 90W PAR30S 830 100-277V 25D ND	PAR30S
929001353802	MAS LED spot ND 20W PAR30L E27 830 15D	PAR30L
929001354002	MAS LED spot ND 20W PAR30L E27 830 30D	PAR30L
929001354808	Master LED PAR30L 32W 30D 840	PAR30L
929001354810	Master LED PAR30L 32W 30D 840 CN	PAR30L
929001354908	Master LED PAR30L 32W 30D 857	PAR30L
929001354910	Master LED PAR30L 32W 30D 860 CN	PAR30L
929001374302	MAS LED spot ND 37W PAR30L E27 827 15D	PAR30L
929001374308	Master LED PAR30L 40W 15D 827	PAR30L

Order Code	Full Product Name	Bulb Shape
929001374310	Master LED PAR30L 40W 15D 827 CN	PAR30L
929001374402	MAS LED spot ND 37W PAR30L E27 830 15D	PAR30L
929001374408	Master LED PAR30L 40W 15D 830	PAR30L
929001374410	Master LED PAR30L 40W 15D 830 CN	PAR30L
929001374508	Master LED PAR30L 40W 15D 840	PAR30L
929001374510	Master LED PAR30L 40W 15D 840 CN	PAR30L
929001374608	Master LED PAR30L 40W 15D 857	PAR30L
929001374610	Master LED PAR30L 40W 15D 860 CN	PAR30L
929001374702	MAS LED spot ND 41W PAR30L E27 827 30D	PAR30L
929001374708	Master LED PAR30L 40W 30D 827	PAR30L
929001374710	Master LED PAR30L 40W 30D 827 CN	PAR30L
929001374802	MAS LED spot ND 41W PAR30L E27 830 30D	PAR30L
929001374808	Master LED PAR30L 40W 30D 830	PAR30L
929001374810	Master LED PAR30L 40W 30D 830 CN	PAR30L
929001374908	Master LED PAR30L 40W 30D 840	PAR30L
929001374910	Master LED PAR30L 40W 30D 840 CN	PAR30L
929001375008	Master LED PAR30L 40W 30D 857	PAR30L
929001375010	Master LED PAR30L 40W 30D 860 CN	PAR30L
929001941912	Master LED PAR30L 28W 15D 830 100-277V	PAR30L
929001942012	Master LED PAR30L 28W 30D 830 100-277V	PAR30L
929001942112	Master LED PAR30L 28W 15D 840 100-277V	PAR30L
929001942212	Master LED PAR30L 28W 30D 840 100-277V	PAR30L
929001358112	LEDspot 50W PAR20 2700K WV 25D ND SO	PAR20

## Temperature


# MASTER LEDspot PAR

Order Code	Full Product Name	T-Case Maximum (Nom)
929001317402	MAS LEDspot CLA D 6-50W 827 PAR20 25D	-
929001317408	MAS LEDspot D 6-50W E27 827 PAR20 25D	-
929001317502	MAS LEDspot CLA D 6-50W 830 PAR20 25D	-
929001317602	MAS LEDspot CLA D 6-50W 840 PAR20 25D	-
929001317702	MAS LEDspot CLA D 6-50W 827 PAR20 40D	-
929001317802	MAS LEDspot CLA D 6-50W 830 PAR20 40D	-
929001317902	MAS LEDspot CLA D 6-50W 840 PAR20 40D	-
929001322502	MAS LEDspot CLA D 13-100W 827 PAR38 25D	-
929001322508	MAS LEDspot D 13-100W E27 927 PAR38 25D	-
929001322702	MAS LEDspot CLA ND 9-60W 827 PAR38 25D	-
929001322902	MAS LEDspot CLA D 9.5-75W 827 PAR30S 25D	-
929001323002	MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D	-
929001323108	MAS LEDspot D 9-70W E27 927 PAR30S 25D	-
929001342902	MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D	-
929001343912	LEDspot 90W PAR30S 830 100-277V 25D ND	-
929001353802	MAS LED spot ND 20W PAR30L E27 830 15D	66 °C
929001354002	MAS LED spot ND 20W PAR30L E27 830 30D	66 °C
929001354808	Master LED PAR30L 32W 30D 840	79 °C
929001354810	Master LED PAR30L 32W 30D 840 CN	79 °C
929001354908	Master LED PAR30L 32W 30D 857	79 °C
929001354910	Master LED PAR30L 32W 30D 860 CN	79 °C
929001374302	MAS LED spot ND 37W PAR30L E27 827 15D	88 °C
929001374308	Master LED PAR30L 40W 15D 827	90 °C
929001374310	Master LED PAR30L 40W 15D 827 CN	90 °C
929001374402	MAS LED spot ND 37W PAR30L E27 830 15D	88 °C
929001374408	Master LED PAR30L 40W 15D 830	90 °C
929001374410	Master LED PAR30L 40W 15D 830 CN	90 °C
929001374508	Master LED PAR30L 40W 15D 840	90 °C
929001374510	Master LED PAR30L 40W 15D 840 CN	90 °C
929001374608	Master LED PAR30L 40W 15D 857	90 °C
929001374610	Master LED PAR30L 40W 15D 860 CN	90 °C
929001374702	MAS LED spot ND 41W PAR30L E27 827 30D	88 °C
929001374708	Master LED PAR30L 40W 30D 827	90 °C
929001374710	Master LED PAR30L 40W 30D 827 CN	90 °C
929001374802	MAS LED spot ND 41W PAR30L E27 830 30D	88 °C
929001374808	Master LED PAR30L 40W 30D 830	90 °C
929001374810	Master LED PAR30L 40W 30D 830 CN	90 °C
929001374908	Master LED PAR30L 40W 30D 840	90 °C
929001374910	Master LED PAR30L 40W 30D 840 CN	90 °C
929001375008	Master LED PAR30L 40W 30D 857	90 °C
929001375010	Master LED PAR30L 40W 30D 860 CN	90 °C
929001941912	Master LED PAR30L 28W 15D 830 100-277V	80 °C
929001942012	Master LED PAR30L 28W 30D 830 100-277V	80 °C
929001942112	Master LED PAR30L 28W 15D 840 100-277V	80 °C
929001942212	Master LED PAR30L 28W 30D 840 100-277V	80 °C
929001358112	LEDspot 50W PAR20 2700K WV 25D ND SO	-




# MASTER LEDspot PAR


## Accent Diagrams




MASTER LEDspot PAR 50W E27 827 25D




MASTER LEDspot PAR 50W E27 830 25D




MASTER LEDspot PAR 50W E27 840 25D




MASTER LEDspot PAR 50W E27 827 40D




MASTER LEDspot PAR 50W E27 830 40D




MASTER LEDspot PAR 50W E27 840 40D




MASTER LEDspot PAR 100W E27 827 25D




MASTER LEDspot PAR 60W E27 827 25D




MASTER LEDspot PAR 75W E27 827 25D



MASTER LEDspot PAR 75W E27 840 25D




MASTER LEDspot PAR 75W E27 830 25D




LEDspot MAS 20W E27 PAR30L 830 15D ND

# MASTER LEDspot PAR


## Accent Diagrams




LEDspot MAS 20W E27 PAR30L 830 30D ND




LEDspot PAR30L E27 32W 4000K 30D




LEDspot PAR30L E27 5700K 30D




LEDspot MAS 37W E27 PAR30L 827 15D ND




LEDspot MAS 37W E27 PAR30L 830 15D ND




LEDspot E27 PAR30L 35W 4000K




LEDspot E27 PAR30L 35W 6000K




LEDspot MAS 41W E27 PAR30L 827 30D ND




LEDspot MAS 41W E27 PAR30L 830 30D ND



LEDspot E27 PAR30L 40W 4000K




LEDspot E27 PAR30L 40W 6000K



LED PAR30L 28W 15D 100-277V


# MASTER LEDspot PAR

## Accent Diagrams




LED PAR30L 28W 30D 100-277V


## Beam Diagrams




MASTER LEDspot PAR 50W E27 827 25D




MASTER LEDspot PAR 50W E27 830 25D




MASTER LEDspot PAR 50W E27 840 25D




MASTER LEDspot PAR 50W E27 827 40D




MASTER LEDspot PAR 50W E27 830 40D




MASTER LEDspot PAR 50W E27 840 40D



MASTER LEDspot PAR 100W E27 827 25D




MASTER LEDspot PAR 60W E27 827 25D




MASTER LEDspot PAR 75W E27 827 25D

# MASTER LEDspot PAR


## Beam Diagrams




MASTER LEDspot PAR 75W E27 840 25D




MASTER LEDspot PAR 75W E27 830 25D




LEDspot MAS 20W E27 PAR30L 830 15D ND




LEDspot MAS 20W E27 PAR30L 830 30D ND




LEDspot PAR30L E27 32W 4000K 30D




LEDspot PAR30L E27 5700K 30D




LEDspot MAS 37W E27 PAR30L 827 15D ND




LEDspot MAS 37W E27 PAR30L 830 15D ND




LEDspot E27 PAR30L 35W 4000K



LEDspot E27 PAR30L 35W 6000K



LEDspot MAS 41W E27 PAR30L 827 30D ND




LEDspot MAS 41W E27 PAR30L 830 30D ND




# MASTER LEDspot PAR


## Beam Diagrams




LEDspot E27 PAR30L 40W 4000K



LEDspot E27 PAR30L 40W 6000K



LED PAR30L 28W 15D 100-277V



LED PAR30L 28W 30D 100-277V

