



The energy-saving alternative for lighting in public areas

MASTER LEDspot PAR

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on.

Benefits

- \cdot Up to 80% energy saving compared to halogen lamps
- · Retrofitable and compatible with existing fixtures with E27 holder
- · Lower maintenance costs

Features

- · Lifetime of 45,000 hours
- · Dimmable (except PAR38 OD)
- \cdot UV- and IR-free light for less heat and protection for heat-sensitive objects
- \cdot Free of mercury and hazardous materials RoHS compliant

Application

 Hotels, restaurants, bars, cafés, museums, shops, musea, art. galleries, lobbies, corridors, stairwells, washrooms, reception areas, exhibitions, display cabinets

Versions








12-120W E26 PAR30S





LEDspots MAS GMGC1 PAR30S E27

Dimensional drawing



U






Product	D	С
MAS LEDspot D 12-100W E27 927 PAR30S 25D	92 mm	84 mm

Product	D	С
Master LED 12-120W PAR30s 827 25D EER1	86 mm	93 mm

Product	D	С
MAS LEDspot D 13-100W E27 927 PAR38 25D	124 mm	130 mm
MAS LEDspot D 13-100W E27 927 PAR38 25D	124 mm	130 mm

Dimensional drawing



Product	D	С
LEDClassic 10-80WPAR38 827 25D 1CT/3 SRT	122 mm	134 mm

Light Technical	
Beam Angle (Nom)	25 degree(s)
Correlated Color Temperature (Nom)	2700 K
LLMF At End Of Nominal Lifetime	70 %
(Nom)	
Operating and Electrical	
Input Frequency	50 to 60 Hz

General Information

			Rated		
		Cap-	Lifetime	Switching	Nominal
Order Code	Full Product Name	Base	(Hours)	Cycle	lifetime
929001322779	LEDClassic	E27	15,000	25,000	15,000
	10-80WPAR38 827 25D		hour(s)		hour(s)
	1CT/3 SRT				
929001918808	Master LED 12-120W	E26	-	50,000	15,000
	PAR30s 827 25D EER1				hour(s)
929002339008	MAS LEDspot D	E27	-	50,000	25,000
	13-100W E27 927 PAR38				hour(s)
	25D				

			Rated		
		Cap-	Lifetime	Switching	Nominal
Order Code	Full Product Name	Base	(Hours)	Cycle	lifetime
929002339068	MAS LEDspot D	E27	-	50,000	25,000
	13-100W E27 927 PAR38				hour(s)
	25D				
929002030808	MAS LEDspot D	E27	-	50,000	25,000
	12-100W E27 927				hour(s)
	PAR30S 25D				

Light Technical

		Color			Luminous
		rendering	Color	Luminous	Intensity
Order Code	Full Product Name	index (CRI)	Code	Flux	(Nom)
929001322779	LEDClassic	80	827	900 lm	1,800 cd
	10-80WPAR38 827				
	25D 1CT/3 SRT				
929001918808	Master LED 12-120W	80	827	1,300 lm	3,200 cd
	PAR30s 827 25D EER1				
929002339008	MAS LEDspot D	90	927	1,100 lm	3,500 cd
	13-100W E27 927				
	PAR38 25D				

		Color			Luminous
		rendering	Color	Luminous	Intensity
Order Code	Full Product Name	index (CRI)	Code	Flux	(Nom)
929002339068	MAS LEDspot D	90	927	-	3,500 cd
	13-100W E27 927				
	PAR38 25D				
929002030808	MAS LEDspot D	90	927	1,000 lm	3,000 cd
	12-100W E27 927				
	PAR30S 25D				

Operating and Electrical

				Starting	
	Full Product	Line	Power	Time	Wattage
Order Code	Name	Frequency	Consumption	(Nom)	Equivalent
929001322779	LEDClassic	-	10 W	0.5 s	80 W
	10-80WPAR38				
	827 25D 1CT/3				
	SRT				
929001918808	Master LED	50 to 60	12 W	0.8 s	120 W
	12-120W PAR30s	Hz			
	827 25D EER1				
929002339008	MAS LEDspot D	-	13 W	0.5 s	100 W
	13-100W E27 927				
	PAR38 25D				

				Starting	
	Full Product	Line	Power	Time	Wattage
Order Code	Name	Frequency	Consumption	(Nom)	Equivalent
929002339068	MAS LEDspot D	50 to 60	13 W	0.5 s	100 W
	13-100W E27 927	Hz			
	PAR38 25D				
929002030808	MAS LEDspot D	-	12 W	0.5 s	100 W
	12-100W E27 927				
	PAR30S 25D				

Temperature

		Ambient	T-Case Maximum
Order Code	Full Product Name	temperature range	(Nom)
929001322779	LEDClassic 10-80WPAR38 827 25D 1CT/3 SRT	-20 to +45 °C	80 ℃
929001918808	Master LED 12-120W PAR30s 827 25D EER1	-	90 ℃
929002339008	MAS LEDspot D 13-100W E27 927 PAR38 25D	-20 to +45 °C	75 °C

			T-Case
		Ambient	Maximum
Order Code	Full Product Name	temperature range	(Nom)
929002339068	MAS LEDspot D 13-100W E27	-	75 ℃
	927 PAR38 25D		
929002030808	MAS LEDspot D 12-100W E27	-20 to +45 ℃	85 °C
	927 PAR30S 25D		

Controls and Dimming

Order Code	Full Product Name	Dimmable
929001322779	LEDClassic 10-80WPAR38 827 25D 1CT/3 SRT	No
929001918808	Master LED 12-120W PAR30s 827 25D EER1	No
929002339008	MAS LEDspot D 13-100W E27 927 PAR38 25D	Only with specific
		dimmers

Order Code	Full Product Name	Dimmable
929002339068	MAS LEDspot D 13-100W E27 927 PAR38 25D	Only with specific
		dimmers
929002030808	MAS LEDspot D 12-100W E27 927 PAR30S 25D	Only with specific
		dimmers

Mechanical and Housing


Order Code Full Product Name Finish Bulb Shape 929001322779 LEDClassic 10-80WPAR38 827 25D 1CT/3 Clear PAR38 5RT PAR30S PAR30S 9290013329008 Master LED 12-120W PAR30S 827 25D EERI - PAR30S 929002339008 MAS LEDspot D 13-100W E27 927 PAR38 Clear PAR38 25D 25D PAR30S PAR30S				
929001322779 LEDClassic 10-80WPAR38 827 25D 1CT/3 Clear PAR38 SRT 929001918808 Master LED 12-120W PAR30s 827 25D EER1 - PAR30S 929002339008 MAS LEDspot D 13-100W E27 927 PAR38 Clear PAR38			Bulb	
SRT 929001918808 Master LED 12-120W PAR30s 827 25D EER1 - PAR30S 929002339008 MAS LEDspot D 13-100W E27 927 PAR38 Clear PAR38	Order Code	Full Product Name	Finish	Bulb Shape
929001918808 Master LED 12-120W PAR30s 827 25D EER1 - PAR30S 929002339008 MAS LEDspot D 13-100W E27 927 PAR38 Clear PAR38	929001322779	LEDClassic 10-80WPAR38 827 25D 1CT/3	Clear	PAR38
929002339008 MAS LEDspot D 13-100W E27 927 PAR38 Clear PAR38		SRT		
·	929001918808	Master LED 12-120W PAR30s 827 25D EER1	-	PAR30S
25D	929002339008	MAS LEDspot D 13-100W E27 927 PAR38	Clear	PAR38
		25D		

		Bulb	
Order Code	Full Product Name	Finish	Bulb Shape
929002339068	MAS LEDspot D 13-100W E27 927 PAR38	-	PAR38
	25D		
929002030808	MAS LEDspot D 12-100W E27 927 PAR30S	Clear	PAR30S
	25D		


Approval and Application

		Energy Consumption
Order Code	Full Product Name	kWh/1000 h
929001322779	LEDClassic 10-80WPAR38 827 25D 1CT/3 SRT	-
929001918808	Master LED 12-120W PAR30s 827 25D EER1	12 kWh
929002339008	MAS LEDspot D 13-100W E27 927 PAR38 25D	-
929002339068	MAS LEDspot D 13-100W E27 927 PAR38 25D	-


		Energy Consumption
Order Code	Full Product Name	kWh/1000 h
929002030808	MAS LEDspot D 12-100W E27 927 PAR30S 25D	-



Accent Diagrams





Accent Diagram - MAS LEDspot D 13-100W E27 927 PAR38 25D




Accent Diagram - MAS LEDspot D 12-100W E27 927 PAR3OS 25D

250 500 1000 E_h(lx)







Accent Diagram - Master LED 12-120W PAR30s 827 25D EER1




Accent Diagram - LEDClassic 10-80WPAR38 827 25D 1CT/3 SRT


Beam Diagrams







Beam diagram - MAS LEDspot D 12-100W E27 927 PAR30S 25D Beam diagram - MAS LEDspot D 13-100W E27 927 PAR38 25D Beam diagram - LEDClassic 10-80WPAR38 827 25D 1CT/3 SRT



Beam diagram - Master LED 12-120W PAR30s 827 25D EER1

