



ArenaVision MVF404 – exceptional optical efficiency

ArenaVision MVF404

The ArenaVision MVF404 floodlight – designed for outdoor sports stadiums – dramatically increases the theatrical and emotional impact of sports for TV audiences and spectators, while allowing the players to perform under optimal visual conditions. Thanks to the innovative Philips MHN-SE 2000 W high-output compact single-ended metal-halide lamp and high-tech single-piece precision optics, ArenaVision MVF404 offers much higher optical efficiency than ever before. In addition, this 2 kW floodlight boasts easy lamp fitting and replacement, full IP65 compliance, safety knife connector system and a breakthrough electronic hot-restrike solution – while continuing to deliver all the traditional benefits of Philips ArenaVision systems. The (optional) flicker-free version of ArenaVision MVF404 is designed to ensure that the flicker effect is fully eliminated in order to guarantee perfect images filmed with super-slow-motion cameras at sports events. The flicker-free version of ArenaVision MVF404 comes equipped with a special electronic ignitor, which works in combination with Philips' flicker-free electronic-ballast GearUnits (ECM330), to be ordered separately.

Faydaları

- Innovative floodlight with Philips' compact single-ended lamp; dedicated optics ensure maximum optical efficiency and enable accurate light distribution with a minimum of spill light
- Quartz metal halide lamp meets the most demanding lighting and TV broadcast requirements with excellent color rendering
- The flicker-free version completely eliminates flicker effect, thereby guaranteeing perfect images filmed with super-slow-motion cameras

ArenaVision MVF404


Özellikler

- Mükemmel renksel geriverime sahip yüksek çıkışlı kompakt tek uçlu metal halojen lamba
- Özel hassas optik sistemler
- IP65
- Bıçak konnektörlü güvenlik sistemi
- Elektronik sıcak çift kaplamalı




Uygulama

- Dış mekan spor stadyumları

ÜRÜN BİLGİLERİ




Seri ateşleyiciler içeren elektrik bağlantı kutusu



OPDP_MVF403i_0013-Detail photo

ÜRÜN BİLGİLERİ





OPDP_MVF403i_0015-Detail
photo



OPDP_MVF403i_0019-Detail
photo



OPDP_MVF403i_0025-Detail
photo



Elektronik ateşleyicili elektrik
bağlantı kutusu

ArenaVision MVF404

Uygulama Koşulları

Maksimum dim seviyesi	Not applicable
-----------------------	----------------

Onay ve Uygulama

Mekanik çarpışma koruma kodu	IK08
------------------------------	------

Ani Akım Koruması (Ortak/ Diferansiyel)	-
--	---

Kontroller ve Dimming

Dim Edilebilir	Hayır
----------------	-------

Genel Bilgiler

Aydınlatma armatürü ışık ışını yayılması	-
---	---

CE işareti	Evet
------------	------

Işık kaynağı rengi	956 gün ışığı
--------------------	---------------

Optik kapak/lens türü	DOWN
-----------------------	------

Alev alma işareti	NO
-------------------	----

Sürücü	-
--------	---

Lamba ailesi kodu	MHN-SEH
-------------------	---------

Lamba gücü	2000 W
------------	--------

Sürücü birimi sayısı	-
----------------------	---

Işık kaynağı sayısı	1
---------------------	---

Ürün Ailesi Kodu	MVF404
------------------	--------

Başlangıç Performansı (IEC Uyumlu)

Başlangıçtaki Renk Sıcaklığı	5600 K
------------------------------	--------

Başlangıçtaki Renksel Geriverim İndeksi	>90
--	-----

Işık Teknik Ayrıntıları

Standart devirme açısı yandan giriş	-
-------------------------------------	---

Standart eğim açısı üstten montaj	-
-----------------------------------	---

Mekanik Ayrıntılar ve Muhafaza

Renk	Aluminum
------	----------

Genel Bilgiler

Order Code	Full Product Name	Optik sistem türü
50205300	MVF404 MHN-SEH2000W/956 B6 SI	Beam category B6
60409200	MVF404 MHN-SEH2000W/956 B8 SI	Beam category B8
59907400	MVF404 MHN-SEH2000W/956 B8 ESI	Beam category B8

