



Zadora adjustable

Zadora, adjustable

Recessed adjustable downlights for MASTERline ES dichroic halogen lamp with beams of 8°, 24°, 36° and 60° and TWISTline lamps. Available in white, chrome, gold, brushed aluminium, black, matt satin, metal grey, and black nickel. Ready-to-install kit versions (downlight, lamp, transformer) available for 12V/50W MASTERline lamps in electromagnetic Class I, Class II, and HF Class II. Kit range also includes a 230V TWISTline version. Kits are available in white, chrome, gold, and brushed aluminium.

Benefits

- Halogen accent lighting with the high power of MASTERLine 35 mm and 50 mm dichroic lamps
- Adjustable downlights with beam widths of 8°, 24°, 36° or 60° and 30° orientation from the vertical to create exactly the right decorative or accent effects
- Also available in complete, ready-to-install kit versions

Features

- Available in fixed and adjustable versions
- MASTERLine 35 mm and 50 mm dichroic lamps and Twistline Alu lamps
- Wide choice of beam widths
- Also available in complete, ready-to-install kit versions

Application

- Retail
- Offices

Specifications

Type	QBD570
Light source	Halogen: <ul style="list-style-type: none">- 1 x MASTERLine ES / GU5.3 / 45 W- 1 x Brilliantline Dichroic / GU4 / 20, 35 W- 1 x Twistline Dichro / GZ10 / 50 W
Lamp beam angle	MASTERLine 25°, 40°

Lamp included	No (optional)
Lamp position	Vertical
Transformer	Electronic (ET)

Zadora, adjustable

Color	Grey (GR)
	White (WH)
	Black (BK)
	Anthracite (ANT)
	Aluminum (ALU)
	Matt finishing (MAT)
	Chrome (CR)
	Gold (GO)

Material	Die-cast aluminum and steel
Installation	Fixation by means of spring fasteners
Maintenance	Direct lamp access
Remarks	Bracket (BR) installed to ensure a safe distance between luminaire and ceiling
	Dedicated ready to install versions available (K), downlight, lamp and electronic transformer
Main applications	Office, retail

Versions



**Zadora QBD570 adjustable
downlight with halogen lamp**

