



Zadora – free to create

Zadora, adjustable

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

Benefits

- Halogen accent lighting with the high power of MASTERLine 35 mm and 50 mm dichroic lamps
- Adjustable downlights with beam widths of 8°, 24°, 36° or 60° and 30° orientation from the vertical to create exactly the right decorative or accent effects
- Also available in complete, ready-to-install kit versions

Features

- Available in fixed and adjustable versions
- MASTERLine 35 mm and 50 mm dichroic lamps and Twistline Alu lamps
- Wide choice of beam widths
- Also available in complete, ready-to-install kit versions

Application

- Retail
- Offices

Specifications

Type	QBD570	Light source	Halogen:
			- 1 x MASTERLine ES / GU5.3 / 45 W
			- 1 x Brilliantline Dichroic / GU4 / 20, 35 W
			- 1 x Twistline Dichro / GZ10 / 50 W

Zadora, adjustable

Lamp beam angle	MASTERLine 25°, 40°	Material	Die-cast aluminum and steel
Lamp included	No (optional)	Installation	Fixation by means of spring fasteners
Lamp position	Vertical	Maintenance	Direct lamp access
Transformer	Electronic (ET)	Remarks	Bracket (BR) installed to ensure a safe distance between luminaire and ceiling
Color	Grey (GR)		Dedicated ready to install versions available (K), downlight, lamp and electronic transformer
	White (WH)	Main applications	Office, retail
	Black (BK)		
	Anthracite (ANT)		
	Aluminum (ALU)		
	Matt finishing (MAT)		
	Chrome (CR)		
	Gold (GO)		

Versions



Zadora QBD570 adjustable
downlight with halogen lamp

