



Smart Halogen Downlight – a reliable way to make your merchandise stand out

Smart Halogen Downlight QBS020

Shop owners opening a new outlet or refurbishing their current installation and contractors looking for attractive propositions for their customers (small/non-chain retailers) now have the ideal solution for impactful, yet affordable accent lighting. Our Smart Halogen Downlight offers customers a choice of different shapes to suit different functions, and the professional finish lends the luminaire an air of contemporary sophistication. Thanks to its robust housing, the Smart Halogen Downlight is a long-lasting solution. Quality clips ensure ease of installation.

Benefits

- Affordable yet highly effective accent-lighting solution
- Safe and durable
- Wide choice for customers; contemporary sophistication

Features

- Robust housing
- Different shapes to suit different functions
- Professional finish
- Good-quality clips for easy installation

Smart Halogen Downlight QBS020

Application

- Retail – sales areas, shop windows
- Offices – exhibition and highlight areas
- Hospitality and cruise ships – corridors, service areas, reception areas, lobbies, lounges, restaurants, cabins
- Healthcare – corridors, reception areas, waiting areas
- Airports – arrival/departure halls, corridors, waiting areas, service desks, shops

Specifications

Type	Die-cast aluminum versions and for MR11 lamp types:
	- QBS020, 022: fixed
	- QBS021: adjustable
	Die-cast aluminum versions and for MR16 lamp types:
	- QBS023, 026, QBS040~046: fixed
- QBS024, 025, 027~029, QBS047: adjustable	
Light source	Halogen:
	- 1 x ESSENTIAL 1CT / GU4 / 20, 35 W
	- 1 x ESSENTIAL Closed 1CT / GU5.3 / 20, 50 W
Lamp beam angle	30 , 36°
Lamp included	No

Lamp position	Vertical
Light distribution	Direct (D)
Transformer	12 V (not included)
Material	QBS020~029, QBS040~047 versions:
	- Die-cast aluminum
	QBS030~032 versions:
	- Cast aluminum
Color	QBS020~029, QBS040~047 versions:
	- White and grey
	QBS030~032 versions:
	- Silver
Installation	Fixation by means of spring fasteners
Maintenance	Direct lamp access
Main applications	Retail, fashion, hospitality

Versions



QBS020 1x MAX35W WH



QBS040 1x MAX50W WH



QBS042 1x MAX50W WH



QBS048 1x MAX50W WH



QBS047 1x MAX50W WH

Smart Halogen Downlight QBS020

Approval and Application

Ingress protection code IP20

Operating and Electrical

Input Voltage 12 V

General Information

Flammability mark F

Number of light sources 1

Service tag Yes

Mechanical and Housing

Color White

Operating and Electrical

Order Code	Full Product Name	Maximum lamp power
910403630255	QBS020 1x MAX35W/12V-GU4 WH	MAX35
910403630284	QBS040 1xMAX50W/12V-GU5.3 WH	MAX50
910403630291	QBS042 1xMAX50W/12V-GU5.3 WH	MAX50

Order Code	Full Product Name	Maximum lamp power
910403630294	QBS048 1xMAX50W/12V-GU5.3 WH	MAX50
910403630295	QBS047 1xMAX50W/12V-GU5.3 WH	MAX50

General Information

Order Code	Full Product Name	Cap-Base
910403630255	QBS020 1x MAX35W/12V-GU4 WH	GU4
910403630284	QBS040 1xMAX50W/12V-GU5.3 WH	GU5.3
910403630291	QBS042 1xMAX50W/12V-GU5.3 WH	GU5.3

Order Code	Full Product Name	Cap-Base
910403630294	QBS048 1xMAX50W/12V-GU5.3 WH	GU5.3
910403630295	QBS047 1xMAX50W/12V-GU5.3 WH	GU5.3

