



A smooth design solution for a seamless look

PAR30/PAR20 LED

Philips PAR30S LED Single Optic Lamps with AirFlux Technology provide superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

Benefits

- Will not fade colors, avoids inventory spoilage
- Lowers maintenance costs by reducing re-lamp frequency
- 5-year limited warranty**
- ** For details see: http://www.usa.lighting.philips.com/connect/tools_literature/warranties.wpd

Features

- Retail Optic reduces glare to improve shopper experience
- 25,000-hour rated average life*
- 12W PAR30S saves 63 watts when compared to a 75W halogen PAR30S
- 83 CRI for excellent color rendering
- Virtually UV/IR free in the beam
- Contains no mercury

Application

- Ideal for general and accent lighting in retail, hospitality and office spaces.


PAR30/PAR20 LED

Versions




LEDspot E27 PAR30S

Dimensional drawing




Product	D	C
LEDspot 70W PAR30S 865 100-277V 25D ND	93 mm	91 mm




PAR30/PAR20 LED

Accent Diagrams



LEDspot PAR30Sd 9-75W 950lm 25D 6500K
E27

Beam Diagrams



LEDspot PAR30Sd 9-75W 950lm 25D 6500K
E27

