



# Accent your merchandise without distraction

## PAR38 LED

Philips PAR38 LED Single Optic Lamps with AirFlux Technology improves shopping experience with superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

### Benefits

- No-fade colours, avoids inventory spoilage
- Lowers maintenance costs by reducing re-lamp frequency
- 5-year limited warranty‡
- ‡ For details, please visit [http://www.usa.lighting.philips.com/connect/tools\\_literature/warranties.wpd](http://www.usa.lighting.philips.com/connect/tools_literature/warranties.wpd)

### Features

- The single optic reduces glare to improve shopper experience
- 25,000-hour rated average life\*
- 19W PAR38 saves 101 watts when compared to a 120 W halogen PAR38
- 83 CRI for excellent colour-rendering
- Virtually UV/IR free in the beam
- Smooth dimming to 5% of full light level†
- Contains no mercury
- † Dimmable when using leading and trailing edge dimmers. (See <http://www.philips.com/ledtechguide> for more details.)

### Application

- Ideal for general and accent lighting in retail and hospitality spaces.

## PAR38 LED


### Warnings and Safety

- Suitable for use in damp locations.
- Not for use in totally enclosed luminaires.
- CAUTION: Risk of electric shock – do not use where directly exposed to water.
- NOTE: This device complies with Part 18 of the FCC rule. This product may cause interference with other devices. If interference occurs, change the location of the products involved. This RFLD device complies with Canadian ICES-005

### Versions



### Dimensional drawing



Product	D	C
LEDspot 120W PAR38 830 100-277V 25D ND	120 mm	133 mm

