




Attractive, dimmable LED alternative to popular incandescents.

A-Shape LED

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

Benefits

- 12.5W and 8W A19 lamps are ENERGY STAR[®] qualified
- Long life properties-- lowers maintenance costs by reducing re-lamp frequency
- Will not fade colors, avoids inventory spoilage
- Contains no mercury
- Emits virtually no UV/IR light in the beam
- 3-year or 5-year limited warranty depending upon operating hours

Features


- 12.5W A19, 8W A19 and 17W A21 versions available
- Smooth dimming to 10% of full light levels*
- Remote phosphor (yellow) disappears when energized to create even, soft white light
- 25,000-hour rated average life⁺
- Instant-on light
- ^{*}Dimmable when using leading edge dimmers (see Philips Website: www.philips.com/ledtechguide for compatible leading edge dimmers.)
- ⁺Rated average life based on engineering testing and probability analysis.

A-Shape LED


Application

- Ideal for decorative and ambient lighting in retail outlets, hotels, restaurants, multi-unit residences and government buildings.



Versions




Single Contact Medium Screw




Single Contact Medium Screw




Single Contact Medium Screw A19 (A19) Frosted




GU24 A 19mm Frosted



Single Contact Medium Screw A19 (A19) Frosted







Single Contact Medium Screw A19 (A19) Frosted



Single Contact Medium Screw A19 (A19) Frosted

A-Shape LED

Dimensional drawing



Product	D	C
5A19/PER/940/P/E26/DIM 6/1FB T20	62.5 mm	111.5 mm
5A19/PER/927/P/E26/DIM 6/1FB T20	62.5 mm	111.5 mm
8.8A19/PER/950/P/E26/DIM 6/1FB T20	62.5 mm	111.5 mm
8.8A19/PER/927/P/E26/DIM 6/1FB T20	62.5 mm	111.5 mm
8.8A19/PER/940/P/E26/DIM 6/1FB T20	62.5 mm	111.5 mm
5A19/PER/930/P/E26/DIM 6/1FB T20	62.5 mm	111.5 mm
5A19/PER/950/P/E26/DIM 6/1FB T20	62.5 mm	111.5 mm
8.8A19/PER/930/P/E26/DIM 6/1FB T20	62.5 mm	111.5 mm




Product	D	C
8A19/PER/927-922/CL/G/E26/WGX 1FB T20	60 mm	108 mm
5A19/PER/927-922/CL/G/E26/WGX 1FB T20	60 mm	108 mm

Product	D	C
8.8A19/PER/930/P/GU24/DIM 6/1FB T20	60 mm	106 mm

Product	D	C
16A19/PER/940/P/E26/DIM 6/1FB T20	60 mm	112 mm
16A19/PER/950/P/E26/DIM 6/1FB T20	60 mm	112 mm
16A19/PER/927/P/E26/DIM 6/1FB T20	60 mm	112 mm
16A19/PER/930/P/E26/DIM 6/1FB T20	60 mm	112 mm

A-Shape LED

Dimensional drawing



Product	D	C
8.5A19/LED/927/FR/P/ND 4/1FB	60 mm	104 mm
8.5A19/LED/930/FR/P/ND 4/1FB	60 mm	104 mm
8.5A19/LED/950/FR/P/ND 4/1FB	60 mm	104 mm
8A19/PER/850/FR/P/E26/D 4/4CT	60 mm	104 mm
8A19/PER/827/FR/P/E26/D 4/4CT	60 mm	104 mm
8A19/PER/830/FR/P/E26/D 4/4CT	60 mm	104 mm
8A19/PER/840/FR/P/E26/D 4/4CT	60 mm	104 mm

Product	D	C
8A19/LED/927/FR/Glass/E26/DIM 1FB T20	60 mm	105 mm
8A19/LED/930/FR/Glass/E26/DIM 1FB T20	60 mm	105 mm
8A19/LED/950/FR/Glass/E26/DIM 1FB T20	60 mm	105 mm

Product	D	C
14A19/PER/827/FR/P/E26/D 4/4CT	60 mm	117 mm
14A19/PER/840/FR/P/E26/D 4/4CT	60 mm	117 mm
14A19/PER/850/FR/P/E26/D 4/4CT	60 mm	117 mm
14A19/PER/830/FR/P/E26/D 4/4CT	60 mm	117 mm

Operating and electrical	
Voltage (Nom)	120 V
Starting Time (Nom)	0.5 s
Light technical	
Llmf At End Of Nominal Lifetime (Nom)	70 %
Mechanical and housing	
Bulb Shape	A19 (A19)

Approval and application

A-Shape LED

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	- kWh
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	- kWh
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	- kWh
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	- kWh
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	- kWh
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	- kWh
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	- kWh
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	- kWh
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	- kWh
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	- kWh
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	- kWh
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	- kWh
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	- kWh
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	- kWh
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	-

Controls and dimming

Order Code	Full Product Name	Dimmable
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	Yes
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	Yes
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	Yes
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	Yes
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	Yes
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	Yes
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	Yes
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	Yes
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	Yes
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	Yes
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	Yes
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	Yes
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	Yes
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	Yes
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	Yes

Operating and electrical

Order Code	Full Product Name	Input Frequency	Wattage Equivalent	Power (Nom)
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	50 to 60 Hz	40 W	5 W
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	50 to 60 Hz	60 W	8 W
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	60 Hz	60 W	8.8 W
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	60 Hz	40 W	5 W

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
565119	8.5A19/LED/927/FR/P/ND 4/1FB	-
565127	8.5A19/LED/930/FR/P/ND 4/1FB	-
565135	8.5A19/LED/950/FR/P/ND 4/1FB	-
581751	8A19/PER/827/FR/P/E26/D 4/4CT	-
581785	8A19/PER/850/FR/P/E26/D 4/4CT	-
581769	8A19/PER/830/FR/P/E26/D 4/4CT	-
581777	8A19/PER/840/FR/P/E26/D 4/4CT	-
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	-
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	-
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	-
581801	14A19/PER/827/FR/P/E26/D 4/4CT	-
581827	14A19/PER/830/FR/P/E26/D 4/4CT	-
581835	14A19/PER/840/FR/P/E26/D 4/4CT	-
581868	14A19/PER/850/FR/P/E26/D 4/4CT	-

Order Code	Full Product Name	Dimmable
565119	8.5A19/LED/927/FR/P/ND 4/1FB	No
565127	8.5A19/LED/930/FR/P/ND 4/1FB	No
565135	8.5A19/LED/950/FR/P/ND 4/1FB	No
581751	8A19/PER/827/FR/P/E26/D 4/4CT	Only with specific dimmers
581785	8A19/PER/850/FR/P/E26/D 4/4CT	Only with specific dimmers
581769	8A19/PER/830/FR/P/E26/D 4/4CT	Only with specific dimmers
581777	8A19/PER/840/FR/P/E26/D 4/4CT	Only with specific dimmers
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
581801	14A19/PER/827/FR/P/E26/D 4/4CT	Only with specific dimmers
581827	14A19/PER/830/FR/P/E26/D 4/4CT	Only with specific dimmers
581835	14A19/PER/840/FR/P/E26/D 4/4CT	Only with specific dimmers
581868	14A19/PER/850/FR/P/E26/D 4/4CT	Only with specific dimmers

Order Code	Full Product Name	Input Frequency	Wattage Equivalent	Power (Nom)
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	60 Hz	40 W	5 W
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	60 Hz	40 W	5 W
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	60 Hz	40 W	5 W
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	60 Hz	60 W	8.8 W
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	60 Hz	60 W	8.8 W

A-Shape LED

Order Code	Full Product Name	Input Frequency	Wattage Equivalent	Power (Nom)
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	60 Hz	60 W	8.8 W
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	60 Hz	100 W	16 W
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	60 Hz	100 W	16 W
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	60 Hz	100 W	16 W
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	60 Hz	100 W	16 W
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	60 Hz	60 W	8.8 W
565119	8.5A19/LED/927/FR/P/ND 4/1FB	60 Hz	60 W	8.5 W
565127	8.5A19/LED/930/FR/P/ND 4/1FB	60 Hz	60 W	8.5 W
565135	8.5A19/LED/950/FR/P/ND 4/1FB	60 Hz	60 W	8.5 W
581751	8A19/PER/827/FR/P/E26/D 4/4CT	60 Hz	60 W	8 W

Order Code	Full Product Name	Input Frequency	Wattage Equivalent	Power (Nom)
581785	8A19/PER/850/FR/P/E26/D 4/4CT	60 Hz	60 W	8 W
581769	8A19/PER/830/FR/P/E26/D 4/4CT	60 Hz	60 W	8 W
581777	8A19/PER/840/FR/P/E26/D 4/4CT	60 Hz	60 W	8 W
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	60 Hz	60 W	8 W
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	60 Hz	60 W	8 W
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	60 Hz	60 W	8 W
581801	14A19/PER/827/FR/P/E26/D 4/4CT	60 Hz	100 W	14 W
581827	14A19/PER/830/FR/P/E26/D 4/4CT	60 Hz	100 W	14 W
581835	14A19/PER/840/FR/P/E26/D 4/4CT	60 Hz	100 W	14 W
581868	14A19/PER/850/FR/P/E26/D 4/4CT	60 Hz	100 W	14 W

General information

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	E26	15000 h	20000X
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	E26	15000 h	20000X
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	E26	15000 h	50000
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	E26	15000 h	50000
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	E26	15000 h	50000
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	E26	15000 h	50000
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	E26	15000 h	50000
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	E26	15000 h	50000
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	E26	15000 h	50000
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	E26	15000 h	50000
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	E26	15000 h	50000
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	E26	15000 h	50000

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	E26	15000 h	50000
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	E26	15000 h	50000
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	GU24	15000 h	50000X
565119	8.5A19/LED/927/FR/P/ND 4/1FB	E26	11000 h	50000
565127	8.5A19/LED/930/FR/P/ND 4/1FB	E26	11000 h	50000
565135	8.5A19/LED/950/FR/P/ND 4/1FB	E26	11000 h	50000
581751	8A19/PER/827/FR/P/E26/D 4/4CT	E26	15000 h	50000
581785	8A19/PER/850/FR/P/E26/D 4/4CT	E26	15000 h	50000
581769	8A19/PER/830/FR/P/E26/D 4/4CT	E26	15000 h	50000
581777	8A19/PER/840/FR/P/E26/D 4/4CT	E26	15000 h	50000
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X
581801	14A19/PER/827/FR/P/E26/D 4/4CT	E26	15000 h	50000

A-Shape LED

Order Code	Full Product Name	Cap-Base	Nominal	Switching Cycle
			Lifetime (Nom)	
581827	14A19/PER/830/FR/P/E26/D 4/4CT	E26	15000 h	50000
581835	14A19/PER/840/FR/P/E26/D 4/4CT	E26	15000 h	50000

Order Code	Full Product Name	Cap-Base	Nominal	Switching Cycle
			Lifetime (Nom)	
581868	14A19/PER/850/FR/P/E26/D 4/4CT	E26	15000 h	50000

Light technical

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index	
					(Nom)	Luminous Flux (Nom)
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	300 °	927-922	2700, 2200 K	90	450 lm
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	300 °	927-922	2700, 2200 K	90	800 lm
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	250 °	940	4000 K	90	800 lm
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	250 °	927	2700 K	90	450 lm
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	250 °	930	3000 K	90	450 lm
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	250 °	940	4000 K	90	450 lm
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	250 °	950	5000 K	90	450 lm
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	250 °	927	2700 K	90	800 lm
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	250 °	930	3000 K	90	800 lm
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	250 °	950	5000 K	90	800 lm
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	250 °	950	5000 K	90	1600 lm
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	250 °	927	2700 K	90	1600 lm
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	250 °	930	3000 K	90	1600 lm
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	250 °	940	4000 K	90	1600 lm
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	250 °	930	3000 K	90	800 lm
565119	8.5A19/LED/927/FR/P/ND 4/1FB	150 °	927	2700 K	90	800 lm
565127	8.5A19/LED/930/FR/P/ND 4/1FB	150 °	930	3000 K	90	800 lm
565135	8.5A19/LED/950/FR/P/ND 4/1FB	150 °	950	5000 K	90	800 lm
581751	8A19/PER/827/FR/P/E26/D 4/4CT	-	827	2700 K	80	800 lm
581785	8A19/PER/850/FR/P/E26/D 4/4CT	-	850	5000 K	80	800 lm
581769	8A19/PER/830/FR/P/E26/D 4/4CT	-	830	3000 K	80	800 lm
581777	8A19/PER/840/FR/P/E26/D 4/4CT	-	841	4000 K	80	800 lm
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	320 °	927	2700 K	90	800 lm
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	320 °	930	3000 K	90	800 lm
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	320 °	950	5000 K	90	800 lm
581801	14A19/PER/827/FR/P/E26/D 4/4CT	-	827	2700 K	80	1600 lm
581827	14A19/PER/830/FR/P/E26/D 4/4CT	-	830	3000 K	80	1600 lm
581835	14A19/PER/840/FR/P/E26/D 4/4CT	-	841	4000 K	80	1600 lm
581868	14A19/PER/850/FR/P/E26/D 4/4CT	-	850	5000 K	80	1600 lm

Mechanical and housing

Order Code	Full Product Name	Bulb Finish
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	Clear
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	Clear
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	Frosted
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	Frosted
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	Frosted
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	Frosted
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	Frosted

Order Code	Full Product Name	Bulb Finish
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	Frosted
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	Frosted
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	Frosted
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	Frosted
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	Frosted
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	Frosted
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	Frosted

A-Shape LED


Order Code	Full Product Name	Bulb Finish
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	Frosted
565119	8.5A19/LED/927/FR/P/ND 4/1FB	Frosted
565127	8.5A19/LED/930/FR/P/ND 4/1FB	Frosted
565135	8.5A19/LED/950/FR/P/ND 4/1FB	Frosted
581751	8A19/PER/827/FR/P/E26/D 4/4CT	Frosted
581785	8A19/PER/850/FR/P/E26/D 4/4CT	Frosted
581769	8A19/PER/830/FR/P/E26/D 4/4CT	Frosted
581777	8A19/PER/840/FR/P/E26/D 4/4CT	Frosted

Order Code	Full Product Name	Bulb Finish
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	Frosted
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	Frosted
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	Frosted
581801	14A19/PER/827/FR/P/E26/D 4/4CT	Frosted
581827	14A19/PER/830/FR/P/E26/D 4/4CT	Frosted
581835	14A19/PER/840/FR/P/E26/D 4/4CT	Frosted
581868	14A19/PER/850/FR/P/E26/D 4/4CT	Frosted











Temperature

Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	-	-	50 °C
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	-	-	60 °C
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	-	-	90 °C
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	-	-	75 °C
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	-	-	75 °C
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	-	-	75 °C
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	-	-	75 °C
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	-	-	90 °C
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	-	-	90 °C
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	-	-	90 °C
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	-	-	90 °C
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	-	-	90 °C
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	-	-	90 °C
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	-	-	90 °C
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	-	-	90 °C
565119	8.5A19/LED/927/FR/P/ND 4/1FB	-	-	85 °C
565127	8.5A19/LED/930/FR/P/ND 4/1FB	-	-	85 °C
565135	8.5A19/LED/950/FR/P/ND 4/1FB	-	-	85 °C

Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)
581751	8A19/PER/827/FR/P/E26/D 4/4CT	45 °C	-20 °C	90 °C
581785	8A19/PER/850/FR/P/E26/D 4/4CT	45 °C	-20 °C	90 °C
581769	8A19/PER/830/FR/P/E26/D 4/4CT	45 °C	-20 °C	90 °C
581777	8A19/PER/840/FR/P/E26/D 4/4CT	45 °C	-20 °C	90 °C
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	45 °C	-20 °C	-
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	45 °C	-20 °C	-
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	45 °C	-20 °C	-
581801	14A19/PER/827/FR/P/E26/D 4/4CT	45 °C	-20 °C	90 °C
581827	14A19/PER/830/FR/P/E26/D 4/4CT	45 °C	-20 °C	90 °C
581835	14A19/PER/840/FR/P/E26/D 4/4CT	45 °C	-20 °C	90 °C
581868	14A19/PER/850/FR/P/E26/D 4/4CT	45 °C	-20 °C	90 °C



A-Shape LED



A-Shape LED

