



Attractive LED alternative to popular incandescents.

A-Shape LED

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Benefits

- This bulb is the perfect replacement for your matted incandescent bulbs
- Lower maintenance costs

Features

- Easy retrofit with existing lamp holders
- Long lifetime
- Instant full light on upon switching on
- UV- and IR-free light
- Free of mercury and hazardous materials – RoHS Compliant

Application

- Ideal for decorative and ambient lighting in retail outlets, hotels, restaurants, multi-unit residences and government buildings.

A-Shape LED

Versions



LEDbulbE A19 E26 FR



LEDbulb CorePro 19.5-150W E27
A67 Frosted 827 15D ND



LEDbulb E26 A9 FR



LEDbulb A19 E26 FR



LEDbulb Color P A19 E27 Red



LEDBulb CorePro E27 A60 8,5W




LEDbulb CLA A19 E26 FR



LEDbulb Color P A19 E27 Yellow


A-Shape LED

Dimensional drawing




Product	D	C
8.5A19/PER/927-22/FR/G/WGX 4/2FB T20	60 mm	108 mm

Product	D	C
LED 75W A60 E27 CW 230V FR ND 2CT/SRT6	60 mm	110 mm
LED 75W A60 E27 WW 230V FR ND 2CT/SRT6	60 mm	110 mm






Product	D	C
8.8A19/AMB/927-22 WG 120V LA	62.5 mm	111.5 mm



Product	D	C
10A19/LED/950/FR/P/E26/ND 4/2CT	60 mm	106 mm
11A19/LED/927/FR/P/E26/ND 4/2CT	60 mm	106 mm

A-Shape LED

Dimensional drawing



Product	D	C
8.8A19/AMB/927/ND D2D 6/1FB T20	61.5 mm	109.8 mm





Product	D	C
LEDGlobe13-100W G30 E27 CDL W ND MX	95 mm	137 mm
LEDGlobe13-100W G30 E27 WW W ND MX	95 mm	137 mm
LEDGlobe13-175W G95 E27 CDL100-240V BR	95 mm	137 mm
LEDGlobe13-175W G95 E27 WW 100-240V BR	95 mm	137 mm

Product	D	C
LED 100W A60 E27 CW 230V FR ND 2CT/SRT6	60 mm	110 mm

Product	D	C
13.5A19/LED/950/FR/P/E26/ND 4/2CT	60 mm	117 mm
14A19/LED/927/FR/P/E26/ND 4/2CT	60 mm	117 mm

A-Shape LED

Dimensional drawing



Product	D	C
BC8A19/LED/RED/ND 120V E27	60 mm	107 mm
BC8A19/LED/YELLOW/ND 120V E27	60 mm	107 mm


Product	D	C
29A21/PER/850/FR/P/E26/D/HO 4/1PF	77 mm	138 mm

Product	D	C
8.8A19/AMB/950 DIM 120V LA	62.5 mm	111.5 mm

Product	D	C
10A19/LED/927/FR/P/E26/ND 4/2CT	60 mm	104 mm
5.5A19/LED/950/FR/P/E26/ND 4/2CT	60 mm	104 mm
6.5A19/LED/927/FR/P/E26/ND 4/2CT	60 mm	104 mm
9A19/LED/950/FR/P/E26/ND 4/2CT	60 mm	104 mm

A-Shape LED

Dimensional drawing



Operating and Electrical	
Starting Time (Nom)	0.5 s

General Information

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929003005103	11A19/LED/927/FR/P/E26	E26	11,000	50,000	11,000
	/ND 4/2CT		hour(s)		hour(s)
929003005303	10A19/LED/950/FR/P/E2	E26	11,000	50,000	11,000
	6/ND 4/2CT		hour(s)		hour(s)
929002343133	29A21/PER/850/FR/P/E2	E26	15,000	50,000	15,000
	6/D/HO 4/1PF		hour(s)		hour(s)
929003004503	6.5A19/LED/927/FR/P/E2	E26	11,000	50,000	11,000
	6/ND 4/2CT		hour(s)		hour(s)
929003004703	5.5A19/LED/950/FR/P/E2	E26	11,000	50,000	11,000
	6/ND 4/2CT		hour(s)		hour(s)
929003004803	10A19/LED/927/FR/P/E26	E26	11,000	50,000	11,000
	/ND 4/2CT		hour(s)		hour(s)
929003005003	9A19/LED/950/FR/P/E26	E26	11,000	50,000	11,000
	/ND 4/2CT		hour(s)		hour(s)
929002333611	8.8A19/AMB/927/ND D2D	E26	-	50,000	15,000
	6/1FB T20				hour(s)
929001940941	8.8A19/AMB/927-22 WG	E26	-	50,000	15,000
	120V LA				hour(s)
929002036341	8.8A19/AMB/950 DIM	E26	-	50,000	15,000
	120V LA				hour(s)
929001234422	LED 75W A60 E27 WW	E27	15,000	50,000	15,000
	230V FR ND 2CT/SRT6		hour(s)		hour(s)
929001234822	LED 75W A60 E27 CW	E27	15,000	50,000	15,000
	230V FR ND 2CT/SRT6		hour(s)		hour(s)

Light Technical

Product	D	C
LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	60 mm	110 mm

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929001312422	LED 100W A60 E27 CW	E27	15,000	50,000	15,000
	230V FR ND 2CT/SRT6		hour(s)		hour(s)
929001998411	BC8A19/LED/RED/ND	E27	-	20,000	10,000
	120V E27				hour(s)
929002069111	LEDbulb 8.5-70W A60 E27	E27	-	50,000	15,000
	927 DIM 1PF/10				hour(s)
929002327703	8.5A19/PER/	E26	-	20,000	15,000
	927-22/FR/G/WGX 4/2FB				hour(s)
	T20				
929001998711	BC8A19/LED/YELLOW/ND	E27	-	20,000	10,000
	120V E27				hour(s)
929003005403	14A19/LED/927/FR/P/E26	E26	11,000	50,000	11,000
	/ND 4/2CT		hour(s)		hour(s)
929003005603	13.5A19/LED/950/FR/P/E	E26	11,000	50,000	11,000
	26/ND 4/2CT		hour(s)		hour(s)
929002441871	LEDGlobe13-175W G95	E27	-	50,000	15,000
	E27 WW 100-240V BR				hour(s)
929002441891	LEDGlobe13-100W G30	E27	-	50,000	15,000
	E27 WW W ND MX				hour(s)
929002441971	LEDGlobe13-175W G95	E27	-	50,000	15,000
	E27 CDL100-240V BR				hour(s)
929002441991	LEDGlobe13-100W G30	E27	-	50,000	15,000
	E27 CDL W ND MX				hour(s)

A-Shape LED

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color	Color rendering index (CRI)	Color Code	LLMF At End Of	Luminous Flux
			Temperature (Nom)			Nominal Lifetime (Nom)	
929003005103	11A19/LED/927/FR/P/E26/ND 4/2CT	150 degree(s)	2700 K	90	927	0.7 %	1,000 lm
929003005303	10A19/LED/950/FR/P/E26/ND 4/2CT	150 degree(s)	5000 K	90	950	0.7 %	1,000 lm
929002343133	29A21/PER/850/FR/P/E26/D/HO 4/1PF	250 degree(s)	5000 K	80	850	70 %	2,610 lm
929003004503	6.5A19/LED/927/FR/P/E26/ND 4/2CT	150 degree(s)	2700 K	90	927	0.7 %	450 lm
929003004703	5.5A19/LED/950/FR/P/E26/ND 4/2CT	150 degree(s)	5000 K	90	950	0.7 %	450 lm
929003004803	10A19/LED/927/FR/P/E26/ND 4/2CT	150 degree(s)	2700 K	90	927	0.7 %	800 lm
929003005003	9A19/LED/950/FR/P/E26/ND 4/2CT	150 degree(s)	5000 K	90	950	0.7 %	800 lm
929002333611	8.8A19/AMB/927/ND D2D 6/1FB T20	220 degree(s)	2700 K	90	927	70 %	800 lm
929001940941	8.8A19/AMB/927-22 WG 120V LA	250 degree(s)	2200 K	90	922-927	70 %	800 lm
929002036341	8.8A19/AMB/950 DIM 120V LA	250 degree(s)	5000 K	90	950	70 %	800 lm
929001234422	LED 75W A60 E27 WW 230V FR ND 2CT/SRT6	200 degree(s)	2700 K	80	827	70 %	1,055 lm
929001234822	LED 75W A60 E27 CW 230V FR ND 2CT/SRT6	200 degree(s)	4000 K	80	840	70 %	1,055 lm
929001312422	LED 100W A60 E27 CW 230V FR ND 2CT/SRT6	200 degree(s)	4000 K	80	840	70 %	1,521 lm
929001998411	BC8A19/LED/RED/ND 120V E27	120 degree(s)	-	54	-	70 %	-
929002069111	LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	150 degree(s)	2700 K	90	927	70 %	806 lm
929002327703	8.5A19/PER/927-22/FR/G/WGX 4/2FB T20	-	2200 K	90	922-927	70 %	800 lm
929001998711	BC8A19/LED/YELLOW/ND 120V E27	160 degree(s)	-	62	-	70 %	-
929003005403	14A19/LED/927/FR/P/E26/ND 4/2CT	150 degree(s)	2700 K	90	927	0.7 %	1,500 lm
929003005603	13.5A19/LED/950/FR/P/E26/ND 4/2CT	150 degree(s)	5000 K	90	950	0.7 %	1,500 lm
929002441871	LEDGlobe13-175W G95 E27 WW 100-240V BR	150 degree(s)	2700 K	80	827	70 %	1,521 lm
929002441891	LEDGlobe13-100W G30 E27 WW W ND MX	150 degree(s)	2700 K	80	827	70 %	1,521 lm
929002441971	LEDGlobe13-175W G95 E27 CDL100-240V BR	150 degree(s)	6500 K	80	865	70 %	1,521 lm
929002441991	LEDGlobe13-100W G30 E27 CDL W ND MX	150 degree(s)	6500 K	80	865	70 %	1,521 lm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003005103	11A19/LED/927/FR /P/E26/ND 4/2CT	60 Hz	60 Hz	11 W	75 W
929003005303	10A19/LED/950/F R/P/E26/ND 4/2CT	60 Hz	60 Hz	10 W	75 W
929002343133	29A21/PER/850/F R/P/E26/D/HO 4/1PF	60 Hz	60 Hz	29 W	150 W
929003004503	6.5A19/LED/927/F R/P/E26/ND 4/2CT	60 Hz	60 Hz	6.5 W	40 W
929003004703	5.5A19/LED/950/ FR/P/E26/ND 4/2CT	60 Hz	60 Hz	5.5 W	40 W
929003004803	10A19/LED/927/F R/P/E26/ND 4/2CT	60 Hz	60 Hz	10 W	60 W
929003005003	9A19/LED/950/FR /P/E26/ND 4/2CT	60 Hz	60 Hz	9 W	60 W
929002333611	8.8A19/AMB/927/ ND D2D 6/1FB T20	60 Hz	60 Hz	8.8 W	60 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929001940941	8.8A19/AMB/ 927-22 WG 120V LA	60 Hz	60 Hz	8.8 W	60 W
929002036341	8.8A19/AMB/950 DIM 120V LA	60 Hz	60 Hz	8.8 W	60 W
929001234422	LED 75W A60 E27 WW 230V FR ND 2CT/SRT6	50 to 60 Hz	50 to 60 Hz	11 W	75 W
929001234822	LED 75W A60 E27 CW 230V FR ND 2CT/SRT6	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929001312422	LED 100W A60 E27 CW 230V FR ND 2CT/SRT6	50 to 60 Hz	50 to 60 Hz	12.5 W	100 W
929001998411	BC8A19/LED/RED /ND 120V E27	50 to 60 Hz	50 to 60 Hz	8 W	-
929002069111	LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	50 to 60 Hz	50 to 60 Hz	8.5 W	70 W
929002327703	8.5A19/PER/ 927-22/FR/G/WG X 4/2FB T20	60 Hz	60 Hz	8.5 W	60 W

A-Shape LED

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929001998711	BC8A19/LED/YELLOW/ND 120V E27	50 to 60 Hz	50 to 60 Hz	8 W	-
929003005403	14A19/LED/927/FR/P/E26/ND 4/2CT	60 Hz	60 Hz	14 W	100 W
929003005603	13.5A19/LED/950/FR/P/E26/ND 4/2CT	60 Hz	60 Hz	13.5 W	100 W
929002441871	LEDGlobe13-175W G95 E27 WW 100-240V BR	50 to 60 Hz	50 to 60 Hz	13 W	175 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002441891	LEDGlobe13-100W G30 E27 WW W ND MX	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002441971	LEDGlobe13-175W G95 E27 CDL100-240V BR	50 to 60 Hz	50 to 60 Hz	13 W	175 W
929002441991	LEDGlobe13-100W G30 E27 CDL W ND MX	50 to 60 Hz	50 to 60 Hz	13 W	100 W

Temperature

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929003005103	11A19/LED/927/FR/P/E26/ND 4/2CT	-	95 °C
929003005303	10A19/LED/950/FR/P/E26/ND 4/2CT	-	95 °C
929002343133	29A21/PER/850/FR/P/E26/D/HO 4/1PF	-20 °C to 45 °C	100 °C
929003004503	6.5A19/LED/927/FR/P/E26/ND 4/2CT	-	75 °C
929003004703	5.5A19/LED/950/FR/P/E26/ND 4/2CT	-	75 °C
929003004803	10A19/LED/927/FR/P/E26/ND 4/2CT	-	85 °C
929003005003	9A19/LED/950/FR/P/E26/ND 4/2CT	-	85 °C
929002333611	8.8A19/AMB/927/ND D2D 6/1FB T20	-	95 °C
929001940941	8.8A19/AMB/927-22 WG 120V LA	-	85 °C
929002036341	8.8A19/AMB/950 DIM 120V LA	-	85 °C
929001234422	LED 75W A60 E27 WW 230V FR ND 2CT/SRT6	-	80 °C
929001234822	LED 75W A60 E27 CW 230V FR ND 2CT/SRT6	-	80 °C
929001312422	LED 100W A60 E27 CW 230V FR ND 2CT/SRT6	-	85 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929001998411	BC8A19/LED/RED/ND 120V E27	-	80 °C
929002069111	LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	-	85 °C
929002327703	8.5A19/PER/927-22/FR/G/WGX 4/2FB T20	-	-
929001998711	BC8A19/LED/YELLOW/ND 120V E27	-	80 °C
929003005403	14A19/LED/927/FR/P/E26/ND 4/2CT	-	95 °C
929003005603	13.5A19/LED/950/FR/P/E26/ND 4/2CT	-	95 °C
929002441871	LEDGlobe13-175W G95 E27 WW 100-240V BR	-	55 °C
929002441891	LEDGlobe13-100W G30 E27 WW W ND MX	-	55 °C
929002441971	LEDGlobe13-175W G95 E27 CDL100-240V BR	-	55 °C
929002441991	LEDGlobe13-100W G30 E27 CDL W ND MX	-	55 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929003005103	11A19/LED/927/FR/P/E26/ND 4/2CT	No
929003005303	10A19/LED/950/FR/P/E26/ND 4/2CT	No
929002343133	29A21/PER/850/FR/P/E26/D/HO 4/1PF	Only with specific dimmers
929003004503	6.5A19/LED/927/FR/P/E26/ND 4/2CT	No
929003004703	5.5A19/LED/950/FR/P/E26/ND 4/2CT	No
929003004803	10A19/LED/927/FR/P/E26/ND 4/2CT	No

Order Code	Full Product Name	Dimmable
929003005003	9A19/LED/950/FR/P/E26/ND 4/2CT	No
929002333611	8.8A19/AMB/927/ND D2D 6/1FB T20	No
929001940941	8.8A19/AMB/927-22 WG 120V LA	Only with specific dimmers
929002036341	8.8A19/AMB/950 DIM 120V LA	Only with specific dimmers
929001234422	LED 75W A60 E27 WW 230V FR ND 2CT/SRT6	No

A-Shape LED

Order Code	Full Product Name	Dimmable
929001234822	LED 75W A60 E27 CW 230V FR ND 2CT/SRT6	No
929001312422	LED 100W A60 E27 CW 230V FR ND 2CT/SRT6	No
929001998411	BC8A19/LED/RED/ND 120V E27	No
929002069111	LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	Yes
929002327703	8.5A19/PER/927-22/FR/G/WGX 4/2FB T20	Yes
929001998711	BC8A19/LED/YELLOW/ND 120V E27	No

Order Code	Full Product Name	Dimmable
929003005403	14A19/LED/927/FR/P/E26/ND 4/2CT	No
929003005603	13.5A19/LED/950/FR/P/E26/ND 4/2CT	No
929002441871	LEDGlobe13-175W G95 E27 WW 100-240V BR	No
929002441891	LEDGlobe13-100W G30 E27 WW W ND MX	No
929002441971	LEDGlobe13-175W G95 E27 CDL100-240V BR	No
929002441991	LEDGlobe13-100W G30 E27 CDL W ND MX	No


Mechanical and Housing

Order Code	Full Product Name	Bulb	
		Bulb Finish	Shape
929003005103	11A19/LED/927/FR/P/E26/ND 4/2CT	Frosted	A19
929003005303	10A19/LED/950/FR/P/E26/ND 4/2CT	Frosted	A19
929002343133	29A21/PER/850/FR/P/E26/D/HO 4/1PF	Frosted	A21
929003004503	6.5A19/LED/927/FR/P/E26/ND 4/2CT	Frosted	A19
929003004703	5.5A19/LED/950/FR/P/E26/ND 4/2CT	Frosted	A19
929003004803	10A19/LED/927/FR/P/E26/ND 4/2CT	Frosted	A19
929003005003	9A19/LED/950/FR/P/E26/ND 4/2CT	Frosted	A19
929002333611	8.8A19/AMB/927/ND D2D 6/1FB T20	Frosted	A19
929001940941	8.8A19/AMB/927-22 WG 120V LA	Frosted	A19
929002036341	8.8A19/AMB/950 DIM 120V LA	Frosted	A19
929001234422	LED 75W A60 E27 WW 230V FR ND 2CT/SRT6	Frosted	A60
929001234822	LED 75W A60 E27 CW 230V FR ND 2CT/SRT6	Frosted	A60










Order Code	Full Product Name	Bulb	
		Bulb Finish	Shape
929001312422	LED 100W A60 E27 CW 230V FR ND 2CT/ SRT6	Frosted	A60
929001998411	BC8A19/LED/RED/ND 120V E27	-	A19
929002069111	LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	Frosted	A60
929002327703	8.5A19/PER/927-22/FR/G/WGX 4/2FB T20	Frosted	A19
929001998711	BC8A19/LED/YELLOW/ND 120V E27	-	A19
929003005403	14A19/LED/927/FR/P/E26/ND 4/2CT	Frosted	A19
929003005603	13.5A19/LED/950/FR/P/E26/ND 4/2CT	Frosted	A19
929002441871	LEDGlobe13-175W G95 E27 WW 100-240V BR	Frosted	G95
929002441891	LEDGlobe13-100W G30 E27 WW W ND MX	Frosted	G30
929002441971	LEDGlobe13-175W G95 E27 CDL100-240V BR	Frosted	G95
929002441991	LEDGlobe13-100W G30 E27 CDL W ND MX	Frosted	G30

Approval and Application


Order Code	Full Product Name	Energy Consumption
		kWh/1000 h
929003005103	11A19/LED/927/FR/P/E26/ND 4/2CT	-
929003005303	10A19/LED/950/FR/P/E26/ND 4/2CT	-
929002343133	29A21/PER/850/FR/P/E26/D/HO 4/1PF	-
929003004503	6.5A19/LED/927/FR/P/E26/ND 4/2CT	-
929003004703	5.5A19/LED/950/FR/P/E26/ND 4/2CT	-
929003004803	10A19/LED/927/FR/P/E26/ND 4/2CT	-
929003005003	9A19/LED/950/FR/P/E26/ND 4/2CT	-
929002333611	8.8A19/AMB/927/ND D2D 6/1FB T20	- kWh
929001940941	8.8A19/AMB/927-22 WG 120V LA	-
929002036341	8.8A19/AMB/950 DIM 120V LA	-
929001234422	LED 75W A60 E27 WW 230V FR ND 2CT/SRT6	11 kWh
929001234822	LED 75W A60 E27 CW 230V FR ND 2CT/SRT6	10 kWh
929001312422	LED 100W A60 E27 CW 230V FR ND 2CT/SRT6	13 kWh
929001998411	BC8A19/LED/RED/ND 120V E27	- kWh
929002069111	LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	- kWh
929002327703	8.5A19/PER/927-22/FR/G/WGX 4/2FB T20	- kWh
929001998711	BC8A19/LED/YELLOW/ND 120V E27	- kWh
929003005403	14A19/LED/927/FR/P/E26/ND 4/2CT	-
929003005603	13.5A19/LED/950/FR/P/E26/ND 4/2CT	-
929002441871	LEDGlobe13-175W G95 E27 WW 100-240V BR	-
929002441891	LEDGlobe13-100W G30 E27 WW W ND MX	-
929002441971	LEDGlobe13-175W G95 E27 CDL100-240V BR	-
929002441991	LEDGlobe13-100W G30 E27 CDL W ND MX	-



A-Shape LED



A-Shape LED



A-Shape LED

