



Energy saving elegance with improved lumens and design versatility

Candle/Decorative LED

Philips Candle Dimmable LED Lamps offer decorative energy saving ambience with the elegant effect of incandescent candles. Available in bent, blunt and flame tip candles, their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Benefits

- \cdot Long life properties-- lowers maintenance costs by reducing re-lamp frequency
- $\boldsymbol{\cdot}$ Installs into existing candelabra and medium-base fixtures
- · Will not fade colors, avoids inventory spoilage
- · Contains no mercury
- · Emits virtually no UV/IR light in beam
- · 3-year or 5-year limited warranty depending upon operating hours

Features

- ${\boldsymbol{\cdot}}$ Dimmable* and non-dimmable versions available
- $\boldsymbol{\cdot}$ Clear design available in bent, blunt and flame tip
- 25,000-hour rated average life⁺for 3.5W Philips LED candle
- ^{*}Dimmable when using leading edge dimmers (see Philips Website: www.philips.com/ledtechguide for compatible leading edge dimmers.)
- ⁺Rated average life based on engineering testing and probability analysis.

Candle/Decorative LED

Application


• Ideal for wall sconces, chandeliers and decorative lighting in retail, office, and hospitality spaces.

Versions



LEDcandle E14 T25

Dimensional drawing




Product	D	С
LED 25W T25 E14 WW ER ND SRT4	25 mm	71 mm



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

Candle/Decorative LED





© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.