



Libra - balance between comfort and lighting performance

Libra

The elegant Libra range has been specially designed for modern energy-efficient compact fluorescent lamps. It combines high-performance optics with a unique Lighting Comfort system for a major reduction in light pollution and glare. The luminaire's aluminum body, high IP rating and Direct Link installation concept minimize installation and maintenance costs. Libra offers the perfect balance for today's public lighting.

Benefits

- Dedicated solution for energy-efficient compact fluorescent lamps
- Safe and easy installation and maintenance
- Perfect balance between design, lighting performance and comfort

Features

- Compact fluorescent optics ensure optimum lighting performance
- Maximum glare control
- Direct Link easy connection – lowers Total Cost of Ownership
- Elegant yet functional design

Application

- Traffic routes: urban main roads, cycle paths, pedestrian crossings, roundabouts, parking areas
- Residential: streets, cycle paths and footpaths, roundabouts, squares/parks and playgrounds, parking areas
- City centers: boulevards and avenues, side streets, pedestrian crossings, squares and parks, public transport, cycle paths and footpaths, parking areas
- Large outdoor areas: industrial areas, harbors, airports, waterways, rail yards

Specifications

Type	SGP630 (Post top / side entry small version) SGP631 (Side entry small version) SGP632 (Post top 0° small version) SGP635 (Post top/side entry large version) SGP636 (Side entry large version) SGP637 (Post top 0° large version)	Optical cover	Polycarbonate bowl, clear (PC)
Light source	Compact fluorescent: - 1 x MASTER PL-L 4 Pin / 2G11 / 18, 24, 36 W (small versions) and 40, 55, 80 W (large versions) - 1 x PL-L-XA / 2GX11 / 28 W - 1 x MASTER PL-L Low Temperature 4 Pin / 2G11 / 24, 36 W (small versions) and 55 W (large versions) in combination with Performer reflector	Options	Including cable Class II version Wired for cell (WFC), mini Photocell or NEMA socket Ingress protection IP66 Distribution pedestrian crossing left (DP-L) or right (DP-R) optic Electrical Connection: Direct Link + SMT, Direct Link, Direct
Lamp included	Yes (lamp color 830 or 840)	Material	Housing: die-cast aluminum Bowl: impact resistant UV stabilized clear polycarbonate Gear tray: steel plate with white reflection coating Spigot: die-cast aluminum
Ballast (integrated)	Electronic, 220-240 V / 50-60 Hz: - High Frequency Performer (HFP) - High Frequency Regulator (HFR) - High Frequency Regulator, DALI (HFD)	Color	Grey aluminum (RAL 9007) Other RAL colors available on request
Mains voltage	230 or 240 V / 50-60 Hz	Maintenance	Tool-less access by stainless steel clips, bowl hinges sideways and is held captively on opening
Dimming	Dimmable versions available	Installation	Operating temperature: -20 °C < Ta < 35 °C Post-top mounting: axial entry Ø 60 - 76 mm (76P) Side-entry mounting: lateral entry Ø 32-60 mm (60S) Recommended mounting height: 6-10 m Max SCx: 0.10 m² (small versions), 0.13 m² (large versions)
Optic	Roadlighting reflector, symmetrical (standard or performer) or pedestrian crossing Optical elementInternal louver (LO-NF)	Accessories	Adapter for Ø 60 mm post top Complete set of lighting comfort louvers

Versions



LIBRA 65 - MASTER PL-L 4 Pin - 840 neutral white - HF Performer - Dust penetration-protected, jet-proof - Symmetrical - Aluminum - Screw connection block 3-pole - Post-top for diameter 76 mm



LIBRA 65 - MASTER PL-L 4 Pin - HF Performer - Dust penetration-protected, jet-proof - Symmetrical - Aluminum - Screw connection block 3-pole - Side-entry for diameter 32 to 60 mm



LIBRA 65 - MASTER PL-L 4 Pin - Electronic high-frequency - Dust penetration-protected, jet-proof - Symmetrical - Aluminum - Screw connection block 3-pole - Post-top for diameter 60 to 76 mm



LIBRA 65 - MASTER PL-L 4 Pin - HF Performer - Dust penetration-protected, jet-proof - Symmetrical - Aluminum - Screw connection block 3-pole - Side-entry for diameter 32 to 60 mm

Approval and Application

Mech. impact protection code	IK08
Surge Protection (Common/Differential)	-

General Information

Luminaire light beam spread	-
CE mark	CE mark
Optical cover/lens type	Polycarbonate bowl/cover clear
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 5 s
Number of gear units	1 unit
Number of light sources	1 pc
Optic type	Symmetrical
Product Family Code	SGP630
UL mark	-

Light Technical

Standard tilt angle side entry	0°
Upward light output ratio	0.03

Mechanical and Housing

Color	Aluminum
-------	----------

Application Conditions

Order Code	Full Product Name	Maximum dim level
910925863724	SGP630 PL-L24W/840 HFP I S LO-NF ALU PW	-
910925863725	SGP630 PL-L36W/840 HFP I S LO-NF ALU PW	-
910925863726	SGP630 PL-L36W/840 HFP I S LO-NF ALU PZX	-
910925863727	SGP630 PL-L36W HFP I S LO-NF ALU 76	-
910925863728	SGP630 PL-L36W/840 HFP I IP66 S LO-NF AL	-
910925863730	SGP630 PL-L24W/840 HFP I S LO-NF ALU P1	-
910925863731	SGP630 PL-L24W HF II S LO-NF ALU KC 32/6	-
910925863732	SGP630 PL-L36W HF II S LO-NF ALU KC 32/6	-
910925863733	SGP630 PL-LLT36W/840 HFP I RR ALU P1 76	-
910925863734	SGP630 PL-LLT24W/840 HFP I RR ALU PW 76	-
910925863735	SGP630 PL-L36W HFR I S LO-NF ALU DDF2A D	10%
910925863761	SGP630 PL-L18W HFP I S LO-NF ALU 76	-
910925863762	SGP630 PL-L24W HFP I S LO-NF ALU 32/60S	-
910925863763	SGP630 PL-L36W HFP I S LO-NF ALU 32/60S	-
910925863736	SGP631 PL-L24W HFP I S LO-NF ALU 32/60S	-
910925863737	SGP631 PL-L36W HF II S LO-NF ALU KC 32/6	-
910925863738	SGP631 PL-L24W HF II S LO-NF ALU KC 32/6	-
910925863739	SGP635 PL-L55W HFR I S LO-NF ALU D4 76	10%
910925863740	SGP635 PL-L55W/840 HFP I S LO-NF ALU PW	-
910925863741	SGP635 PL-L55W/840 HFP I S LO-NF ALU P1	-
910925863742	SGP635 PL-L80W/840 HFP I S LO-NF ALU PW	-
910925863743	SGP635 PL-L80W/840 HFP I S LO-NF ALU P1	-
910925863745	SGP635 PL-L55W HFP I S LO-NF ALU 76	-
910925863746	SGP635 PL-L40W HF II S LO-NF ALU KC 76	-
910925863747	SGP635 PL-L40W/840 HFP I S LO-NF ALU P1	-
910925863748	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	-
910925863750	SGP635 PL-L80W HF II S LO-NF ALU KC 32/6	-
910925863751	SGP635 PL-L80W/840 HFP I RR ALU P1 76	-
910925863752	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	-
910925863753	SGP635 PL-L40W/840 HFR I S LO-NF ALU DDF	10%
910925863754	SGP635 PL-LLT55W HFR I RR ALU DDF4A D14	10%
910925863755	SGP635 PL-L80W/840 HFP I RR ALU PW 76	-
910925863764	SGP635 PL-L40W HFP I S LO-NF ALU 32/60S	-
910925863765	SGP635 PL-L55W HFP I S LO-NF ALU 32/60S	-
910925863766	SGP635 PL-L80W HFP I IP66 S LO-NF ALU 32	-
910925863759	SGP636 PL-L55W HFP I S LO-NF ALU 32/60S	-
910925863760	SGP636 PL-L80W HF II S LO-NF ALU KC 32/6	-

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910925863724	SGP630 PL-L24W/840 HFP I S LO-NF ALU PW	No	910925863734	SGP630 PL-LLT24W/840 HFP I RR ALU PW 76	No
910925863725	SGP630 PL-L36W/840 HFP I S LO-NF ALU PW	No	910925863735	SGP630 PL-L36W HFR I S LO-NF ALU DDF2A D	Yes
910925863726	SGP630 PL-L36W/840 HFP I S LO-NF ALU PZX	No	910925863761	SGP630 PL-L18W HFP I S LO-NF ALU 76	No
910925863727	SGP630 PL-L36W HFP I S LO-NF ALU 76	No	910925863762	SGP630 PL-L24W HFP I S LO-NF ALU 32/60S	No
910925863728	SGP630 PL-L36W/840 HFP I IP66 S LO-NF AL	No	910925863763	SGP630 PL-L36W HFP I S LO-NF ALU 32/60S	No
910925863730	SGP630 PL-L24W/840 HFP I S LO-NF ALU P1	No	910925863736	SGP631 PL-L24W HFP I S LO-NF ALU 32/60S	No
910925863731	SGP630 PL-L24W HF II S LO-NF ALU KC 32/6	No	910925863737	SGP631 PL-L36W HF II S LO-NF ALU KC 32/6	No
910925863732	SGP630 PL-L36W HF II S LO-NF ALU KC 32/6	No	910925863738	SGP631 PL-L24W HF II S LO-NF ALU KC 32/6	No
910925863733	SGP630 PL-LLT36W/840 HFP I RR ALU P1 76	No	910925863739	SGP635 PL-L55W HFR I S LO-NF ALU D4 76	Yes

Order Code	Full Product Name	Dimmable
910925863740	SGP635 PL-L55W/840 HFP I S LO-NF ALU PW	No
910925863741	SGP635 PL-L55W/840 HFP I S LO-NF ALU P1	No
910925863742	SGP635 PL-L80W/840 HFP I S LO-NF ALU PW	No
910925863743	SGP635 PL-L80W/840 HFP I S LO-NF ALU P1	No
910925863745	SGP635 PL-L55W HFP I S LO-NF ALU 76	No
910925863746	SGP635 PL-L40W HF II S LO-NF ALU KC 76	No
910925863747	SGP635 PL-L40W/840 HFP I S LO-NF ALU P1	No
910925863748	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	No
910925863750	SGP635 PL-L80W HF II S LO-NF ALU KC 32/6	No
910925863751	SGP635 PL-L80W/840 HFP I RR ALU P1 76	No

Order Code	Full Product Name	Dimmable
910925863752	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	No
910925863753	SGP635 PL-L40W/840 HFR I S LO-NF ALU DDF	Yes
910925863754	SGP635 PL-LLT55W HFR I RR ALU DDF4A D14	No
910925863755	SGP635 PL-L80W/840 HFP I RR ALU PW 76	No
910925863764	SGP635 PL-L40W HFP I S LO-NF ALU 32/60S	No
910925863765	SGP635 PL-L55W HFP I S LO-NF ALU 32/60S	No
910925863766	SGP635 PL-L80W HFP I IP66 S LO-NF ALU 32	No
910925863759	SGP636 PL-L55W HFP I S LO-NF ALU 32/60S	No
910925863760	SGP636 PL-L80W HF II S LO-NF ALU KC 32/6	No

General Information (1/2)

Order Code	Full Product Name	Light source	Lamp family		Lamp power
		color	Gear	code	
910925863724	SGP630 PL-L24W/840 HFP I S LO-NF ALU PW	840 neutral white	HFP	PL-L	-
910925863725	SGP630 PL-L36W/840 HFP I S LO-NF ALU PW	840 neutral white	HFP	PL-L	-
910925863726	SGP630 PL-L36W/840 HFP I S LO-NF ALU PZX	840 neutral white	HFP	PL-L	-
910925863727	SGP630 PL-L36W HFP I S LO-NF ALU 76	-	HFP	PL-L	-
910925863728	SGP630 PL-L36W/840 HFP I IP66 S LO-NF AL	840 neutral white	HFP	PL-L	36 W
910925863730	SGP630 PL-L24W/840 HFP I S LO-NF ALU P1	840 neutral white	HFP	PL-L	-
910925863731	SGP630 PL-L24W HF II S LO-NF ALU KC 32/6	-	HF	PL-L	-
910925863732	SGP630 PL-L36W HF II S LO-NF ALU KC 32/6	-	HF	PL-L	-
910925863733	SGP630 PL-LLT36W/840 HFP I RR ALU P1 76	840 neutral white	HFP	MASTER PL-L Low Temperature 4 Pin	-
910925863734	SGP630 PL-LLT24W/840 HFP I RR ALU PW 76	840 neutral white	HFP	MASTER PL-L Low Temperature 4 Pin	-
910925863735	SGP630 PL-L36W HFR I S LO-NF ALU DDF2A D	-	HF	PL-L	-
910925863761	SGP630 PL-L18W HFP I S LO-NF ALU 76	-	HFP	PL-L	-
910925863762	SGP630 PL-L24W HFP I S LO-NF ALU 32/60S	-	HFP	PL-L	-

Order Code	Full Product Name	Light source	Lamp family		Lamp power
		color	Gear	code	
910925863763	SGP630 PL-L36W HFP I S LO-NF ALU 32/60S	-	HFP	PL-L	-
910925863736	SGP631 PL-L24W HFP I S LO-NF ALU 32/60S	-	HFP	PL-L	-
910925863737	SGP631 PL-L36W HF II S LO-NF ALU KC 32/6	-	HF	PL-L	-
910925863738	SGP631 PL-L24W HF II S LO-NF ALU KC 32/6	-	HF	PL-L	-
910925863739	SGP635 PL-L55W HFR I S LO-NF ALU D4 76	-	HF	PL-L	-
910925863740	SGP635 PL-L55W/840 HFP I S LO-NF ALU PW	840 neutral white	HFP	PL-L	-
910925863741	SGP635 PL-L55W/840 HFP I S LO-NF ALU P1	840 neutral white	HFP	PL-L	-
910925863742	SGP635 PL-L80W/840 HFP I S LO-NF ALU PW	840 neutral white	HFP	PL-L	-
910925863743	SGP635 PL-L80W/840 HFP I S LO-NF ALU P1	840 neutral white	HFP	PL-L	-
910925863745	SGP635 PL-L55W HFP I S LO-NF ALU 76	-	HFP	PL-L	-
910925863746	SGP635 PL-L40W HF II S LO-NF ALU KC 76	-	HF	PL-L	-
910925863747	SGP635 PL-L40W/840 HFP I S LO-NF ALU P1	840 neutral white	HFP	PL-L	-
910925863748	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	-	HFP	MASTER PL-L Low Temperature 4 Pin	-
910925863750	SGP635 PL-L80W HF II S LO-NF ALU KC 32/6	-	HF	PL-L	-

Order Code	Full Product Name	Light source	Lamp family		Lamp power
		color	Gear	code	
910925863751	SGP635 PL-L80W/840 HFP I RR ALU P1 76	840 neutral white	HFP	PL-L	-
910925863752	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	840 neutral white	HFP	MASTER PL-L Low Temperature 4 Pin	-
910925863753	SGP635 PL-L40W/840 HFR I S LO-NF ALU DDF	840 neutral white	HF	PL-L	-
910925863754	SGP635 PL-LLT55W HFR I RR ALU DDF4A D14	-	HF	MASTER PL-L Low	-

Order Code	Full Product Name	Light source	Lamp family		Lamp power
		color	Gear	code	
910925863755	SGP635 PL-L80W/840 HFP I RR ALU PW 76	840 neutral white	HFP	PL-L	-
910925863764	SGP635 PL-L40W HFP I S LO-NF ALU 32/60S	-	HFP	PL-L	-
910925863765	SGP635 PL-L55W HFP I S LO-NF ALU 32/60S	-	HFP	PL-L	-
910925863766	SGP635 PL-L80W HFP I IP66 S LO-NF ALU 32	-	HFP	PL-L	-
910925863759	SGP636 PL-L55W HFP I S LO-NF ALU 32/60S	-	HFP	PL-L	-
910925863760	SGP636 PL-L80W HF II S LO-NF ALU KC 32/6	-	HF	PL-L	-

General Information (2/2)

Order Code	Full Product Name	Optical element
910925863724	SGP630 PL-L24W/840 HFP I S LO-NF ALU PW	-
910925863725	SGP630 PL-L36W/840 HFP I S LO-NF ALU PW	-
910925863726	SGP630 PL-L36W/840 HFP I S LO-NF ALU PZX	-
910925863727	SGP630 PL-L36W HFP I S LO-NF ALU 76	-
910925863728	SGP630 PL-L36W/840 HFP I IP66 S LO-NF AL	Internal louver not fitted
910925863730	SGP630 PL-L24W/840 HFP I S LO-NF ALU P1	-
910925863731	SGP630 PL-L24W HF II S LO-NF ALU KC 32/6	-
910925863732	SGP630 PL-L36W HF II S LO-NF ALU KC 32/6	-
910925863733	SGP630 PL-LLT36W/840 HFP I RR ALU P1 76	-
910925863734	SGP630 PL-LLT24W/840 HFP I RR ALU PW 76	-
910925863735	SGP630 PL-L36W HFR I S LO-NF ALU DDF2A D	-
910925863761	SGP630 PL-L18W HFP I S LO-NF ALU 76	-
910925863762	SGP630 PL-L24W HFP I S LO-NF ALU 32/60S	-
910925863763	SGP630 PL-L36W HFP I S LO-NF ALU 32/60S	-
910925863736	SGP631 PL-L24W HFP I S LO-NF ALU 32/60S	-
910925863737	SGP631 PL-L36W HF II S LO-NF ALU KC 32/6	-
910925863738	SGP631 PL-L24W HF II S LO-NF ALU KC 32/6	-
910925863739	SGP635 PL-L55W HFR I S LO-NF ALU D4 76	-

Order Code	Full Product Name	Optical element
910925863740	SGP635 PL-L55W/840 HFP I S LO-NF ALU PW	-
910925863741	SGP635 PL-L55W/840 HFP I S LO-NF ALU P1	-
910925863742	SGP635 PL-L80W/840 HFP I S LO-NF ALU PW	-
910925863743	SGP635 PL-L80W/840 HFP I S LO-NF ALU P1	-
910925863745	SGP635 PL-L55W HFP I S LO-NF ALU 76	-
910925863746	SGP635 PL-L40W HF II S LO-NF ALU KC 76	-
910925863747	SGP635 PL-L40W/840 HFP I S LO-NF ALU P1	-
910925863748	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	-
910925863750	SGP635 PL-L80W HF II S LO-NF ALU KC 32/6	-
910925863751	SGP635 PL-L80W/840 HFP I RR ALU P1 76	-
910925863752	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	-
910925863753	SGP635 PL-L40W/840 HFR I S LO-NF ALU DDF	-
910925863754	SGP635 PL-LLT55W HFR I RR ALU DDF4A D14	-
910925863755	SGP635 PL-L80W/840 HFP I RR ALU PW 76	-
910925863764	SGP635 PL-L40W HFP I S LO-NF ALU 32/60S	-
910925863765	SGP635 PL-L55W HFP I S LO-NF ALU 32/60S	-
910925863766	SGP635 PL-L80W HFP I IP66 S LO-NF ALU 32	-
910925863759	SGP636 PL-L55W HFP I S LO-NF ALU 32/60S	-
910925863760	SGP636 PL-L80W HF II S LO-NF ALU KC 32/6	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color
			Rendering Index
910925863724	SGP630 PL-L24W/840 HFP I S LO-NF ALU PW	4000 K	80
910925863725	SGP630 PL-L36W/840 HFP I S LO-NF ALU PW	4000 K	80

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color
			Rendering Index
910925863726	SGP630 PL-L36W/840 HFP I S LO-NF ALU PZX	4000 K	80
910925863727	SGP630 PL-L36W HFP I S LO-NF ALU 76	-	-

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color	
			Rendering	Index
910925863728	SGP630 PL-L36W/840 HFP I IP66 S LO-NF AL	4000 K		80
910925863730	SGP630 PL-L24W/840 HFP I S LO-NF ALU P1	4000 K		80
910925863731	SGP630 PL-L24W HF II S LO-NF ALU KC 32/6	-	-	-
910925863732	SGP630 PL-L36W HF II S LO-NF ALU KC 32/6	-	-	-
910925863733	SGP630 PL-LLT36W/840 HFP I RR ALU P1 76	4000 K		80
910925863734	SGP630 PL-LLT24W/840 HFP I RR ALU PW 76	4000 K		80
910925863735	SGP630 PL-L36W HFR I S LO-NF ALU DDF2A D	-	-	-
910925863761	SGP630 PL-L18W HFP I S LO-NF ALU 76	-	-	-
910925863762	SGP630 PL-L24W HFP I S LO-NF ALU 32/60S	-	-	-
910925863763	SGP630 PL-L36W HFP I S LO-NF ALU 32/60S	-	-	-
910925863736	SGP631 PL-L24W HFP I S LO-NF ALU 32/60S	-	-	-
910925863737	SGP631 PL-L36W HF II S LO-NF ALU KC 32/6	-	-	-
910925863738	SGP631 PL-L24W HF II S LO-NF ALU KC 32/6	-	-	-
910925863739	SGP635 PL-L55W HFR I S LO-NF ALU D4 76	-	-	-
910925863740	SGP635 PL-L55W/840 HFP I S LO-NF ALU PW	4000 K		80
910925863741	SGP635 PL-L55W/840 HFP I S LO-NF ALU P1	-		80
910925863742	SGP635 PL-L80W/840 HFP I S LO-NF ALU PW	4000 K		80

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color	
			Rendering	Index
910925863743	SGP635 PL-L80W/840 HFP I S LO-NF ALU P1	4000 K		80
910925863745	SGP635 PL-L55W HFP I S LO-NF ALU 76	-	-	-
910925863746	SGP635 PL-L40W HF II S LO-NF ALU KC 76	-	-	-
910925863747	SGP635 PL-L40W/840 HFP I S LO-NF ALU P1	4000 K		80
910925863748	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	-		80
910925863750	SGP635 PL-L80W HF II S LO-NF ALU KC 32/6	-	-	-
910925863751	SGP635 PL-L80W/840 HFP I RR ALU P1 76	4000 K		80
910925863752	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	4000 K		80
910925863753	SGP635 PL-L40W/840 HFR I S LO-NF ALU DDF	4000 K		80
910925863754	SGP635 PL-LLT55W HFR I RR ALU DDF4A D14	-	-	-
910925863755	SGP635 PL-L80W/840 HFP I RR ALU PW 76	4000 K		80
910925863764	SGP635 PL-L40W HFP I S LO-NF ALU 32/60S	-	-	-
910925863765	SGP635 PL-L55W HFP I S LO-NF ALU 32/60S	-	-	-
910925863766	SGP635 PL-L80W HFP I IP66 S LO-NF ALU 32	-	-	-
910925863759	SGP636 PL-L55W HFP I S LO-NF ALU 32/60S	-	-	-
910925863760	SGP636 PL-L80W HF II S LO-NF ALU KC 32/6	-	-	-

Light Technical

Order Code	Full Product Name	Standard tilt angle posttop
910925863724	SGP630 PL-L24W/840 HFP I S LO-NF ALU PW	5°
910925863725	SGP630 PL-L36W/840 HFP I S LO-NF ALU PW	5°
910925863726	SGP630 PL-L36W/840 HFP I S LO-NF ALU PZX	5°
910925863727	SGP630 PL-L36W HFP I S LO-NF ALU 76	5°
910925863728	SGP630 PL-L36W/840 HFP I IP66 S LO-NF AL	5°
910925863730	SGP630 PL-L24W/840 HFP I S LO-NF ALU P1	5°
910925863731	SGP630 PL-L24W HF II S LO-NF ALU KC 32/6	5°
910925863732	SGP630 PL-L36W HF II S LO-NF ALU KC 32/6	5°
910925863733	SGP630 PL-LLT36W/840 HFP I RR ALU P1 76	5°
910925863734	SGP630 PL-LLT24W/840 HFP I RR ALU PW 76	5°
910925863735	SGP630 PL-L36W HFR I S LO-NF ALU DDF2A D	5°

Order Code	Full Product Name	Standard tilt angle posttop
910925863761	SGP630 PL-L18W HFP I S LO-NF ALU 76	5°
910925863762	SGP630 PL-L24W HFP I S LO-NF ALU 32/60S	5°
910925863763	SGP630 PL-L36W HFP I S LO-NF ALU 32/60S	5°
910925863736	SGP631 PL-L24W HFP I S LO-NF ALU 32/60S	-
910925863737	SGP631 PL-L36W HF II S LO-NF ALU KC 32/6	-
910925863738	SGP631 PL-L24W HF II S LO-NF ALU KC 32/6	-
910925863739	SGP635 PL-L55W HFR I S LO-NF ALU D4 76	5°
910925863740	SGP635 PL-L55W/840 HFP I S LO-NF ALU PW	5°
910925863741	SGP635 PL-L55W/840 HFP I S LO-NF ALU P1	5°
910925863742	SGP635 PL-L80W/840 HFP I S LO-NF ALU PW	5°
910925863743	SGP635 PL-L80W/840 HFP I S LO-NF ALU P1	5°

Order Code	Full Product Name	Standard tilt angle posttop
910925863745	SGP635 PL-L55W HFP I S LO-NF ALU 76	5°
910925863746	SGP635 PL-L40W HF II S LO-NF ALU KC 76	5°
910925863747	SGP635 PL-L40W/840 HFP I S LO-NF ALU P1	5°
910925863748	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	5°
910925863750	SGP635 PL-L80W HF II S LO-NF ALU KC 32/6	5°
910925863751	SGP635 PL-L80W/840 HFP I RR ALU P1 76	5°
910925863752	SGP635 PL-LLT55W/840 HFP I RR ALU P1 76	5°
910925863753	SGP635 PL-L40W/840 HFR I S LO-NF ALU DDF	5°

Order Code	Full Product Name	Standard tilt angle posttop
910925863754	SGP635 PL-LLT55W HFR I RR ALU DDF4A D14	5°
910925863755	SGP635 PL-L80W/840 HFP I RR ALU PW 76	5°
910925863764	SGP635 PL-L40W HFP I S LO-NF ALU 32/60S	5°
910925863765	SGP635 PL-L55W HFP I S LO-NF ALU 32/60S	5°
910925863766	SGP635 PL-L80W HFP I IP66 S LO-NF ALU 32	5°
910925863759	SGP636 PL-L55W HFP I S LO-NF ALU 32/60S	-
910925863760	SGP636 PL-L80W HF II S LO-NF ALU KC 32/6	-

