



Malaga – contemporary style

Malaga SGS101

Malaga is a versatile road-lighting luminaire. It offers modern styling and quality lighting for safe and comfortable driving, and for area illumination, with low investment and maintenance costs. The optical system has been designed to deliver good beam control and light output. Malaga provides optimal illuminance and good uniformity when the mounting height approximately equals the road width and the mast spacing is approximately 3.5 times the road width. It is suitable for post-top and side-entry mounting; a wall-mounting bracket is also available.

Benefits

- Versatile road lighting luminaire offering modern styling and quality lighting for safe, comfortable driving and for area illumination
- Optical system delivers good beam control and light output, with optimal illuminance and good uniformity
- Designed for low investment and maintenance costs

Features

- Modern styling
- Effective beam control and uniform light distribution
- Suitable for post-top and side-entry mounting; wall-mounting bracket also available

Application

- Residential areas
- Roads
- Car parks
- Industry

Specifications

Malaga SGS101

Type	SGS101 (small version)
Light source	HID: - 1 x MASTER SON-T PIA Plus / E27 / 50, 70 W - 1 x SON / E27 / 50, 70 W - 1 x SON-I / E27 / 50, 70 W - 1 x SON-T / E27 / 50, 70 W - 1 x HPL-N / E27 / 80, 125 W
Lamp included	Yes (K) No
Gear	Electro magnetic (low loss, 230 or 240 V / 50 Hz: - Inductive (IN)
Mains voltage	230 or 240 V
Optic	3 parts optic of high finish stucco aluminum
Optical cover	Polycarbonate bowl
Ignitor	Semi-parallel (SP) Semi-parallel, self-stopping (ST)
Options	Photocell: NEMA socket (P1), Minicell (P3)
Materials and finishing	Canopy: glass-fiber-reinforced polypropylene, UV-stabilized Optical cover: polycarbonate Mounting module: die-cast aluminum, non-corrosive Gear carrier: glass-fiber-reinforced polycarbonate

Color	Grey, RAL 7035
Installation	Side-entry mounting: lateral entry Ø 42 / 60 mm Post-top mounting: axial entry Ø 42 / 60 mm Spigot is reversible for side-entry and post-top mounting Recommended mounting height: 6 m Standard tilt angle post-top: 15° Adjustable tilt angle: n/a Adjustable light distribution: n/a Max windage area: 0.09 m Max SCx values by side: 0.04 m
Maintenance	Hinged bowl with quick-release clips and easily removable gear tray
Accessories	Spigots for 34 - 42 mm side-entry and 76 mm post-top Wall-mounting bracket
Main applications	Residential areas, roads, car parks, industry

Versions

Malaga SGS101 road-lighting
luminaire with polycarbonate
bowl, side-entry mounting



Malaga SGS101 road-lighting
luminaire with flat glass, side-
entry mounting



Product details

OPDP_SGS101k_0001-Detail
photo



Malaga SGS101 road-lighting
luminaire with flat glass, post-top
mounting



Product details



Malaga SGS101 road-lighting luminaire with flat glass, side-entry mounting

Approval and Application

Mech. impact protection code IK08

General Information

Cap-Base E27
CE mark CE mark
Product Family Code SGS101

General Information

Order Code	Full Product Name	Optical cover/lens			Number of light		
		type	Gear	Lamp family code	Lamp power	sources	Optic type
26912200	SGS101 MAX125W-E27 II MR-AS 42/60	-	-	-	-	-	Moveable reflector with Allen screw
93190600	SGS101 MAX70W-E27 II MR	-	-	-	-	1	Moveable reflector
63674100	SGS101 MAX70W-E27 II MR 42/60	PC	E	-	-	1	Moveable reflector
11859800	SGS101 SON-T50W II MR SKD 42/60	PC	CONV	SON-T	50 W	1	Moveable reflector
26903000	SGS101 SON-T50W II MR-AS SKD 42/60	PC	CONV	SON-T	50 W	1	Moveable reflector with Allen screw
63456300	SGS101 SON-I-70W II MR-AS SA 42/60	PC	CONV	SON-I	70 W	1	Moveable reflector with Allen screw
63457000	SGS101 SON-T70W II MR-AS SA SKD 42/60	PC	CONV	SON-T	70 W	1	Moveable reflector with Allen screw
63458700	SGS101 SON-T70W II MR SKD 42/60	PC	CONV	SON-T	70 W	1	Moveable reflector
63459400	SGS101 SON-T70W II MR-AS SKD 42/60	PC	CONV	SON-T	70 W	1	Moveable reflector with Allen screw
11977900	SGS101 SON-TPP70W K II MR SKD 42/60A	PC	CONV	SON-TPP	70 W	1	Moveable reflector
63460000	SGS101 SON-TPP70W K II MR-AS SKD 42/60	PC	CONV	SON-TPP	70 W	1	Moveable reflector with Allen screw
11978600	SGS101 SON-I-70W-CO K II MR 42/60A	PC	CONV	SON-I	70 W	1	Moveable reflector
11862800	SGS101 SON-I-70W II MR 42/60	PC	CONV	SON-I	70 W	1	Moveable reflector
26917700	SGS101 SON-I-70W II MR-AS 42/60	PC	CONV	SON-I	70 W	1	Moveable reflector with Allen screw
63647500	SGS101 SON-T70W II MR FG SKD 42/60	FG	CONV	SON-T	70 W	1	Moveable reflector
63648200	SGS101 SON-T70W II MR-AS FG SKD 42/60	FG	CONV	SON-T	70 W	1	Moveable reflector with Allen screw

Mechanical and Housing

Order Code	Full Product Name	Color	Order Code	Full Product Name	Color
26912200	SGS101 MAX125W-E27 II MR-AS 42/60	-	63457000	SGS101 SON-T70W II MR-AS SA SKD 42/60	Sand
93190600	SGS101 MAX70W-E27 II MR	-	63458700	SGS101 SON-T70W II MR SKD 42/60	Gray
63674100	SGS101 MAX70W-E27 II MR 42/60	Gray	63459400	SGS101 SON-T70W II MR-AS SKD 42/60	Gray
11859800	SGS101 SON-T50W II MR SKD 42/60	Gray	11977900	SGS101 SON-TPP70W K II MR SKD 42/60A	Gray
26903000	SGS101 SON-T50W II MR-AS SKD 42/60	Gray	63460000	SGS101 SON-TPP70W K II MR-AS SKD 42/60	Gray
63456300	SGS101 SON-I-70W II MR-AS SA 42/60	Sand	11978600	SGS101 SON-I-70W-CO K II MR 42/60A	Gray

Malaga SGS101

Order Code	Full Product Name	Color
11862800	SGS101 SON-I-70W II MR 42/60	Gray
26917700	SGS101 SON-I-70W II MR-AS 42/60	Gray

Order Code	Full Product Name	Color
63647500	SGS101 SON-T70W II MR FG SKD 42/60	Gray
63648200	SGS101 SON-T70W II MR-AS FG SKD 42/60	Gray

Light Technical

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
26912200	SGS101 MAX125W-E27 II MR-AS 42/60	-	-
93190600	SGS101 MAX70W-E27 II MR	-	-
63674100	SGS101 MAX70W-E27 II MR 42/60	15°	15°
11859800	SGS101 SON-T50W II MR SKD 42/60	15°	15°
26903000	SGS101 SON-T50W II MR-AS SKD 42/60	15°	15°
63456300	SGS101 SON-I-70W II MR-AS SA 42/60	15°	15°
63457000	SGS101 SON-T70W II MR-AS SA SKD 42/60	15°	15°
63458700	SGS101 SON-T70W II MR SKD 42/60	15°	15°
63459400	SGS101 SON-T70W II MR-AS SKD 42/60	15°	15°

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
11977900	SGS101 SON-TPP70W K II MR SKD 42/60A	0°	0°
63460000	SGS101 SON-TPP70W K II MR-AS SKD 42/60	15°	15°
11978600	SGS101 SON-I-70W-CO K II MR 42/60A	0°	0°
11862800	SGS101 SON-I-70W II MR 42/60	15°	15°
26917700	SGS101 SON-I-70W II MR-AS 42/60	15°	15°
63647500	SGS101 SON-T70W II MR FG SKD 42/60	15°	15°
63648200	SGS101 SON-T70W II MR-AS FG SKD 42/60	15°	15°

