



EFix – for a greener office

EFix TCS260

The EFix TL5 luminaire range is a dedicated, affordable choice of innovative lighting that enables massive energy savings to be made when old electromagnetic installations are replaced by the latest Philips technology. The range's optical performance complies with the latest EN-12464 norms, ensuring improved lighting quality in every application. Used in combination with high-frequency gear, Philips MASTER TL5 lamps enable substantial energy savings to be made. These savings can be further increased by using a Luxsense daylight controller integrated into the luminaire. The practical design of EFix combines both surface-mounted (TCS260) and suspended (TPS262) luminaires in one design. Thanks to the luminaire's easily removable top cover, the beam can be adjusted to provide direct or direct/indirect lighting. EFix is supplied with lamps and is ready to install, minimizing installation time. EFix recessed TBS260 completes Philips' range of luminaires for general lighting applications in offices and shops.

Benefits

- In its segment the easiest product to install
- Dedicated TL5 luminaire design, which is appealing because of its simplicity
- Office compliant luminaire using the mini optics

Features

- Simple design
- MASTER TL5 lamps; suitable for use with high-frequency gear
- Mini optics; performance compliant with EN-12464 norms
- Integrated Luxsense daylight controller available
- Easily removable top cover: allows beam adjustment to provide direct or direct/indirect lighting

Application


- Offices
- Shops

Specifications

Type	TCS260
Light source	Fluorescent: - 1 x or 2 x MASTER TL5 / G5 / 28, 35, 49, 54, 80 W
Lamp included	Yes (lamp color 830 or 840)
Gear	Electronic, 220 - 240 V / 50 - 60 Hz: - High Frequency Performer Intelligent (HFPI) - High Frequency Performer (HFP) - High Frequency Regulator (HFR)
Optic	High-gloss optic, double parabolic, closed (C6) Semi-high-gloss optic, double parabolic (D6) Matt optic, double parabolic louvers, closed (M6) Matt mirror, ribbed cross louvers (M2) Asymmetrical mirror (A) Prismatic/opal curved polycarbonate cover in matt high-quality aluminum optic (OD)

Connection	Push-in connector, from outside
Color	White, RAL 9016 (WH) Silver, RAL 9006 (SI)
Option	Lighting controls: - Luxsense daylight controller (LX) - Actilume multi controller (ACL)
Material	Housing: pre-lacquered steel Optic: pre-lacquered steel or aluminum End cap: polycarbonate
Installation	Individual or in line; clicking the luminaire into pre-screwed ceiling brackets
Accessory	Suspension set delivered with electrical cable, ZCS260 SME WH or SI
Remarks	Delivered with lamps, push-in connector and ceiling brackets

Accessories




Suspension set with electrical cable, 3 or 5 pole

Ordercode 910925225011, 910925225411




Suspension set with electrical cable, 3 or 5 pole

Ordercode 910925225111, 910925225511



Suspension set twin, 1500 mm

Ordercode 61402200



Suspension set twin, 1500 mm

Ordercode 62212600

