



Waterproof TCW060 – just light

TCW060

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

Benefits

- Economical, compact waterproof luminaire designed for use in demanding environments
- Operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces at the same cost as a standard electromagnetic solution
- Dedicated versions available for TL5 and TL-D lamps

Features

- Dedicated versions for TL-D and TL5 lamps
- IP65
- Electronic gear
- Flexible ceiling clip

Application

- Wet environments
- Light industry
- Parking garages

Specifications

Type	TCW060	Light source	Fluorescent: – 1 or 2 x MASTER TL5 / G5 / 14, 28, 35, 49 W
------	--------	--------------	---

TCW060

	- 1 or 2 x MASTER TL-D / G13 / 18, 36, 58 W
Lamp included	No
Ballast	Electronic, High Frequency 220 - 240 V / 50 - 60 Hz: - Standard, (HFS) - Performer (HFP) - Regulator, 1-10 V (HFR) - Regulator, DALI (HFD)
Optical cover	Polycarbonate, prismatic (PCP)
Option	Emergency lighting (integrated): - 1 hour (EL1), 3 hours (EL3)
Connection	Screw connector


Material	Housing: polycarbonate, grey
	Cover: polycarbonate, UV-resistant
	Also available in compliance with Glow Wire 850°C requirements
	Ceiling clips: stainless steel
Installation	Cover clips: polycarbonate, grey or stainless steel
	Surface mounted
	Operating temperature: -15°C < T
Maintenance	Hingeable cover for easy lamp replacement
Main applications	Wet environments, light industries, parkings

Versions



Svitidlo TCW060/059 pro
přisazenou montáž/zavěšení pro
zářivky TL-D

Dimensional drawing



Product	A	B
TCW060 2xTL-D58W HF	1200 mm	1570 mm

Product details

Suspension bracket



Cover clip



TCW060


Product details



IPDP_TCW060i_0005-Detail
photo



Polar Wide Diagrams



IFPS_TCW060 2xTL-D58W HF-Polar Normal
(separate)

