



Waterproof TCW060 – just light

TCW060

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

Benefits

- Economical, compact waterproof luminaire designed for use in demanding environments
- Operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces at the same cost as a standard electromagnetic solution
- Dedicated versions available for TL5 and TL-D lamps

Features

- Dedicated versions for TL-D and TL5 lamps
- IP65
- Electronic gear
- Flexible ceiling clip

Application

- Wet environments
- Light industry
- Parking garages

Specifications

Type	TCW060	Light source	Fluorescent: – 1 or 2 x MASTER TL5 / G5 / 14, 28, 35, 49 W
------	--------	--------------	---

TCW060

	- 1 or 2 x MASTER TL-D / G13 / 18, 36, 58 W
Lamp included	No
Ballast	Electronic, High Frequency 220 - 240 V / 50 - 60 Hz: <ul style="list-style-type: none">- Standard, (HFS)- Performer (HFP)- Regulator, 1-10 V (HFR)- Regulator, DALI (HFD)
Optical cover	Polycarbonate, prismatic (PCP)
Option	Emergency lighting (integrated): <ul style="list-style-type: none">- 1 hour (EL1), 3 hours (EL3)
Connection	Screw connector

Material	Housing: polycarbonate, grey <ul style="list-style-type: none">Cover: polycarbonate, UV-resistantAlso available in compliance with Glow Wire 850°C requirementsCeiling clips: stainless steelCover clips: polycarbonate, grey or stainless steel
Installation	Surface mounted <ul style="list-style-type: none">Operating temperature: -15°C < T
Maintenance	Hingeable cover for easy lamp replacement
Main applications	Wet environments, light industries, parkings

Accessories

Ordercode 910930025618

