



Waterproof TCW060 – just light

TCW060 C

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

Benefits

- Economical, compact waterproof luminaire designed for use in demanding environments
- Operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces at the same cost as a standard electromagnetic solution
- Dedicated versions available for TL5 and TL-D lamps

Features

- Dedicated housings for TLD and for TL5 types
- Fully complies with IP65 ingress protection norms - provides protection against moderate to challenging impact of moisture and dust
- Available in 1- and 2-lamp TL-D and TL5 versions
- Electronic HF driver is energy efficient and produces less noise and flicker
- Easy-to-use clippers ensure flexibility in installation and ease in maintenance

Application

- Car parks
- Warehouses
- General industrial applications
- Food and beverage industry

Specifications

TCW060 C

Type	TCW060
Light source	Fluorescent: - 1 or 2 x TL5 / G5 / 28 W - 1 or 2 x TL-D / G13 / 18, 36 W
Lamp included	No
Ballast	Electronic, 220-240 V / 50-60 Hz: - High Frequency (HF)
Optical cover	Polycarbonate
Connection	Screw connector

Material	Housing: polycarbonate, grey Cover: polycarbonate, UV-resistant Ceiling clips: stainless steel Cover clips: polycarbonate, grey
Installation	Surface mounted Operating temperature: -15°C < T
Maintenance	Hingeable cover for easy lamp replacement
Main applications	Wet environments, light industries, parkings

Versions



TCW060 C 1xTL



TCW060 C 2xTL




TCW060 C 1xTL5




TCW060 C 2xTL5

Dimensional drawing



Product	A	B
TCW060 C 1xTL5-28W HF 220V	800 mm	1215 mm




Product	A	B
TCW060 C 2xTL-D36W HF 220V	900 mm	1270 mm
TCW060 C 2xTL-D18W HF 220V	350 mm	660 mm

TCW060 C

Dimensional drawing

A



Product	A	B
TCW060 C 2xTL5-28W HF 220V	800 mm	1215 mm

Product	A	B
TCW060 C 1xTL-D18W HF 220V	350 mm	660 mm
TCW060 C 1xTL-D36W HF 220V	900 mm	1270 mm

Product details

IPDP_TCW060c_0001-Detail photo



IPDP_TCW060c_0003-Detail photo



Operating and Electrical

Input Voltage 220 V

General Information

Gear HF

General Information

Order Code	Full Product Name	Lamp family code	Lamp power	Number of light sources
910403630026	TCW060 C 1xTL-D18W HF 220V	TL-D	18 W	1 pc

Order Code	Full Product Name	Lamp family code	Lamp power	Number of light sources
910403630028	TCW060 C 1xTL-D36W HF 220V	TL-D	36 W	1 pc

TCW060 C

Order Code	Full Product Name	Lamp family code	Lamp power	Number of light sources
910403630027	TCW060 C 2xTL-D18W HF 220V	TL-D	18 W	2 pcs
910403630029	TCW060 C 2xTL-D36W HF 220V	TL-D	36 W	2 pcs

Order Code	Full Product Name	Lamp family code	Lamp power	Number of light sources
910403630030	TCW060 C 1xTL5-28W HF 220V	TL5	28 W	1 pc
910403630031	TCW060 C 2xTL5-28W HF 220V	TL5	28 W	2 pcs

