



Waterproof TCW060 – just light

TCW060 C

灯具本体及灯罩采用聚碳酸酯材料，保证了其坚固耐用的性能；独特设计的密封圈和不锈钢搭扣使其达到 IP65 的防护等级，保证抵御水和灰尘的侵入，在潮湿和满是尘土的条件下同样能提供良好的照明效果；良好的配光在保证提供工业场所必要照明的同时，可以达到节能和降低耗电的效果；无需复杂的工具即可进行安装和维护，节约安装所要耗费的时间和成本。

优点

- 灯具本体及灯罩采用聚碳酸酯材料，保证了其坚固耐用的性能
- 独特设计的密封圈和不锈钢搭扣使其达到 IP65 的防护等级，保证抵御水和灰尘的侵入，在潮湿和满是尘土的条件下同样能提供良好的照明效果
- 极佳的配光在保证提供工业场所必要照明的同时，可以达到节能和降低耗电的效果
- 无需复杂的工具即可进行安装和维护，节约安装所要耗费的时间和成本

特点

- 为 TLD 和 TL5 光源定制不同灯体
- 灯具输出 LOR：68%
- 应用环境温度：-5 ~ +25°C

应用

- 停车场
- 仓储
- 一般的车间或装配线
- 食品与饮料行业

规格

类型	TCW060
光源	Fluorescent: - 1 or 2 x TL5 / G5 / 28 W - 1 or 2 x TL-D / G13 / 18, 36 W

包括光源	No
镇流器	Electronic, 220-240 V / 50-60 Hz: - High Frequency (HF)
光盖	Polycarbonate

TCW060 C

连接	Screw connector
材质	Housing: polycarbonate, grey
	Cover: polycarbonate, UV-resistant
	Ceiling clips: stainless steel
	Cover clips: polycarbonate, grey

安装	Surface mounted
	Operating temperature: $-15^{\circ}\text{C} < T$
维护	Hingeable cover for easy lamp replacement
主要应用	Wet environments, light industries, parkings

Versions



TCW060 C 2xTL




TCW060 C 1xTL




TCW060 C 1xTL5

二维绘图




Product	A	B
TCW060 C 2xTL-D36W HF 220V	900 mm	1270 mm
TCW060 C 2xTL-D18W HF 220V	350 mm	660 mm



Product	A	B
TCW060 C 1xTL-D36W HF 220V	900 mm	1270 mm

TCW060 C

二维绘图



Product	A	B
TCW060 C 1xTL5-28W HF 220V	800 mm	1215 mm

产品详细

IPDP_TCW060c_0001-Detail photo



IPDP_TCW060c_0003-Detail photo



运营和电气

输入电压 220 V

基本信息

装置 HF

基本信息

Order Code	Full Product Name	灯具系列代码	照明功率	光源数量	Order Code	Full Product Name	灯具系列代码	照明功率	光源数量
910403630027	TCW060 C 2xTL-D18W HF 220V	TL-D	18 W	2	910403630028	TCW060 C 1xTL-D36W HF 220V	TL-D	36 W	1
910403630029	TCW060 C 2xTL-D36W HF 220V	TL-D	36 W	2	910403630030	TCW060 C 1xTL5-28W HF 220V	TL5	28 W	1

