



# Extended design possibilities

## MASTER TL5 Circular

This circular TL5 lamp (tube diameter 16 mm) offers extended design possibilities. The slim tube allows the creation of extremely flat luminaires and enables omni-directional light distribution. It is suitable for a wide range of professional and semi-professional applications, and is ideal for use in shops, offices and public areas with unconventional layouts.

### Benefits

- Slim 16 mm tube allows creation of extremely flat luminaires
- Allows appealing circular designs
- High lamp efficacy
- Good color rendering
- Higher average system efficiency

### Features

- Perfect circular shape
- Highly efficient 3-band fluorescent coating
- Specifically designed for operation with electronic gear
- Amalgam technology (55 and 60W only)

### Application

- Brings the benefits of TL5 lighting to an even wider range of attractive applications
- Suitable for a wide range of professional and semi-professional applications
- Ideal for use in shops, offices and public areas with non-traditional lay-outs
- Amalgam lamps 55W and 60W are limited suitable for dimming applications

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# MASTER TL5 Circular

## Versions



22 W 2GX13 C-T5 16 mm

## Dimensional drawing



| Product             | D (max) | D (min) | E (min) | E (max) | I (min) | I (max) |
|---------------------|---------|---------|---------|---------|---------|---------|
| MASTER TL5 Circular | 18 mm   | 14 mm   | 293 mm  | 305 mm  | 260 mm  | 272 mm  |
| 55W/830 1CT/10      |         |         |         |         |         |         |

